


# **Ultrafast Rectifier, 15 A FRED Pt®**





PRODUCT SUMMARY					
Package	TO-220AC				
I <sub>F(AV)</sub>	15 A				
$V_{R}$	1200 V				
V <sub>F</sub> at I <sub>F</sub> at 125 °C	2.25 V				
t <sub>rr</sub>	44 ns				
T <sub>J</sub> max.	175 °C				
Diode variation	Single die				

#### **FEATURES**

- · Ultrafast and soft recovery time
- Optimized forward voltage drop
- 175 °C maximum operating junction temperature
- Polyimide passivation
- · Rugged design
- Good thermal performance
- Meets JESD 201 class 2 whisker test
- Material categorization: for definitions of compliance please see <a href="https://www.vishav.com/doc?99912"><u>www.vishav.com/doc?99912</u></a>





COMPLIANT HALOGEN FREE

### **DESCRIPTION / APPLICATIONS**

Ultrafast recovery rectifiers designed with optimized performance of forward voltage drop, recovery time, and soft recovery. Polyimide passivated, planar structure and the platinum doped life time control guarantee, ruggedness, reliability characteristics, and solid value proposition for efficiency and thermal performance.

These devices are intended for use in boost stage in the AC/DC section of SMPS, high frequency output rectification of battery charger, inverters of solar inverters, or as freewheeling diodes in motor drive.

ABSOLUTE MAXIMUM RATINGS								
PARAMETER	SYMBOL	TEST CONDITIONS	VALUES	UNITS				
Repetitive peak reverse voltage	$V_{RRM}$		1200	V				
Average rectified forward current	I <sub>F(AV)</sub>	T <sub>C</sub> = 115 °C, D = 0.50	15					
Non-repetitive peak surge current	I <sub>FSM</sub>	$T_C = 25$ °C, $t_p = 10$ ms, sine wave	150	А				
Repetitive peak forward current	I <sub>FRM</sub>		30					
Operating junction and storage temperature	T <sub>J</sub> , T <sub>Stg</sub>		-55 to +175	°C				

<b>ELECTRICAL SPECIFICATIONS</b> (T <sub>J</sub> = 25 °C unless otherwise specified)								
PARAMETER	SYMBOL	TEST CONDITIONS	MIN.	TYP.	MAX.	UNITS		
Breakdown voltage, blocking voltage	V <sub>BR</sub> , V <sub>R</sub>	Ι <sub>R</sub> = 250 μΑ	1200	-	-			
Forward voltage	V <sub>F</sub>	I <sub>F</sub> = 15 A	-	2.3	2.78	V		
		I <sub>F</sub> = 15 A, T <sub>J</sub> = 125 °C	-	2.25	2.7			
Deverage legitage everyont	I <sub>R</sub>	$V_R = V_R$ rated	-	-	80			
Reverse leakage current		T <sub>J</sub> = 125 °C, V <sub>R</sub> = V <sub>R</sub> rated	-	-	150	μΑ		
Junction capacitance	C <sub>T</sub>	V <sub>R</sub> = 200 V	-	13	-	pF		
Series inductance	L <sub>S</sub>	Measured lead to lead 5 mm from package body	-	8.0	-	nH		



<b>DYNAMIC RECOVERY CHARACTERISTICS</b> (T <sub>J</sub> = 25 °C unless otherwise specified)								
PARAMETER	SYMBOL	TEST CO	MIN.	TYP.	MAX.	UNITS		
		$I_F = 1.0 \text{ A}, dI_F/dt = 10$	00 A/μs, V <sub>R</sub> = 30 V	-	44	-		
Reverse recovery time	t <sub>rr</sub>	T <sub>J</sub> = 25 °C	I <sub>F</sub> = 15 A dI <sub>F</sub> /dt = 100 A/μs V <sub>R</sub> = 390 V	-	167	-	ns	
		T <sub>J</sub> = 125 °C		-	248	-		
Peak recovery current	I <sub>RRM</sub>	T <sub>J</sub> = 25 °C		-	6	-	А	
		T <sub>J</sub> = 125 °C		-	9	-		
Reverse recovery charge	Q <sub>rr</sub>	T <sub>J</sub> = 25 °C		-	507	-	nC	
		T <sub>J</sub> = 125 °C		-	1110	-		

THERMAL - MECHANICAL SPECIFICATIONS								
PARAMETER	SYMBOL	TEST CONDITIONS	MIN.	TYP.	MAX.	UNITS		
Thermal resistance, junction to case	R <sub>thJC</sub>		-	1.1	1.3			
Thermal resistance, junction to ambient	R <sub>thJA</sub>	Typical socket mount	-	54	60	°C/W		
Thermal resistance, case to heat sink	R <sub>thCS</sub>	Mounting surface, flat, smooth and greased	-	0.2	0.4			
Wai-lat			-	0.2	-	g		
Weight			-	0.07	-	oz.		
Mounting torque			6.0	_	12	kgf · cm		
Modifiling torquo			(5.0)		(10)	(lbf · in)		
Marking device		Case style: TO-220AC	15ETU12					
Maximum junction and storage temperature range	T <sub>J</sub> , T <sub>Stg</sub>		-55	-	175	°C		




Fig. 1 - Typical Forward Voltage Drop Characteristics




Fig. 2 - Typical Values of Reverse Current vs. Reverse Voltage






Fig. 3 - Typical Junction Capacitance vs. Reverse Voltage




Fig. 4 - Maximum Thermal Impedance Z<sub>thJC</sub> Characteristics




Fig. 5 - Maximum Allowable Case Temperature vs.
Average Forward Current




Fig. 6 - Forward Power Loss Characteristics

#### www.vishay.com

## Vishay Semiconductors




Fig. 7 - Typical Reverse Recovery Time vs. dI<sub>F</sub>/dt




Fig. 8 - Typical Reverse Recovery Time vs. dI<sub>F</sub>/dt




Fig. 9 - Typical Stored Charge vs.  $dI_F/dt$ 




Fig. 10 - Typical Stored Charge vs. dl<sub>F</sub>/dt




Fig. 11 - Typical Reverse Current vs. dl<sub>F</sub>/dt





Fig. 12 - Typical Reverse Current vs. dl<sub>F</sub>/dt






- (1) dl<sub>F</sub>/dt rate of change of current through zero crossing
  - ough zero crossing and I<sub>RRM</sub>
- (2)  $I_{RRM}$  peak reverse recovery current
- $Q_{rr} = \frac{t_{rr} \times I_{RRM}}{2}$
- (3)  $\rm t_{rr}$  reverse recovery time measured from zero crossing point of negative going  $\rm I_F$  to point where a line passing through 0.75  $\rm I_{RRM}$  and 0.50  $\rm I_{RRM}$  extrapolated to zero current.
- (5) dl<sub>(rec)M</sub>/dt peak rate of change of current during t<sub>b</sub> portion of t<sub>rr</sub>

(4) Q<sub>rr</sub> - area under curve defined by t<sub>rr</sub>

Fig. 13 - Reverse Recovery Waveform and Definitions

### **ORDERING INFORMATION TABLE**

#### **Device code**



- 1 Vishay Semiconductors product
- 2 Current rating (15 = 15 A)
- 3 E = single diode
- 4 Package:

T = TO-220

- 5 U = ultrafast recovery
- 6 Voltage rating (12 = 1200 V)
- 7 Environmental digit:

-N3 = halogen-free, RoHS-compliant, and totally lead (Pb)-free


ORDERING INFORMATION (Example)							
PREFERRED P/N QUANTITY PER TUBE MINIMUM ORDER QUANTITY PACKAGING DESCRIPTION							
VS-15ETU12-N3	50	1000	Antistatic plastic tube				

LINKS TO RELATED DOCUMENTS					
Dimensions <u>www.vishay.com/doc?95221</u>					
Part marking information	www.vishay.com/doc?95068				



### **TO-220AC**

#### **DIMENSIONS** in millimeters and inches



SYMBOL	MILLIN	IETERS	INC	INCHES	
STIVIBUL	MIN.	MAX.	MIN.	MAX.	NOTES
А	4.25	4.65	0.167	0.183	
A1	1.14	1.40	0.045	0.055	
A2	2.56	2.92	0.101	0.115	
b	0.69	1.01	0.027	0.040	
b1	0.38	0.97	0.015	0.038	4
b2	1.20	1.73	0.047	0.068	
b3	1.14	1.73	0.045	0.068	4
С	0.36	0.61	0.014	0.024	
c1	0.36	0.56	0.014	0.022	4
D	14.85	15.25	0.585	0.600	3
D1	8.38	9.02	0.330	0.355	
D2	11.68	12.88	0.460	0.507	6
Е	10.11	10.51	0.398	0.414	3, 6

SYMBOL	MILLIN	IETERS	INCHES		NOTES
STIVIBUL	MIN.	MAX.	MIN.	MAX.	NOTES
E1	6.86	8.89	0.270	0.350	6
E2	-	0.76	-	0.030	7
е	2.41	2.67	0.095	0.105	
e1	4.88	5.28	0.192	0.208	
H1	6.09	6.48	0.240	0.255	6, 7
L	13.52	14.02	0.532	0.552	
L1	3.32	3.82	0.131	0.150	2
L3	1.78	2.13	0.070	0.084	
L4	0.76	1.27	0.030	0.050	2
ØΡ	3.54	3.73	0.139	0.147	
Q	2.60	3.00	0.102	0.118	
θ	90° t	o 93°	90° t	o 93°	

#### Notes

- (1) Dimensioning and tolerancing as per ASME Y14.5M-1994
- (2) Lead dimension and finish uncontrolled in L1
- (3) Dimension D, D1 and E do not include mold flash. Mold flash shall not exceed 0.127 mm (0.005") per side. These dimensions are measured at the outermost extremes of the plastic body
- (4) Dimension b1, b3 and c1 apply to base metal only
- (5) Controlling dimension: inches
- (6) Thermal pad contour optional within dimensions E, H1, D2 and E1
- (7) Dimension E2 x H1 define a zone where stamping and singulation irregularities are allowed
- (8) Outline conforms to JEDEC TO-220, D2 (minimum) where dimensions are derived from the actual package outline



## **Legal Disclaimer Notice**

Vishay

### **Disclaimer**

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.