

**TS TTB 6 VT****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

The test socket is used to connect test devices with a standard 4.0 plug with widths up to 10 mm into the terminal. Test sockets are arranged at an angle, therefore all standard measurements (even adjoining) can be realised within the terminal width of 8.1 mm. Once mounted, the test socket cannot be removed from the application.

**General ordering data**

Order No.	<a href="#">2710530000</a>
Type	TS TTB 6 VT
GTIN (EAN)	4050118881097
Qty.	48 pc(s).

## TS TTB 6 VT

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	51.3 mm	Depth (inches)	2.02 inch
Height	9.4 mm	Height (inches)	0.37 inch
Width	6.3 mm	Width (inches)	0.248 inch
Net weight	1.1 g		

## Temperatures

Storage temperature	-25 °C...55 °C	Continuous operating temp., min.	-60 °C
Continuous operating temp., max.	130 °C		

## Material data

Material	Wemid	Colour	violet
UL 94 flammability rating	V-0		

## Additional technical data

Explosion-tested version	No	Type of fixing	Plugged
Type of mounting	Plugged		

## Dimensions

Metric size of the thread, external	0 mm	Plug-in depth	11.5 mm
-------------------------------------	------	---------------	---------

## General

Operating temperature range, max.	130 °C
-----------------------------------	--------

## Classifications

ETIM 6.0	EC002848	ETIM 7.0	EC002848
ETIM 8.0	EC002848	ECLASS 9.0	27-14-11-92
ECLASS 9.1	27-14-11-92	ECLASS 10.0	27-14-11-92
ECLASS 11.0	27-14-11-92	ECLASS 12.0	27-14-11-92

## Approvals

ROHS	Conform
------	---------

## Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">EPLAN</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>