

Würth Elektronik eiSos GmbH & Co. KG

EMC & Inductive Solutions

Max-Eyth-Straße 1 · 74638 Waldenburg · Germany

Tel. +49 (0) 79 42 945-0 · Fax +49 (0) 79 42 945-400

eiSos@we-online.de · www.we-online.de



Product/Process Change Notice (PCN)

- Major change
 Minor change

PCN #: PCN_FeSTAR-BUENO_20180301

Product Affected: 74275812, 74275812S

PCN Date: December 1st, 2017

Effective Date: March 1st, 2018

Contact: Product Management

Phone: +49 (0) 7942 - 945 5001

Fax: +49 (0) 7942 - 945 5179

E-mail: pcn.eisos@we-online.de

- Product Mark
 Date Code
 Packaging
 Others

Attachment: Yes No

Samples:

DESCRIPTION AND PURPOSE OF CHANGE:

In order to improve the transportation and handling safety, Würth Elektronik will change the packaging by implementing a new tray design.

All products with date code 2018-03-01 or later, will be affected by this packaging change.

Würth Elektronik eiSos GmbH & Co. KG

EMC & Inductive Solutions

Max-Eyth-Straße 1 · 74638 Waldenburg · Germany

Tel. +49 (0) 79 42 945-0 · Fax +49 (0) 79 42 945-400

eiSos@we-online.de · www.we-online.de

**DETAIL OF CHANGE:**

The tray changes in the design and in the size from a PET plastic tray to a paper mould tray. Due to this change, the packaging size and standard packaging quantity will change as detailed in the table below.

The carton box material will remain double wall corrugated cardboard.

	Unit	New Packaging	Old Packaging
Carton Packaging Quantity (CPQ)	pcs	448	160
Standard Packaging Quantity (SPQ)	pcs	56	40
Number of trays	pcs	8	4
Moisture Impermeable Bag (MIB)		yes	yes
Dimensions of the carton (LxWxH)	mm	400 x 300 x 163	400 x 300 x 140
Dimensions of the tray (LxWxH)	mm	370 x 280 x 12	340 x 260 x 18
Weight of a CPQ	g	6500	3300
Weight of a SPQ	g	800	560

New Packaging:**RELIABILITY / QUALIFICATION SUMMARY:**

1. Drop test according to DIN EN 22248 "Packaging; complete, filled transport packages; vertical impact test by dropping (ISO 2248:1985)" has been done.
2. Vibrations test according to MIL-STD-202 Method 204 has been done under the following test conditions:

Acceleration: 10G

Frequency range: 15-2000Hz

Duration: 4 hours at Z axis

DATA SHEET CHANGE: Yes No