

High-Voltage, ±15kV ESD-Protected Electroluminescent Lamp Driver

General Description

The MAX4990 high-voltage DC-AC converter is ideal for driving electroluminescent (EL) lamps. The MAX4990 features a wide +2.4V to +5.5V input range that allows the device to accept a wide variety of voltage sources such as single-cell lithium-ion (Li+) batteries and higher voltage battery chargers. The lamp outputs of the device generate up to 250V peak-to-peak output voltage for maximum lamp brightness.

The MAX4990 utilizes an inductor-based boost converter to generate the high voltage necessary to drive an EL lamp. The boost-converter switching frequency is set with the combination of an external capacitor connected from SW to GND and an external resistor connected from SLEW to GND.

The MAX4990 uses a high-voltage full-bridge output stage to convert the high voltage generated by the boost converter to an AC waveform suitable for driving the EL panel. The EL output switching frequency is set with the combination of an external capacitor connected from EL to GND and an external resistor connected from SLEW to GND.

The MAX4990 uses a proprietary acoustic noise-reduction circuit that controls the slew rate of the AC voltage, reducing audible noise from the EL panel. The slew rate is set with an external resistor connected from SLEW to GND.

The MAX4990 features an EL lamp dimming control (DIM) that allows the user to set the EL output voltage with a PWM signal, a DC analog voltage, or a resistor connected from the DIM input to GND. A capacitor placed in parallel to the resistor on DIM allows the user to program a slow turn-on/-off time that generates a soft fade-on/fade-off effect of the EL lamp.

The MAX4990 enters a low-power shutdown mode (100nA max) when the EN and DIM inputs are connected to GND. The MAX4990 also enters thermal shutdown if the die temperature rises above +158°C.

The MAX4990 is available in a space-saving, 14-pin, $3mm \times 3mm$ TDFN package and is specified over the extended -40°C to +85°C operating temperature range.

Typical Application Circuits appear at end of data sheet.

Features

- ESD-Protected EL Lamp Outputs ±15kV Human Body Model ±4kV IEC 61000-4-2 Contact Discharge ±15kV IEC 61000-4-2 Air-Gap Discharge
- ♦ 250V_{P-P} (MAX) Output for Highest Brightness
- Wide +2.4V to +5.5V Input Voltage Range
- Resistor-Adjustable Slew-Rate Control for Audible Noise Reduction
- Externally Driven Lamp and Switching Converter Frequencies
- Capacitor-Adjustable Lamp and Switching Converter Frequencies
- Low 100nA Shutdown Current
- DIM Input for Controlling Output Voltage Through DC Analog Voltage, PWM, or Resistor to GND
- Capacitor Adjustable for Slow Turn-On/-Off
- Space-Saving Packages 14-Pin, 3mm x 3mm TDFN

Applications

Keypad Backlighting MP3 Players LCD Backlighting PDAs/Smartphones Automotive Instrument Clusters

Pin Configuration



Ordering Information

PART	PIN-PACKAGE	TOP MARK	PKG CODE	±15kV PROTECTION	DIM CONTROL	SLEW-RATE CONTROL
MAX4990ETD+	14 TDFN-EP (3mm x 3mm)	ADL	T1433-2	Yes	Yes	Yes

Note: The device operates over the -40°C to +85°C operating temperature range.

+Denotes a lead-free package.

EP = Exposed paddle.

Maxim Integrated Products 1

For pricing, delivery, and ordering information, please contact Maxim Direct at 1-888-629-4642, or visit Maxim's website at www.maxim-ic.com.

ABSOLUTE MAXIMUM RATINGS

(All voltages referenced to GND.)

V _{DD}	0.3V to +7V
CS, LX	-0.3V to +160V
VA, VB	0.3V to (V _{CS} + 0.3V)
EN, EL, SLEW, DIM, SW	0.3V to (VDD + 0.3V)
Continuous Power Dissipation ($T_A = -$	+70°C)

14-Pin TDFN (derate 24.4mW/°C above +70°C) 1951mW

Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

ELECTRICAL CHARACTERISTICS

 $(V_{DD} = +2.4V \text{ to } +5.5V, C_{LAMP} = 10nF, C_{CS} = 3.3nF, L_X = 220\mu H (I_{SAT} = 170mA, R_S = 5.5\Omega), T_A = T_{MIN} \text{ to } T_{MAX}$, unless otherwise noted. Typical values are at $V_{DD} = +3.0V$ and $T_A = +25^{\circ}C$.) (Note 1)

PARAMETER	SYMBOL	CONDITIONS	MIN	ТҮР	МАХ	UNITS	
Power-Supply Voltage	V _{DD}		2.4		5.5	V	
Power-Supply Current	IDD	$R_{SLEW} = 375k\Omega$, slope = 30V/100µs; f _{EL} = 200Hz, V _A - V _B = 250V _{P-P}			350	μA	
Shutdown Supply Current		$EN = 0V$, $DIM = 0V$, $T_A = +25^{\circ}C$		25	100	۳٨	
Shutdown Supply Current	15HDN	$EN = 0V$, $DIM = 0V$, $T_A = -40^{\circ}C$ to $+85^{\circ}C$	300		ΠA		
Shutdown Inductor Supply Current	ILX _{SHDN}	$EN = 0V$, $DIM = 0V$, $LX = V_{DD}$, $CS = V_{DD}$			1500	nA	
Undervoltage Lockout	VLO	V _{DD} rising	1.8	2.1	2.3	V	
UVLO Hysteresis	V _{HYST}			125		mV	
EL OUTPUTS (VA - VB)							
		$V_{DD} = +3V, DIM = +0.5V$	84	100	122		
Peak-to-Peak Output Voltage	VA - VB	$V_{DD} = +3V$, DIM = $+1V$	170	200	230	V	
		$V_{DD} = +3V, DIM = +1.3V$	210	250	280		
Pulldown Switch On-Resistance	R _{ONPD}	$I_{SINK} = 1mA, V_{CS} = +10V,$ $V_A, V_B < +0.6V, V_{DD} = +3V$	50	165	500	Ω	
Pullup Switch On-Resistance	Ronpu	$V_{CS} = +125V, I_{SOURCE} = 1mA$	700	1500	2200	Ω	
Switch Off Lookaga	I _{LKG_NMOS}	V_A = +125V, V_B = +125V, shutdown mode, V_{CS} = +125V	-1		+1		
Switch On-Leakage	ILKG_PMOS	$V_A = 0V, V_B =$ unconnected, shutdown mode, $V_{CS} = +125V$	-60		+60	μΑ	
V_A , V_B Differential Resistor	V _{AB_RES}	$V_A = +0.1V$, $V_B = 0V$, shutdown mode, CS = unconnected	2		7	MΩ	
EL Lamp Switching Frequency	fEL	C_{EL} = 872pF, R_{SLEW} = 375k Ω	210	250	290	Hz	
		Human Body Model		±15			
ESD Protection (V _A , V _B Only)		IEC 61000-4-2 Contact Discharge		±4		kV	
		IEC 61000-4-2 Air-Gap Discharge		±15			

ELECTRICAL CHARACTERISTICS (continued)

 $(V_{DD} = +2.4V \text{ to } +5.5V, C_{LAMP} = 10nF, C_{CS} = 3.3nF, L_X = 220\mu\text{H} (I_{SAT} = 170\text{mA}, R_S = 5.5\Omega), T_A = T_{MIN} \text{ to } T_{MAX}$, unless otherwise noted. Typical values are at $V_{DD} = +3.0V$ and $T_A = +25^{\circ}\text{C.}$ (Note 1)

	SVMBOL	CONDITIONS	MIN	TVD	MAY	
	STMBOL	CONDITIONS	IVIIIN	ITP	IVIAA	UNITS
BOOST CONVERTER			40	50	01	
		$V_{DD} = +3V$, DIM = +0.5V forced externally	42	50	10	
Output Peak voitage	VCS	$V_{DD} = +3V$, DIM = + IV forced externally	85	100	115	V
		$V_{DD} = +3V$, DIM = +1.3V forced externally	105	125	140	
Boost Switching Frequency	fsw	$C_{SW} = 96 pF, R_{SLEW} = 375 k\Omega$	80	100	120	kHz
Switch On-Resistance	RLX	$I_{SINK} = 25 \text{mA}, V_{DD} = +3 \text{V}$			20	Ω
LX Leakage Current	ILX	$V_{LX} = +125V$	-1		+1	μA
CS Input Current	I _{CS}	No load, $V_{CS} = +125V$, EN = 0V, DIM = 0V			50	μA
CONTROL INPUT SW		1	1			r
Input Voltage-High Threshold	VIH_SW	$R_{SLEW} = 375 k\Omega$	0.9	0.98	1.06	V
Input Voltage-Low Threshold	VIL_SW	$R_{SLEW} = 375 k\Omega$	0.43	0.49	0.55	V
Input Low Current	I _{IL_SW}	$R_{SLEW} = 375 k\Omega$, $CS = +40V$, $EL = V_{DD}$, DIM = V_{DD}	43		77	μA
Input High Current	I _{IH_SW}	$R_{SLEW} = 375k\Omega$, $CS = +40V$, $EL = V_{DD}$, DIM = V_{DD}	5.0		7.5	μA
CONTROL INPUT EL	1					
Input Voltage-High Threshold	VIH CEL	$R_{SLEW} = 375 k\Omega$	1.08		1.32	V
Input Voltage-Low Threshold	VIL CEL	$R_{SLEW} = 375 k\Omega$	0.22		0.39	V
Input Low Current		$R_{SLEW} = 375 k\Omega$	1.2		1.87	μA
Input High Current		$R_{SLEW} = 375 k\Omega$	1.2		1.87	μA
CONTROL INPUT SLEW						
Force Voltage	VFORCE	$I_{SOURCE} = 20\mu A$	0.89	0.95	1.04	V
High-Voltage Output Slew Rate		$R_{SLEW} = 375 k\Omega$		30		V/100µs
CONTROL INPUT DIM						. · · ·
Input Logic-High Voltage	Vih dim	Output voltage (max)	1.3			V
Input Logic-Low Voltage	Vil dim	Output voltage (off)			0.15	V
Input Low Current		$V_{\text{DIM}} = 0$ V, RSI FW = 375k Ω	2.22		3.0	μA
Input High Current	Ін рім		-1		+1	μA
PWM Frequency Range				0.2 to 1		MHz
Low-Peak Detector Threshold	Vipd		0.15		0.35	V
Low-Peak Detector Hysteresis	VIPD HYST			100		mV
CONTROL INPUT EN	2.2_1101	1	1			1
Input Voltage-High Threshold	Vih en		1.2			V
Input Voltage-Low Threshold	VIL FN		1		0.2	V
Input Low Current	IIL FN		-1		+1	μA
Input High Current	IIH EN		-1		+1	μA

ELECTRICAL CHARACTERISTICS (continued)

 $(V_{DD} = +2.4V \text{ to } +5.5V, C_{LAMP} = 10$ nF, C_{CS} = 3.3nF, L_X = 220 μ H (I_{SAT} = 170mA, R_S = 5.5 Ω), T_A = T_{MIN} to T_{MAX}, unless otherwise noted. Typical values are at V_{DD} = +3.0V and T_A = +25°C.) (Note 1)

PARAMETER	SYMBOL	CONDITIONS	MIN	ТҮР	MAX	UNITS
THERMAL SHUTDOWN						
Thermal Shutdown				158		°C
Thermal Shutdown Hysteresis				8		°C

Note 1: Specifications at $T_A = -40^{\circ}C$ are guaranteed by design and not production.

Typical Operating Characteristics

 $(V_{DD} = +3.6V, C_{LAMP} = 10nF, C_{CS} = 3.3nF, L_X = 220 \mu H (I_{SAT} = 170mA, R_S = 5.5\Omega), R_{SLEW} = 390 k\Omega, DIM = V_{DD}, C_{SW} = 100 pF, C_{EL} = 1.2nF, T_A = +25^{\circ}C$, unless otherwise noted.)



MAX4990

Typical Operating Characteristics (continued)



(V_{DD} = +3.6V, C_{LAMP} = 10nF, C_{CS} = 3.3nF, L_X = 220μH (I_{SAT} = 170mA, R_S = 5.5Ω), R_{SLEW} = 390kΩ, DIM = V_{DD}, C_{SW} = 100pF,

MAX4990

Typical Operating Characteristics (continued)

(V_{DD} = +3.6V, C_{LAMP} = 10nF, C_{CS} = 3.3nF, L_X = 220μH (I_{SAT} = 170mA, R_S = 5.5Ω), R_{SLEW} = 390kΩ, DIM = V_{DD}, C_{SW} = 100pF, $C_{EL} = 1.2$ nF, $T_A = +25$ °C, unless otherwise noted.)



6

Pin Description

PIN	NAME	FUNCTION
1	SLEW	High-Voltage Slew-Rate Control. Connect an external resistor, RSLEW, to GND to set the slew rate of the VA and VB high-voltage outputs.
2	EN	Enable Input. Drive EN > +1.2V and DIM > +0.35V to turn on the device. Drive EN < +0.2V and DIM < +0.15V to turn off the device.
3	DIM	EL Panel Dimming Control. Apply a PWM signal or DC analog control signal, or connect a resistor to GND to adjust peak-to-peak output voltage. Use DIM together with EN to control device shutdown (see <i>Shutdown</i> section).
4	EL	EL Voltage Switching Frequency. Connect an external capacitor, CEL, to GND or drive with an external oscillator to set the switching frequency of the VA and VB high-voltage outputs. Connect EL to GND to shut off the EL oscillator. Drive EL high to keep alternatively VA or VB output high.
5	SW	Boost-Converter Switching Frequency. Connect an external capacitor, CSW, to GND or drive with an external oscillator to set the switching frequency of the boost converter. Connect SW to GND to shut off the boost oscillator. Do not keep SW high to avoid LX shorting to GND, which causes the internal die temperature to increase. The MAX4990 is protected by entering a themal-shutdown state. (See the <i>Thermal Short-Circuit Protection</i> section.)
6	VDD	Power-Supply Voltage
7	GND	Ground
8	LX	Internal Switching DMOS Drain Connection. Connect LX to a switching inductor and an anode of a rectifying diode.
9, 11, 13	N.C.	No Connection. Leave N.C. unconnected.
10	CS	High-Voltage Supply. Connect CS to output capacitor of boost converter.
12	VB	High-Voltage EL Panel Output. Connect to non-VA side of EL lamp.
14	VA	High-Voltage EL Panel Output. Connect to non-VB side of EL lamp.
EP	EP	Exposed Pad. Connect exposed pad to GND.

Detailed Description

The MAX4990 high-voltage DC-AC converter is ideal for driving EL lamps. The MAX4990 features a wide +2.4V to +5.5V input range that allows the device to accept a wide variety of voltage sources such as single cell Li+ batteries and higher voltage battery chargers. The lamp outputs of the device generate up to 250V peak-to-peak output voltage for maximum lamp brightness.

The MAX4990 utilizes an inductor-based boost converter that allows for the use of a 220µH inductor to generate the high voltage necessary to drive an EL lamp. The boost converter switching frequency is set with the combination of an external capacitor connected from the SW input to GND and an external resistor connected from SLEW to GND. Applying a PWM signal to the SW input allows the switching frequency of the boost converter to take the frequency of the PWM signal. The MAX4990 uses a high-voltage full-bridge output stage to convert the high voltage generated by the boost converter to an AC waveform suitable for driving the EL panel. The EL output switching frequency is set with the combination of an external capacitor connected from EL to GND and an external resistor connected from SLEW to GND. The MAX4990 allows programmability of the EL Lamp output frequency by applying a clock signal to the EL input. Applying a clock signal to the EL input allows the switching frequency of the lamp to take the frequency of the clock signal divided by 4 to switch at the EL input frequency divided by 4.

The MAX4990 uses a proprietary acoustic noise-reduction circuit to control the slew rate of the AC voltage, reducing audible noise from the EL panel. The slew rate is set with an external resistor connected from SLEW to GND.

The MAX4990 enters a low-power shutdown mode (100nA max) when EN and DIM inputs are connected



to GND. The MAX4990 also enters thermal shutdown if the die temperature rises above +158°C.

The MAX4990 features an EL lamp dimming control (DIM) that allows the user to set the EL output voltage with a PWM, DC analog voltage, or a resistor connected to GND. A capacitor placed in parallel to the resistor on the DIM input allows the user to program a slow turn-on/-off time of the MAX4990's outputs to generate a soft fade-on/fade-off effect of the EL lamp.

The high-voltage outputs are ESD protected up to ± 15 kV Human Body Model, ± 15 kV Air-Gap Discharge, and ± 4 kV Contact Discharge, as specified in the IEC 61000-4-2 specification.

EL Output Voltage

The slew rate, frequency, and peak-to-peak voltage of the MAX4990 EL lamp outputs are programmed through a combination of external components and/or DC inputs.

The device uses resistor R_{SLEW} to set the bias current used as a reference current for the MAX4990 internal circuitry. The reference current directly affects the slew rate of the EL lamp output. Increasing the value of R_{SLEW} decreases the slew rate, and decreasing the value of R_{SLEW} increases the slew rate. (See the R_{SLEW} *Resistor Selection* section on how to select R_{SLEW} .)

The MAX4990 EL lamp output frequency uses an internal EL oscillator to set the desired frequency. The output frequency is adjusted by either 1) the combination of a resistor from SLEW to GND and an external capacitor from the EL input to GND, or 2) by driving a clock signal directly into the EL input. (See the *C_{EL} Capacitor Selection* section for choosing the C_{EL} capacitor value.)

The peak-to-peak voltage of the EL lamp output is varied from $70V_{P-P}$ to $250V_{P-P}$ by applying an external DC voltage ranging from +0.35V to +1.3V to the DIM input.



Increasing the voltage on the DIM input increases the peak-to-peak voltage, and decreasing the voltage on the input decreases the peak-to-peak voltage. The EL lamp peak-to-peak voltage is also adjusted by applying a PWM signal to the DIM input. The duty cycle of the PWM determines the EL lamp output peak-to-peak voltage. As the duty cycle is increased, the peak-to-peak output voltage is increased, and as the duty cycle is decreased, the peak-to-peak voltage is decreased. The MAX4990 also features a slow turn-on and slow turn-off time feature that is enabled by connecting a resistor and capacitor from DIM to GND (see the Typical Application Circuits and the RDIM Resistor and CDIM Capacitor Selection section). This slow turn-on/-off feature causes the peak-to-peak voltage of the EL outputs to slowly rise from zero to the maximum set value when the device is enabled. This feature also causes the peak-to-peak voltage of the EL outputs to fall from the maximum set value to zero when the device is placed into shutdown. The slow rise and fall of the peak-to-peak EL output voltage creates a soft fade-on and fade-off of the EL lamp, rather than an abrupt change in brightness.

Boost Converter

The MAX4990 boost converter consists of an external inductor from V_{DD} to the LX input, an internal DMOS switch, an external diode from LX to the CS output, an external capacitor from the CS output to GND, and the EL lamp, C_{LAMP}, connected to the EL lamp outputs. When the DMOS switch is turned on, LX is connected to GND, and the inductor is charged. When the DMOS switch is turned off, the energy stored in the inductor is transferred to the capacitor C_{CS} and the EL lamp.

Note: Keeping SW high shorts LX to GND, causing the internal die temperature to increase. The MAX4990 is protected by entering a thermal-shutdown state (See the *Thermal Short-Circuit Protection* section.)

The MAX4990 boost converter frequency uses an internal switch oscillator to set the desired frequency of the boost converter. The boost converter frequency is adjusted by either 1) the combination of a resistor from SLEW to GND and an external capacitor from SW to GND, or 2) by driving a PWM signal directly into the SW input. When SW is driven with an external PWM signal at a suggested 90% duty cycle, the boost converter frequency is changed to the frequency of the external PWM signal. (See the *CsW Capacitor Selection* section for choosing the CsW capacitor value.)

Dimming Control

The MAX4990 features a dimming control input, DIM, that controls the peak-to-peak voltage on the lamp outputs V_A and V_B . DIM is controlled by a resistor con-



The duty cycle of a PWM signal to the DIM input is internally translated into a DC voltage with the 0 to +1.22V range. The DIM input accepts the frequency range of 200kHz to 1MHz. As the duty cycle increases, the peak-to-peak voltage of the output increases, and as the duty cycle decreases, the peak-to-peak voltage of the output decreases.

The peak-to-peak voltage is adjusted by applying a DC voltage to the DIM input. Increasing the voltage on DIM increases the peak-to-peak output, and decreasing the voltage on DIM decreases the peak-to-peak output voltage.

The DIM input, in combination with the EN input, controls the shutdown mode of the MAX4990 shutdown. (See the *Shutdown* section.)

Slow Turn-On, Slow Turn-Off

The MAX4990 provides a slow turn-on/-off feature by connecting a resistor in parallel with a capacitor connected from the DIM input to GND (see the *R_{DIM} Resistor and C_{DIM} Capacitor Selection* section). When EN is driven high, the reference current I_B (set by R_{SLEW}) is used to charge capacitor C_{DIM}. When EN is driven to GND, I_B is removed, and the voltage on the capacitor C_{DIM} and resistor decays with a time constant of R_{DIM} x C_{DIM}. A slow turn-on effect is seen by driving EN high. The slow rise and fall of the voltage on DIM during transitions on the EN input modulates the peak-to-peak voltage of the EL outputs, creating a soft fade-on/-off effect at the EL lamp.

Shutdown

The MAX4990 features an enable logic input, EN, to enable and disable the device. To enable the device, apply +1.2V or greater to the EN input and +0.35V or greater to the DIM input. To place the device in shutdown, apply +0.2V or less to the EN input, and +0.15V or less to the DIM input.

Undervoltage Lockout (UVL0)

The MAX4990 has a UVLO threshold of +2.1V (typ). When V_{DD} falls below +2.1V (typ), the device enters a nonoperative mode.

Thermal Short-Circuit Protection

The MAX4990 enters a nonoperative mode if the internal die temperature of the device reaches or exceeds +158°C (typ). The device turns back on when the internal die temperature cools to +150°C.



±15kV ESD Protection

As with all Maxim devices, ESD-protection structures are incorporated on all pins to protect against electrostatic discharges encountered during handling and assembly. The EL lamp driver outputs of the MAX4990 have extra protection against static electricity. Maxim's engineers have developed state-of-the-art structures to protect these pins against ESD of ± 15 kV without damage. The ESD structures withstand high ESD in all states: normal operation, shutdown, and powered down. After an ESD event, the MAX4990 keep working without latchup or damage.

ESD protection can be tested in various ways. The transmitter EL lamp outputs of the MAX4990 are characterized for protection to the following limits:

- ±15kV using the Human Body Model
- ±4kV IEC 61000-4-2 Contact Discharge
- ±15kV IEC 61000-4-2 Air-Gap Discharge

ESD Test Conditions

ESD performance depends on a variety of conditions. Contact Maxim for a reliability report that documents test setup, test methodology, and test results.

Human Body Model

Figure 1a shows the Human Body Model, and Figure 1b shows the current waveform it generates when discharged into a low impedance. This model consists of a 100pF capacitor charged to the ESD voltage of interest, which is then discharged into the test device through a $1.5 k\Omega$ resistor.

IEC 61000-4-2

The IEC 61000-4-2 standard covers ESD testing and performance of finished equipment. However, it does not specifically refer to integrated circuits. The MAX4990 assists in designing equipment to meet IEC 61000-4-2 without the need for additional ESD-protection components.

The major difference between tests done using the Human Body Model and IEC 61000-4-2 is higher peak current in IEC 61000-4-2 because series resistance is lower in the IEC 61000-4-2 model. Hence, the ESD withstand voltage measured to IEC 61000-4-2 is generally lower than that measured using the Human Body Model. Figure 1c shows the IEC 61000-4-2 model, and Figure 1d shows the current waveform for IEC 61000-4-2 ESD Contact Discharge test.

Machine Model

The machine model for ESD tests all pins using a 200pF storage capacitor and zero discharge resistance.

The objective is to emulate the stress caused when I/O pins are contacted by handling equipment during test and assembly. Of course, all pins require this protection.

The Air-Gap test involves approaching the device with a charged probe. The Contact Discharge method connects the probe to the device before the probe is energized.

Design Procedure

LX Inductor Selection

The recommended inductor values are 220μ H/330 μ H. For most applications, series resistance (DCR) should be below 8Ω for reasonable efficiency. Do not exceed the inductor's saturation current.

RSLEW Resistor Selection

To help reduce audible noise emission by the EL lamp, the MAX4990 features a slew-rate control input (SLEW) that allows the user to set the slew-rate of the high-voltage outputs, V_A and V_B, by connecting a resistor, R_{SLEW}, from the SLEW input to GND. R_{SLEW} precisely sets the reference current I_B that is used to charge and discharge the capacitances at the SW input and EL input, and is used as a reference current for internal circuitry. The reference current is related to R_{SLEW} by the following equation: I_B = 1V/R_{SLEW}. Decreasing the value of R_{SLEW} increases I_B and increases the slew rate at the EL lamp output. Increasing the value of R_{SLEW} by the following equation: Slew rate is related to R_{SLEW} by the following equation: Slew rate at the Slew rate at the EL lamp output. Increasing the value of R_{SLEW} by the following equation: Slew rate is related to R_{SLEW} by the following equation: Slew rate is related to R_{SLEW} by the following equation:

SlewRate
$$\left(\frac{V}{100\mu s}\right) = \frac{11.25}{R_{SLEW}(M\Omega)}$$

The ideal value for a given design varies depending on lamp size and mechanical enclosure. Typically, the best slew rate for minimizing audible noise is between 10V/100µs and 20V/100µs. This results in R_{SLEW} values ranging from 1.125M Ω to 0.5625M Ω . For example, if the desired slew rate is 20 (V/100µs), this leads to an R_{SLEW} resistor value in M Ω of R_{SLEW} = 11.25/20V = 0.5625M Ω .

Note: Connecting R_{SLEW} to GND will not damage the device. However, for the device to operate correctly, R_{SLEW} should be in the 100k Ω to 2.2M Ω range.

R_{SLEW} also affects the frequency of the boost converter (see the C_{SW} Capacitor Selection), the frequency of the EL lamp (see the C_{EL} Capacitor Selection section), and the peak-to-peak voltage of the EL lamp.





Figure 1a. Human Body ESD Test Model



Figure 1b. Human Body Current Waveform

Table 1. Inductor Vendors



Figure 1c. IEC 61000-4-2 ESD Test Model



Figure 1d. IEC 61000-4-2 ESD Generator Current Waveform

INDUCTOR VALUE (µH)	VENDOR	WEBSITE	PART
220	ТОКО	www.tokoam.com	D312C 1001BS-221M
330	Coilcraft	www.coilcraft.com	DO1608C-334ML
470	Coilcraft	www.coilcraft.com	DO1608C-474ML
220	Coilcraft	www.coilcraft.com	LPS4018-224ML
330	Coilcraft	www.coilcraft.com	LPS4018-334ML
470	Coilcraft	www.coilcraft.com	LPS4018-474ML
220	Cooper Bussmann	www.cooperet.com	SDH3812-221-R
220	Cooper Bussmann	www.cooperet.com	SD3110-221-R

The peak-to-peak voltage is adjusted by connecting a resistor from the SLEW input to GND together with a resistor from the DIM input to GND. The equation relating the peak-to-peak voltage to the resistors is the following:

$$V_{P-P} = 200 \times \frac{R_{DIM}}{R_{SLEW}}$$

RDIM Resistor and CDIM Capacitor Selection

The MAX4990 provides a slow turn-on/-off feature by connecting a resistor in parallel with a capacitor connected from the DIM input to GND. The reference current IB is used to charge the resistor and capacitor. When EN is driven to GND, IB is removed, and the voltage across the capacitor and resistor decay with a time constant of RC that provides a slow turn off of the EL **MAX4990**

lamp outputs. A slow turn-on effect is produced by driving EN high. Slow turn-on/-off time is related by the following equation:

 $t_{ON} = 2.6 \times R_{DIM} \times C_{DIM}$ $t_{OFF} = 1.2 \times R_{DIM} \times C_{DIM}$

For this equation to be valid, R_{DIM}/R_{SLEW} must be \leq 1.3.

Ccs Capacitor Selection

C_{CS} is the output of the boost converter and provides the high-voltage source for the EL lamp. Connect a 3.3nF capacitor from CS to GND and place as close to the CS input as possible. When using an inductor value larger than 220µH, it may be necessary to increase the C_{CS}. For a L_X = 470µH and C_{LAMP} = 20nF, a C_{CS} ranging from 3.3nF to 6.8nF is recommended.

CEL Capacitor Selection

The MAX4990 EL lamp output frequency is set by connecting a capacitor from the EL input to GND together with a resistor from SLEW to GND or by driving the EL input with an external clock (0 to +1.5V). The EL lamp output frequency is related to the C_{EL} capacitor by the following equation:

$$f_{EL} = \frac{0.0817}{R_{SLEW} \times C_{EL}}$$

For example, an R_{SLEW} = $375k\Omega$ and a C_{EL} capacitor value of 1000pF equals an EL lamp output frequency of F_{EL} = 217Hz.

Csw Capacitor Selection

The boost converter switching frequency is set by connecting a capacitor from the SW input to GND, together with the resistance from the SLEW input to GND, or driving the SW input with an external clock (0 to +1.5V). The switching frequency of the boost converter is related to the capacitor from SW to GND by the following equation:

$$f_{SW} = \frac{3.61}{R_{SLEW} \times C_{SW}}$$

Connect the SW input to GND to turn the switch oscillator of the boost converter off. Although the optimal fsw depends on the inductor value, the suggested fsw range is 20kHz to 150kHz.

Note: Driving SW with a logic-high causes LX to be driven to GND. Keeping SW high shorts LX to GND, causing the internal die temperature to increase. The MAX4990 is protected by entering a thermal-shutdown state. (See the *Thermal Short-Circuit Protection* section.)

CB Capacitor Selection

Bypass V_{DD} with a $0.1\mu F$ ceramic capacitor as close to the IC as possible and a $4.7\mu F$ ceramic capacitor as close to the inductor as possible

Diode Selection

Connect a diode, D_1 , from the LX node to CS to rectify the boost voltage on CS. The diode should be a fast-recovery diode that is tolerant to +150V.

EL Lamp Selection

Chip Information

EL lamps have a capacitance of approximately 2.5nF to 3.5nF per square inch. The MAX4990 effectively charges capacitance ranging from 2nF to 20nF.

Applications Information

PCB Layout

Keep PCB traces as short as possible. Ensure that bypass capacitors are as close to the device as possible. Use large ground planes where possible.

PROCESS: BICMOS-DMOS

0664XA0

Typical Application Circuits



13

MAX4990

Package Information

(The package drawing(s) in this data sheet may not reflect the most current specifications. For the latest package outline information, go to **www.maxim-ic.com/packages**.)



Package Information (continued)

(The package drawing(s) in this data sheet may not reflect the most current specifications. For the latest package outline information, go to **www.maxim-ic.com/packages**.)

COMMON	I DIMENS	SIONS		PACKAGE VA	RIAT	IONS					
SYMBOL	MIN.	MAX.		PKG. CODE	N	D2	E2	e	JEDEC SPEC	b	[(N/2)-1] x e
А	0.70	0.80		T633-2	6	1.50±0.10	2.30±0.10	0.95 BSC	MO229/WEEA	0.40±0.05	1.90 REF
D	2.90	3.10		T833-2	8	1.50±0.10	2.30±0.10	0.65 BSC	MO229 / WEEC	0.30±0.05	1.95 REF
Е	2.90	3.10		T833-3	8	1.50±0.10	2.30±0.10	0.65 BSC	MO229 / WEEC	0.30±0.05	1.95 REF
A1	0.00	0.05		T1033-1	10	1.50±0.10	2.30±0.10	0.50 BSC	MO229 / WEED-3	0.25±0.05	2.00 REF
L	0.20	0.40		T1033-2	10	1.50±0.10	2.30±0.10	0.50 BSC	MO229 / WEED-3	0.25±0.05	2.00 REF
k	0.25	MIN.		T1433-1	14	1.70±0.10	2.30±0.10	0.40 BSC		0.20±0.05	2.40 REF
A2	0.20	REF.		T1433-2	14	1.70±0.10	2.30±0.10	0.40 BSC		0.20±0.05	2.40 REF
NOTES:	DIMENSI	DNS AR	E IN mr	N. ANGLES IN	DEG	REES.					
NOTES: 1. ALL [2. COPL 3. WARF 4. PACK 5. DRAW 6. "N" 7. NUME 3. MARK	Dimensio Anarity 'Age Sh 'Age Lei 'Ing Co 'S The ' Ser Of Ser Of 'Ing Is	DNS AR SHALL NGTH/F NFORMS TOTAL I LEADS FOR P/	E IN mm NOT EX T EXCEE ACKAGE TO JEE UMBER SHOWN CKAGE (ANGLES IN CEED 0.08 m D 0.10 mm. WIDTH ARE Cd EC M0229, E CF LEADS. ARE FOR REF DRIENTATION F	DEGF m. DNSIE XCEP EREN REFER	REES. DERED AS S T DIMENSIO CE ONLY. ENCE ONLY	SPECIAL CHA NS "D2" AM	NRACTERISTI ND "E2", AN	C(S). ND T1433-1 & T	1433–2.	
NOTES: 1. ALL I 2. COPL 3. WARF 4. PACK 5. DRAW 6. "N" I 7. NUME MARK	Dimensio Anarity Age Sh Age Lei Ving Co S The Ber Of Sing IS	DNS AR SHALL ALL NO NGTH/F NFORM TOTAL I LEADS FOR P/	E IN mm NOT EX T EXCEE ACKAGE 5 TO JEC IUMBER SHOWN CKAGE (ANGLES IN CEED 0.08 m D 0.10 mm. WIDTH ARE Cd EC M0229, E CG LEADS. ARE FOR REF DRIENTATION F	DEGF m. DNSIE XCEP EREN REFER	REES. DERED AS S T DIMENSIO CE ONLY. ENCE ONLY	SPECIAL CHA NS "D2" AN	NRACTERISTI ND "E2", AP	C(S). ND T1433-1 & T E E PACKAGE TDFN, EX	1433-2.	6,8,10 & 14L J. 3×3×0.80

Revision History

REVISION NUMBER	REVISION DATE	DESCRIPTION	PAGES CHANGED
0	8/07	Initial release	—
1	11/07	Revise lead–free part number from MAX4990E to MAX4990	1-13

Maxim cannot assume responsibility for use of any circuitry other than circuitry entirely embodied in a Maxim product. No circuit patent licenses are implied. Maxim reserves the right to change the circuitry and specifications without notice at any time.

_Maxim Integrated Products, 120 San Gabriel Drive, Sunnyvale, CA 94086 408-737-7600

16

MAX4990

© 2007 Maxim Integrated Products

is a registered trademark of Maxim Integrated Products, Inc.