PI7C9X20303UL

PCI EXPRESS® PACKET SWITCH

DATASHEET REVISION 1.1 August 2009



3545 North 1ST Street, San Jose, CA 95134 Telephone: 1-877-PERICOM, (1-877-737-4266) FAX: 408-435-1100

Internet: http://www.pericom.com



DISCLAIMER

The information contained in this document is proprietary and confidential to Pericom Semiconductor Cooperation (PSC). No part of this document may be copied or reproduced in any form or by any means without prior written consent of PSC.

The information in this document is subjected to change without notice. PSC retains the right to make changes to this document at any time without notice. While the information contained in this document has been checked for accuracy, such information is preliminary, and PSC does not warrant the accuracy and completeness of such information. PSC does not assume any liability or responsibility for damages arising from any use of the information contained in this document.

LIFE SUPPORT POLICY

Pericom Semiconductor Corporation's products are not authorized for use as critical components in life support devices or systems unless a specific written agreement pertaining to such intended use is executed between the manufacturer and an officer of PSC.

- 1) Life support devices or system are devices or systems which:
 - a) Are intended for surgical implant into the body or
 - b) Support or sustain life and whose failure to perform, when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury to the user.
- 2) A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness. Pericom Semiconductor Corporation reserves the right to make changes to its products or specifications at any time, without notice, in order to improve design or performance and to supply the best possible product. Pericom Semiconductor does not assume any responsibility for use of any circuitry described other than the circuitry embodied in a Pericom Semiconductor product. The Company makes no representations that circuitry described herein is free from patent infringement or other rights of third parties which may result from its use. No license is granted by implication or otherwise under any patent, patent rights or other rights, of Pericom Semiconductor Corporation.

All other trademarks are of their respective companies.



REVISION HISTORY

Date	Revision Number	Description
11/27/08	0.0	Preliminary datasheet drafted
2/26/08	0.1	Corrected Chapter 5 Functional Description (multiple virtual channels)
2,20,00		Updated Chapter 6 EEPROM (0Ch)
		Updated Chapter 6 EEPROM (A0h, A2h, A4h)
		Modified Chapter 7 Registers (7.2.2 Device ID Register, 7.2.50 Replay
		Time-Out Counter Bit[13:15], 7.2.52 Switch Operation Mode Bit[14:15],
		7.2.64 PCI Express Capability Bit[24], 7.2.70 Link Status Bit[28], 7.2.99
		Power Budgeting Data, 7.2.100 Power Budget Capability)
		Updated 9.5 JTAG Boundary Scan Register Order
		Updated Chapter 3.5 Power Pins (VDDC, VDDA, VDDAUX)
		Updated Chapter 6 EEPROM (A0h, A2h, A4h)
		Updated Chapter 1 Features (Power Dissipation)
		Updated Chapter 11.1 AC Specification (VDDAUX)
		Updated Chapter 11.2 DC Specification (Power Consumption, VDDAUX)
		Updated Chapter 10 Power Management (VDDAUX)
		Updated Figure 12-1 Package outline drawing (Revision B)
		Corrected 3.1 PCI EXPRESS INTERFACE SIGNALS (DWNRST_L), 3.3
		MISCELLANEOUS SIGNALS (PORTERR, MRL_PDC, NC)
		Updated 4.1 PIN LIST of 132-PIN TQFN (A30, B5, B46) Modified 6.1.4 MAPPING EEPROM CONTENTS TO CONFIGURATION
		REGISTERS (0Ch: B0h, 0Eh: Revision ID)
		Corrected 7.2.52 Switch Operation Mode (Upstream Port) Bit[16:31],
		Corrected 7.2.52 Switch Operation Mode (Downstream Port) Bit[16:31]
5/20/08	0.2	Updated 1 Features (typical latency, removed peer-to-peer switching, power
2,20,00	V.2	consumption)
		Updated Chapter 3.1 PCI Express Interface Signals (REFCLKP,
		REFCLKN)
		Updated Chapter 3.3 Miscellaneous Signals (MRL_PDC to PRSNT)
		Updated 3.2 Port Configuration Signals (SLOT_IMP, MRL_PDC)
		Updated 4.1 Pin-List
		Modified 5.1 Physical Layer Circuit
		Updated Chapter 6.1.3 EEPROM Space Address Map (10h to 14h, 50h to
		54h)
		Modified 6.1.4 Mapping EEPROM Contents To Configuration Registers
		(0Ch: Ordering Frozen, TX SOF Latency, Surprise Down Capability Enable, Power Management Data Select, 20h, 22h, 24h: Removed LPVC, Added
		PMCSR, 51h, 52h, 53h, 54h, 55h, 56h)
		Updated Chapter 7.2 Transparent Mode Configuration Registers (A4h, B4h,
		B8, BCh, C0h, C4h)
		Updated 7.2.5 Revision ID Register, 7.2.27 Interrupt Pin Register, 7.2.32
		Power Management Data Register Bit[3], 7.2.46 Next Item Pointer Register,
		7.2.50 Replay Time-Out Counter, 7.2.51 Acknowledge Latency Timer,
		7.5.52 Switch Operation Mode, 7.2.53 Switch Operation Mode
		(Downstream Port) Bit[16:31], 7.2.54 XPIP CSR2, 7.2.55 SSID/SSVID
		Capability ID Register, 7.2.56 Next Item Pointer Register, 7.2.57 Subsystem
		Vendor ID Register, 7.2.58 Subsystem ID Register, 7.2.65 PCI Express
		Capabilities Register Bit[19:16], 7.2.69 Link Capabilities Register Bit 19,
		7.2.86 Capability Version Bit[19:16], 7.2.93 VC Resource Control Register
		Bit [26:24], 7.2.97 Capability Version Bit[19:16]
		Updated 9.5 JTAG Boundary Scan Register Order Added Chapter 11.2 Power Consumption
		Corrected Chapter 11.3 DC Specifications



2008/7/10	0.3	Modified 1. Features (0.25W typical power dissipation) Modified 3.3 Miscellaneous Signals (DEQ[3] to P0_CTCDIS, HIDRV to P1_CTCDIS, P2_LODRV to CTCDIS[2], DTX[3] to TEST7, TEST2) Modified 4.1 Pin List (DEQ[3] to P0_CTCDIS, HIDRV to P1_CTCDIS, LODRV to P2_CTCDIS, DTX[3] to TEST7, TEST2) Modified 6.1.4 Mapping EEPROM Contents To Configuration Registers (0Ch, 10h, 12h, 14h) Corrected 7.2.27 Interrupt Pin Register Added 7.2.55 TL CSR Modified 11.2 Power Consumption (0.25W L0 Normal Mode with Power Saving)
9/30/08	0.4	Updated Chapter 1 Features (updated Industrial Temperature Range, 0.30 W typical in L0 normal mode) Updated Chapter 3.5 Power Pints (added GND, thermal pad, to VSS) Updated Chapter 4.1 Pin List (added GND) Updated 11.1 Absolute Maximum Ratings: Ambient Temperature with power applied Modified 11.2 Power Consumption (0.30W L0 Normal Mode with Power Saving, 0.30W L1 Normal Mode without Power Saving) Updated Chapter 12 Package Information (added Figure 12-2 Package bottom view)
11/24/08	1.0	Corrected Chapter 7.2 (8Ch - Next Item Pointer) Updated Chapter 13 Ordering Information Updated Header (UltraLo TM Family) Removed "Preliminary" and "Confidential" references
8/12/09	1.1	Updated Chapter 3.1 PCI Express Interface Signals (WAKEUP_L changed to NC) Updated Chapter 3.2 Port Configuration Signals (SLOTCLK) Updated Chapter 3.3 Miscellaneous Signals (updated PWR_SAV pin, PRSNT, SMBCLK, SMBDATA, PWR_SAV, CTCDIS, EEPD) Updated Chapter 3.4 JTAG Boundary Scan Signals (TMS, TDI, TRST_L, WAKEUP_L) Updated Chapter 5.1 Physical Layer Circuit Updated Chapter 7.2.52 and 7.2.53 Switch Operation Mode (Bit[31:16]) Updated Chapter 10 Power Management Updated Figure 12-1 Package outline drawing Updated Table 11-4 Transmitter Characteristics Updated Table 11-5 Receiver Characteristics Updated Chapter 13 Ordering Information



TABLE OF CONTENTS

1 F	TEATURES	10
2 G	GENERAL DESCRIPTION	11
3 P	PIN DESCRIPTION	12
3.1	PCI EXPRESS INTERFACE SIGNALS	12
3.2		
3.3		
3.4		
3.5		
4 P	PIN ASSIGNMENTS	15
4.1	PIN LIST of 132-PIN TQFN	15
5 F	FUNCTIONAL DESCRIPTION	16
5.1	PHYSICAL LAYER CIRCUIT	16
5.2	DATA LINK LAYER (DLL)	18
5.3		
5.4	ROUTING	18
5.5		
5.6		
5	5.6.1 PH	
_	5.6.2 PD	
-	5.6.3 NPHD	
_	5.6.4 CPLH	
	5.6.5 CPLD	
5.7		
5.8		
5.9 5.10		
	`	
6 E	EEPROM INTERFACE AND SYSTEM MANAGEMENT BUS	
6.1		
-	5.1.1 AUTO MODE EERPOM ACCESS	
-	5.1.2 EEPROM MODE AT RESET	
-	6.1.3 EEPROM SPACE ADDRESS MAP	
6.2	5.1.4 MAPPING EEPROM CONTENTS TO CONFIGURATION REGISTERS SMBus INTERFACE	
	REGISTER DESCRIPTION	
7.1 7.2		
	7.2.1 VENDOR ID REGISTER – OFFSET 00h	
	7.2.2 DEVICE ID REGISTER – OFFSET 00h	
	7.2.3 COMMAND REGISTER – OFFSET 04h	
	7.2.4 PRIMARY STATUS REGISTER – OFFSET 04h	
	7.2.5 REVISION ID REGISTER – OFFSET 08h	
	7.2.6 CLASS CODE REGISTER – OFFSET 08h	
	7.2.7 CACHE LINE REGISTER – OFFSET OCh	



7.2.8	PRIMARY LATENCY TIMER REGISTER – OFFSET 0Ch	34
7.2.9	HEADER TYPE REGISTER – OFFSET OCh	34
7.2.10	PRIMARY BUS NUMBER REGISTER – OFFSET 18h	
7.2.11	SECONDARY BUS NUMBER REGISTER – OFFSET 18h	
7.2.12	SUBORDINATE BUS NUMBER REGISTER – OFFSET 18h	
7.2.13	SECONDARY LATENCY TIMER REGISTER – OFFSET 18h	
7.2.14	I/O BASE ADDRESS REGISTER – OFFSET 1Ch	
7.2.15	I/O LIMIT ADDRESS REGISTER – OFFSET 1Ch	
7.2.16	SECONDARY STATUS REGISTER – OFFSET 1Ch	
7.2.17	MEMORY BASE ADDRESS REGISTER – OFFSET 20h	
7.2.17	MEMORY LIMIT ADDRESS REGISTER – OFFSET 20h	
7.2.19	PREFETCHABLE MEMORY BASE ADDRESS REGISTER – OFFSET 24h	
7.2.19	PREFETCHABLE MEMORY LIMIT ADDRESS REGISTER – OFFSET 24h	
7.2.21	PREFETCHABLE MEMORY BASE ADDRESS UPPER 32-BITS REGISTER – OFFSET 28h	
7.2.21	PREFETCHABLE MEMORY LIMIT ADDRESS UPPER 32-BITS REGISTER – OFFSET 2Ch	
7.2.23	I/O BASE ADDRESS UPPER 16-BITS REGISTER - OFFSET 30h	
7.2.24	I/O LIMIT ADDRESS UPPER 16-BITS REGISTER – OFFSET 30h	
7.2.25	CAPABILITY POINTER REGISTER – OFFSET 34h	
7.2.26	INTERRUPT LINE REGISTER – OFFSET 3Ch	
7.2.27	INTERRUPT PIN REGISTER – OFFSET 3Ch	
7.2.28	BRIDGE CONTROL REGISTER – OFFSET 3Ch	
7.2.29	POWER MANAGEMENT CAPABILITY ID REGISTER – OFFSET 80h	
7.2.30	NEXT ITEM POINTER REGISTER – OFFSET 80h	
7.2.31	POWER MANAGEMENT CAPABILITIES REGISTER – OFFSET 80h	
7.2.32	POWER MANAGEMENT DATA REGISTER – OFFSET 84h	
7.2.33	PPB SUPPORT EXTENSIONS – OFFSET 84h	
7.2.34	DATA REGISTER – OFFSET 84h	
7.2.35	MSI CAPABILITY ID REGISTER – OFFSET 8Ch (Downstream Port Only)	
7.2.36	NEXT ITEM POINTER REGISTER - OFFSET 8Ch (Downstream Port Only)	
7.2.37	MESSAGE CONTROL REGISTER – OFFSET 8Ch (Downstream Port Only)	
7.2.38	MESSAGE ADDRESS REGISTER – OFFSET 90h (Downstream Port Only)	
7.2.39	MESSAGE UPPER ADDRESS REGISTER - OFFSET 94h (Downstream Port Only)	41
7.2.40	MESSAGE DATA REGISTER – OFFSET 98h (Downstream Port Only)	41
7.2.41	VPD CAPABILITY ID REGISTER – OFFSET 9Ch (Upstream Port Only)	41
7.2.42	NEXT ITEM POINTER REGISTER – OFFSET 9Ch (Upstream Port Only)	42
7.2.43	VPD REGISTER – OFFSET 9Ch (Upstream Port Only)	42
7.2.44	VPD DATA REGISTER – OFFSET A0h (Upstream Port Only)	42
7.2.45	VENDOR SPECIFIC CAPABILITY ID REGISTER – OFFSET A4h	42
7.2.46	NEXT ITEM POINTER REGISTER – OFFSET A4h	
7.2.47	LENGTH REGISTER – OFFSET A4h	
7.2.48	XPIP CSR0 – OFFSET A8h (Test Purpose Only)	
7.2.49	XPIP CSR1 – OFFSET ACh (Test Purpose Only)	
7.2.50	REPLAY TIME-OUT COUNTER – OFFSET B0h	
7.2.51	ACKNOWLEDGE LATENCY TIMER – OFFSET BOh	
7.2.52	SWITCH OPERATION MODE – OFFSET B4h (Upstream Port)	
7.2.53	SWITCH OPERATION MODE – OFFSET B4h (Downstream Port)	
7.2.54	XPIP CSR2 – OFFSET B8h (Test Purpose Only)	
7.2.55	TL CSR – OFFSET BCh	
7.2.55 7.2.56	SSID/SSVID CAPABILITY ID REGISTER – OFFSET COh	
7.2.50 7.2.57	NEXT ITEM POINTER REGISTER – OFFSET COh	
7.2.57 7.2.58	SUBSYSTEM VENDOR ID REGISTER – OFFSET C4h	
7.2.58 7.2.59	SUBSYSTEM VENDOR ID REGISTER – OFFSET C4hSUBSYSTEM ID REGISTER – OFFSET C4h	
7.2.60	GPIO CONTROL REGISTER – OFFSET D8h (Upstream Port Only)	4/



7.2.61	EEPROM CONTROL REGISTER - OFFSET DCh (Upstream Port Only)	48
7.2.62	EEPROM ADDRESS REGISTER - OFFSET DCh (Upstream Port Only)	49
7.2.63	EEPROM DATA REGISTER - OFFSET DCh (Upstream Port Only)	49
7.2.64	PCI EXPRESS CAPABILITY ID REGISTER – OFFSET E0h	49
7.2.65	NEXT ITEM POINTER REGISTER – OFFSET E0h	
7.2.66	PCI EXPRESS CAPABILITIES REGISTER – OFFSET E0h	
7.2.67	DEVICE CAPABILITIES REGISTER – OFFSET E4h	
7.2.68	DEVICE CONTROL REGISTER – OFFSET E8h	
7.2.69	DEVICE STATUS REGISTER – OFFSET E8h	
7.2.70	LINK CAPABILITIES REGISTER – OFFSET ECh	
7.2.71	LINK CONTROL REGISTER – OFFSET F0h	
7.2.72	LINK STATUS REGISTER – OFFSET F0h	
7.2.73	SLOT CAPABILITIES REGISTER (Downstream Port Only) – OFFSET F4h	
7.2.74	SLOT CONTROL REGISTER (Downstream Port Only) – OFFSET F8h	55
7.2.75	SLOT STATUS REGISTER (Downstream Port Only) – OFFSET F8h	56
7.2.76	PCI EXPRESS ADVANCED ERROR REPORTING CAPABILITY ID REGISTER – OFFSET	Γ 100h.57
7.2.77	CAPABILITY VERSION – OFFSET 100h	
7.2.78	NEXT ITEM POINTER REGISTER – OFFSET 100h	
7.2.79	UNCORRECTABLE ERROR STATUS REGISTER – OFFSET 104h	
7.2.80	UNCORRECTABLE ERROR MASK REGISTER – OFFSET 108h	
7.2.81	UNCORRECTABLE ERROR SEVERITY REGISTER – OFFSET 10Ch	
7.2.82	CORRECTABLE ERROR STATUS REGISTER – OFFSET 110 h	
7.2.83	CORRECTABLE ERROR MASK REGISTER – OFFSET 114 h	
7.2.84	ADVANCE ERROR CAPABILITIES AND CONTROL REGISTER – OFFSET 118h	
7.2.85	HEADER LOG REGISTER – OFFSET From 11Ch to 128h	
7.2.86	PCI EXPRESS VIRTUAL CHANNEL CAPABILITY ID REGISTER – OFFSET 140h (Upstro	• •
7.2.87	CAPABILITY VERSION – OFFSET 140h (Upstream Only)	
7.2.88	NEXT ITEM POINTER REGISTER - OFFSET 140h (Upstream Only)	61
7.2.89	PORT VC CAPABILITY REGISTER 1 – OFFSET 144h (Upstream Only)	
7.2.90	PORT VC CAPABILITY REGISTER 2 – OFFSET 148h (Upstream Only)	62
7.2.91	PORT VC CONTROL REGISTER - OFFSET 14Ch (Upstream Only)	62
7.2.92	PORT VC STATUS REGISTER - OFFSET 14Ch (Upstream Only)	62
7.2.93	VC RESOURCE CAPABILITY REGISTER (0) – OFFSET 150h (Upstream Only)	63
7.2.94	VC RESOURCE CONTROL REGISTER (0) – OFFSET 154h (Upstream Only)	63
7.2.95	VC RESOURCE STATUS REGISTER (0) – OFFSET 158h (Upstream Only)	64
7.2.96	PORT ARBITRATION TABLE REGISTER (0) – OFFSET 180h-1BCh (Upstream Only)	64
7.2.97	PCI EXPRESS POWER BUDGETING CAPABILITY ID REGISTER – OFFSET 20Ch	
7.2.98	CAPABILITY VERSION – OFFSET 20Ch	64
7.2.99	NEXT ITEM POINTER REGISTER – OFFSET 20Ch	
7.2.100		
7.2.101	POWER BUDGETING DATA REGISTER – OFFSET 214h	65
7.2.102	POWER BUDGET CAPABILITY REGISTER – OFFSET 218h	66
CLOC	K SCHEME	67
IEEE 1	149.1 COMPATIBLE JTAG CONTROLLER	68
9.1 IN	STRUCTION REGISTER	60
	YPASS REGISTER	
	EVICE ID REGISTER	
	OUNDARY SCAN REGISTER	
	AG BOUNDARY SCAN REGISTER ORDER	
POWE	R MANAGEMENT	7 1

8

10



11 EL	ECTRICAL AND TIMING SPECIFICATIONS	72
11.1	ABSOLUTE MAXIMUM RATINGS	72
	POWER CONSUMPTION	
	DC SPECIFICATIONS	
	AC SPECIFICATIONS	
10 DA	CKAGE INFORMATION	7
12 PA	CNAGE INFUKNIATION	
13 OR	DERING INFORMATION	7'



TABLE OF FIGURES

THE OF THE CITES	
FIGURE 6-1 SMBUS ARCHITECTURE IMPLEMENTATION ON PI7C9X20303UL	29
FIGURE 12-1 PACKAGE OUTLINE DRAWING	75
FIGURE 12-2 PACKAGE BOTTOM VIEW.	
I IOT OF TABLES	
LIST OF TABLES	
TABLE 5-1 NOMINAL DRIVER CURRENT VALUES (INOM)	16
TABLE 5-2 RATIO OF ACTUAL CURRENT AND NOMINAL CURRENT	16
TABLE 5-3 DE-EMPHASIS LEVEL VERSUS DEQ [3:0]	17
TABLE 5-4 SUMMARY OF PCI EXPRESS ORDERING RULES	
TABLE 6-1 SMBUS ADDRESS PIN CONFIGURATION	29
TABLE 7-1 TABLE ENTRY SIZE IN 4 BITS	64
TABLE 8-1 INPUT CLOCK REQUIREMENTS	
TABLE 9-1 INSTRUCTION REGISTER CODES	
TABLE 9-2 JTAG DEVICE ID REGISTER	68
TABLE 9-3 JTAG BOUNDARY SCAN REGISTER DEFINITION	
TABLE 11-1 ABSOLUTE MAXIMUM RATINGS	
TABLE 11-2 PI7C9X303UL POWER DISSIPATION	
TABLE 11-3 DC ELECTRICAL CHARACTERISTICS	
TABLE 11-4 TRANSMITTER CHARACTERISTICS.	
TABLE 11-5 RECEIVER CHARACTERISTICS	





1 Features

- 3-lane PCI Express Switch with 3 PCI Express ports
- Non-blocking full-wired switching capability at 12 Gbps when all 3 ports are enabled
- Supports "Cut-through" (Default) as well as "Store and Forward" mode for packet switching
- 150 ns typical latency for packet routed through Switch without blocking
- Strapped pins configurable with optional EEPROM or SMBus
- SMBus interface support
- Compliant with System Management (SM) Bus, Version 1.0
- Compliant with PCI Express Base Specification Revision 1.1
- Compliant with PCI Express CEM Specification Revision 1.1
- Compliant with PCI-to-PCI Bridge Architecture Specification Revision 1.2
- Compliant with Advanced Configuration Power Interface (ACPI) Specification
- Reliability, Availability and Serviceability
 - Supports Data Poisoning and End-to-End CRC
 - Advanced Error Reporting and Logging
 - IEEE 1149.6 JTAG interface support
- Advanced Power Saving
 - Empty downstream ports are set to idle state to minimize power consumption
- Link Power Management
 - Supports L0, L0s, L1, L2, L2/L3_{Ready} and L3 link power states
 - Active state power management for L0s and L1 states
- Device State Power Management
 - Supports D0, D3_{Hot} and D3_{Cold} device power states
 - 3.3V Aux Power support in D3_{Cold} power state
- Port Arbitration: Round Robin (RR), Weighted RR and Time-based Weighted RR
- Supports up to 256-byte maximum payload size
- Programmable driver current and de-emphasis level at each individual port
- Low Power Dissipation at 0.30 W typical in L0 normal mode, 0.15 W typical in L1 standby mode
- Industrial Temperature Range -40° to 85°C
- 132-pin TQFN 10mm x 10mm package





2 GENERAL DESCRIPTION

Similar to the role of PCI/PCIX Bridge in PCI/PCIX bus architecture, the function of PCI Express (PCIE) Switch is to expand the connectivity to allow more end devices to be reached by host controllers in PCIE serial interconnect architecture. The 3-lane PCIE Switch can be configured as 3-port type combinations. It provides users the flexibility to expand or fan-out the PCI Express lanes based on their application needs. For some systems that do not need all the 3 lanes, the unused lanes can be disabled to reduce power consumption.

In the PCI Express Architecture, the PCIE Switch forwards posted and non-posted requests and completion packets in either downstream or upstream direction concurrently as if a virtual PCI Bridge is in operation on each port. By visualizing the port as a virtual Bridge, the Switch can be logically viewed as two-level cascaded multiple virtual PCI-to-PCI Bridges, where one upstream-port Bridge sits on all downstream-port Bridges. Similar to a PCI Bridge during enumeration, each port is given a unique bus number, device number, and function number by the initiating software. The bus number, device number, and function number are combined to form a destination ID for each specific port. In addition to that, the memory-map and IO address ranges are exclusively allocated to each port as well. After the software enumeration is finished, the packets are routed to the dedicated port based on the embedded address or destination ID. To ensure the packet integrity during forwarding, the Switch is not allowed to split the packets to multiple small packets or merge the received packets into a large transmit packet. Also, the IDs of the requesters and completers are kept unchanged along the path between ingress and egress port.

The Switch employs the architecture of Combined Input and Output Queue (CIOQ) in implementation. The main reason for choosing CIOQ is that the required memory bandwidth of input queue equals to the bandwidth of ingress port rather than increasing proportionally with port numbers as an output queue Switch does. The CIOQ at each ingress port contains separate dedicated queues to store packets. The packets are arbitrated to the egress port based on the PCIe transaction-ordering rule. For the packets without ordering information, they are permitted to pass over each other in case that the addressed egress port is available to accept them. As to the packets required to follow the ordering rule, the Head-Of-Line (HOL) issue becomes unavoidable for packets destined to different egress ports since the operation of producer-consumer model has to be retained; otherwise the system might occur hang-up problem. On the other hand, the Switch places replay buffer at each egress port to defer the packets before sending it out. This can assure the maximum throughput being achieved and therefore the Switch works efficiently. Another advantage of implementing CIOQ in PCIe Switch is that the credit announcement to the counterpart is simplified and streamlined because of the credit-based flow control protocol. The protocol requires that each ingress port maintains the credits independently without checking other ports' credit availability, which is otherwise required by pure output queue architecture.



3 PIN DESCRIPTION

3.1 PCI EXPRESS INTERFACE SIGNALS

NAME	PIN	TYPE	DESCRIPTION
REFCLKP	B42,	I	Reference Clock Input Pairs: Connect to external 100MHz
REFCLKN	B43	_	differential clock
			The input clock signals must be delivered to the clock buffer cell
			through an AC-coupled interface so that only the AC information of
			the clock is received, converted, and buffered. It is recommended that a
			0.1uF be used in the AC-coupling.
PERP [2:0]	A68, B53,	I	PCI Express Data Serial Input Pairs: Differential data receive
	A58		signals in three ports.
			Port 0 (Upstream Port) is PERP[0] and PERN[0]
PERN [2:0]	B57, A64,	I	Port 1 (Downstream Port) is PERP[1] and PERN[1]
	B48		Port 2 (Downstream Port) is PERP[2] and PERN[2]
PETP [2:0]	B56, B52,	О	PCI Express Data Serial Output Pairs: Differential data transmit
	A60		signals in three ports.
DETN. [2, 0]	A ((A (2	0	Post O (Lineture Post) :- PETP[O] PETN[O]
PETN [2:0]	A66, A62,	О	Port 0 (Upstream Port) is PETP[0] and PETN[0] Port 1 (Downstream Port) is PETP[1] and PETN[1]
	A61		Port 2 (Downstream Port) is PETP[1] and PETN[1] Port 2 (Downstream Port) is PETP[2] and PETN[2]
PERST L	A25	I	System Reset (Active LOW): When PERST L is asserted, the
I LKSI_L	H23	1	internal states of whole chip except sticky logics are initialized.
DWNRST L [2:1]	B44, A52	0	Downstream Device Reset (Active LOW): It provides a reset signal
D WINKSI_L [2.1]	D-1-1, 11.3.2		to the devices connected to the downstream ports of Switch. The signal
			is active when either PERST L is asserted or the device is just plugged
			into the Switch. DWNRST_L [x] corresponds to Portx, where $x=1,2$.
L	1		I make the second of the secon

3.2 PORT CONFIGURATION SIGNALS

NAME	PIN	TYPE	DESCRIPTION
SLOTCLK	B59	Ι	Slot Clock Configuration: It determines if the downstream component uses the same physical reference clock that the platform provides on the connector. When SLOTCLK is high, the platform reference clock is employed. By default, all downstream ports use the same physical
			reference clock provided by platform. The pin has internal pull-down.

3.3 MISCELLANEOUS SIGNALS

NAME	PIN	TYPE	DESCRIPTION
EECLK	A23	O	EEPROM Clock: Clock signal to the EEPROM interface.
EEPD	B19	I/O	EEPROM Data: Bi-directional serial data interface to and from the
			EEPROM. The pin is set to 1 by default. The pin has internal pull-up.
SMBCLK	B7	I	SMBus Clock: System management Bus Clock. The pin has internal
			pull-up.
SMBDATA	B8	I/O	SMBus Data: Bi-directional System Management Bus Data. The pin
			has internal pull-up.
SCAN_EN	A31	I/O	Full-Scan Enable Control: For normal operation, SCAN_EN is an
			output with a value of "0". SCAN_EN becomes an input during
			manufacturing testing.
PORTERR [2:0]	B24, A27,	О	Port PHY Error Status: These pins are used to display the PHY Error
	A26		status of the ports. When PORTERR is flashing (alternating high and
			low signals), it indicates that a PHY error is detected. When it is low,
			no PHY error is detected. PORTERR [x] is correspondent to Port x,
			where x=0,1,2.



NAME	PIN	TYPE	DESCRIPTION
PRSNT [2:1]	A5, A71	I	Present: When asserted low, it represents the device is present in the
			slot of downstream ports. Otherwise, it represents the absence of the
			device. PRSNT [x] is correspondent to Port x, where $x=1,2$. The pins
			have internal pull-down.
GPIO [7:0]	B13, A15,	I/O	General Purpose Input and Output: These eight general-purpose
	B12, A14,		pins are programmed as either input-only or bi-directional pins by
	B11, A13,		writing the GPIO output enable control register.
	A12, B10		When SMBus is implemented, GPIO[7:5] act as the SMBus address
			pins, which set Bit 2 to 0 of the SMBus address.
PWR_SAV	A10	I	Power Saving Mode: PWR_SAV is a strapping pin. When this pin is
			pulled high when system is reset, the Power Saving Mode is enabled.
			When this pin is pulled low when system is reset, the Power Saving
			Mode is disabled. When this pin is pulled low, it should be tied to
			ground through a pull-down resistor. When this pin is pulled high, a
			pull-up resistor should be used. The suggested value for the pull-up and
			pull-down resistor is 5.1K. Pin has an internal pull-down.
P0_CTCDIS	B9	I	P0/P1/P2 CTC Disable: These pins should be tied to ground through a
P1_CTCDIS	B15		pull-down resistor. The suggested value for the pull-down resistor is
P2_CTCDIS	A18		5.1K. The pins have internal pull-down.
TEST1/3/4/5/6/7	A17, A8, B6,	I	Test1/3/4/5/6/7: These pins are for internal test purpose.
	A7, A70, B18		Test1/3/4/5/6/7 should be tied to ground through a pull-down resistor.
			The suggested value for the pull-down resistor is 5.1K.
TEST2	A38	I	Test2: This pin is for internal test purpose.
			Test2 should be tied to 3.3V through a pull-up resistor. The suggested
			value for the pull-up resistor is 5.1K.
NC	A1, A2, A3,		Not Connected: These pins can be left floating.
	A16, A19,		
	A20, A24,		
	A30, A35,		
	A36, A37,		
	A39, A40,		
	A42, A46,		
	A48, A49,		
	A50, A53,		
	A54, A55,		
	A56, A59,		
	A72, B4, B5,		
	B28, B33,		
	B34, B39,		
	B40, B46		

3.4 JTAG BOUNDARY SCAN SIGNALS

NAME	PIN	TYPE	DESCRIPTION
TCK	B27	I	Test Clock: Used to clock state information and data into and out of the chip during boundary scan. When JTAG boundary scan function is
			not implemented, this pin should be left open (NC).
TMS	A34	I	Test Mode Select: Used to control the state of the Test Access Port
			controller. The pin has internal pull-up. When JTAG boundary scan
			function is not implemented, this pin should be pulled low through a
			5.1K pull-down resistor.
TDO	A32	О	Test Data Output: When SCAN_EN is high, it is used (in conjunction
			with TCK) to shift data out of the Test Access Port (TAP) in a serial bit
			stream. When JTAG boundary scan function is not implemented, this
			pin should be left open (NC).
TDI	B29	I	Test Data Input: When SCAN_EN is high, it is used (in conjunction
			with TCK) to shift data and instructions into the TAP in a serial bit
			stream. The pin has internal pull-up. When JTAG boundary scan
			function is not implemented, this pin should be left open (NC).
TRST_L	B31	I	Test Reset (Active LOW): Active LOW signal to reset the TAP
			controller into an initialized state. The pin has internal pull-up. When
			JTAG boundary scan function is not implemented, this pin should be
			pulled low through a 5.1K pull-down resistor.



3.5 POWER PINS

NAME	PIN	TYPE	DESCRIPTION
VDDC	A9, A21, A28, A29, A33, A41, A47, A57, A67, A69, B2, B14, B20, B22, B49	P	VDDC Supply (1.0V): Used as digital core power pins.
VDDR	A6, A11, A22, B17, B23, B26, B47, B58	P	VDDR Supply (3.3V): Used as digital I/O power pins.
VDDA	A44, A45, A51, A65, B37, B54	Р	VDDA Supply (1.0V): Used as analog power pins.
VDDAUX	A43, A63, B3	P	VDDAUX Supply (1.0V): Used as auxiliary core power pins.
VAUX	A4	P	VAUX Supply (3.3V): Used as auxiliary I/O power pins.
VTT	B35, B38, B51, B55	Р	Transmit Termination Voltage (1.5V): Provides driver termination voltage at transmitter. Should be given the same consideration as VDDAUX.
VSS	B1, B16, B21, B25, B30, B32, B36, B41, B45, B50, B60, GND	Р	VSS Ground: Used as ground pins. GND: The central thermal pad underneath the package should be connected to ground.



4 PIN ASSIGNMENTS

4.1 PIN LIST of 132-PIN TQFN

NC NC NC	A34 A35	TMS	A67	UDDC	D20	
NC	A35		Α07	VDDC	B28	NC
		NC	A68	PERP[2]	B29	TDI
	A36	NC	A69	VDDC	B30	VSS
VAUX	A37	NC	A70	TEST6	B31	TRST L
PRSNT[2]	A38	TEST2	A71	PRSNT[1]	B32	VSS
VDDR	A39	NC	A72	NC	B33	NC
TEST5	A40	NC	B1	VSS	B34	NC
TEST3	A41	VDDC	B2	VDDC	B35	VTT
VDDC	A42	NC	В3	VDDAUX	B36	VSS
PWR SAV	A43	VDDAUX	B4	NC	B37	VDDA
VDDR	A44	VDDA	B5	NC	B38	VTT
GPIO[1]	A45	VDDA	В6	TEST4	B39	NC
GPIO[2]	A46	NC	B7	SMBCLK	B40	NC
GPIO[4]	A47	VDDC	B8	SMBDATA	B41	VSS
GPIO[6]	A48	NC	В9	P0 CTCDIS	B42	REFCLKP
NC	A49	NC	B10	GPIO[0]	B43	REFCLKN
TEST1	A50	NC	B11	GPIO[3]	B44	DWNRST L[2]
P2 CTCDIS	A51	VDDA	B12	GPIO[5]	B45	VSS
NC	A52	DWNRST L[1]	B13	GPIO[7]	B46	NC
NC	A53	NC	B14	VDDC	B47	VDDR
VDDC	A54	NC	B15	P1_CTCDIS	B48	PERN[0]
VDDR	A55	NC	B16	VSS	B49	VDDC
EECLK	A56	NC	B17	VDDR	B50	VSS
NC	A57	VDDC	B18	TEST7	B51	VTT
PERST_L	A58	PERP[0]	B19	EEPD	B52	PETP[1]
PORTERR[0]	A59	NC	B20	VDDC	B53	PERP[1]
PORTERR[1]	A60	PETP[0]	B21	VSS	B54	VDDA
VDDC	A61	PETN[0]	B22	VDDC	B55	VTT
VDDC	A62	PETN[1]	B23	VDDR	B56	PETP[2]
NC	A63	VDDAUX	B24	PORTERR[2]	B57	PERN[2]
SCAN_EN	A64	PERN[1]	B25	VSS	B58	VDDR
TDO	A65	VDDA	B26	VDDR	B59	SLOTCLK
VDDC	A66	PETN[2]	B27	TCK	B60	VSS
	TEST5 TEST3 VDDC PWR_SAV VDDR GPIO[1] GPIO[2] GPIO[4] GPIO[6] NC TEST1 P2_CTCDIS NC NC VDDC VDDC VDDR EECLK NC PERST L PORTERR[0] PORTERR[1] VDDC VDDC VDDC NC SCAN_EN TDO	TEST5 A40 TEST3 A41 VDDC A42 PWR_SAV A43 VDDR A44 GPIO[1] A45 GPIO[2] A46 GPIO[4] A47 GPIO[6] A48 NC A49 TEST1 A50 P2 CTCDIS A51 NC A52 NC A53 VDDC A54 VDDR A55 EECLK A56 NC A57 PERST L A58 PORTERR[0] A59 PORTERR[1] A60 VDDC A61 VDDC A62 NC A63 SCAN_EN A64 TDO A65 VDDC A66	TEST5 A40 NC TEST3 A41 VDDC VDDC A42 NC PWR_SAV A43 VDDAUX VDDR A44 VDDA GPIO[1] A45 VDDA GPIO[2] A46 NC GPIO[4] A47 VDDC GPIO[6] A48 NC NC A49 NC TEST1 A50 NC P2 CTCDIS A51 VDDA NC A52 DWNRST L[1] NC A53 NC VDDC A54 NC VDDR A55 NC EECLK A56 NC NC A57 VDDC PERST L A58 PERP[0] PORTERR[0] A59 NC PORTERR[1] A60 PETP[0] VDDC A61 PETN[0] VDDC A62 PETN[1] NC A63 VDDAUX <td>TEST5 A40 NC B1 TEST3 A41 VDDC B2 VDDC A42 NC B3 PWR_SAV A43 VDDAUX B4 VDDR A44 VDDA B5 GPIO[1] A45 VDDA B6 GPIO[2] A46 NC B7 GPIO[4] A47 VDDC B8 GPIO[6] A48 NC B9 NC A49 NC B10 TEST1 A50 NC B11 P2_CTCDIS A51 VDDA B12 NC A52 DWNRST L[1] B13 NC A53 NC B14 VDDC A54 NC B15 VDDR A55 NC B16 EECLK A56 NC B17 NC A57 VDDC B18 PERST L A58 PERP[0] B20 PORTERR[0] <t< td=""><td>TEST5 A40 NC B1 VSS TEST3 A41 VDDC B2 VDDC VDDC A42 NC B3 VDDAUX PWR_SAV A43 VDDAUX B4 NC VDDR A44 VDDA B5 NC GPIO[1] A45 VDDA B6 TEST4 GPIO[2] A46 NC B7 SMBCLK GPIO[4] A47 VDDC B8 SMBDATA GPIO[6] A48 NC B9 P0_CTCDIS NC A49 NC B10 GPIO[0] TEST1 A50 NC B11 GPIO[3] P2_CTCDIS A51 VDDA B12 GPIO[5] NC A52 DWNRST L[1] B13 GPIO[7] NC A53 NC B14 VDDC VDDC A54 NC B15 P1_CTCDIS VDDR A55 NC B16 VSS</td><td>TEST5 A40 NC B1 VSS B34 TEST3 A41 VDDC B2 VDDC B35 VDDC A42 NC B3 VDDAUX B36 PWR SAV A43 VDDAUX B4 NC B37 VDDR A44 VDDA B5 NC B38 GPIO[1] A45 VDDA B6 TEST4 B39 GPIO[2] A46 NC B7 SMBCLK B40 GPIO[2] A46 NC B7 SMBCLK B40 GPIO[4] A47 VDDC B8 SMBDATA B41 GPIO[6] A48 NC B9 P0_CTCDIS B42 NC A49 NC B10 GPIO[0] B43 TEST1 A50 NC B11 GPIO[3] B44 P2_CTCDIS A51 VDDA B12 GPIO[5] B45 NC A52 DWNRST L[1] B13</td></t<></td>	TEST5 A40 NC B1 TEST3 A41 VDDC B2 VDDC A42 NC B3 PWR_SAV A43 VDDAUX B4 VDDR A44 VDDA B5 GPIO[1] A45 VDDA B6 GPIO[2] A46 NC B7 GPIO[4] A47 VDDC B8 GPIO[6] A48 NC B9 NC A49 NC B10 TEST1 A50 NC B11 P2_CTCDIS A51 VDDA B12 NC A52 DWNRST L[1] B13 NC A53 NC B14 VDDC A54 NC B15 VDDR A55 NC B16 EECLK A56 NC B17 NC A57 VDDC B18 PERST L A58 PERP[0] B20 PORTERR[0] <t< td=""><td>TEST5 A40 NC B1 VSS TEST3 A41 VDDC B2 VDDC VDDC A42 NC B3 VDDAUX PWR_SAV A43 VDDAUX B4 NC VDDR A44 VDDA B5 NC GPIO[1] A45 VDDA B6 TEST4 GPIO[2] A46 NC B7 SMBCLK GPIO[4] A47 VDDC B8 SMBDATA GPIO[6] A48 NC B9 P0_CTCDIS NC A49 NC B10 GPIO[0] TEST1 A50 NC B11 GPIO[3] P2_CTCDIS A51 VDDA B12 GPIO[5] NC A52 DWNRST L[1] B13 GPIO[7] NC A53 NC B14 VDDC VDDC A54 NC B15 P1_CTCDIS VDDR A55 NC B16 VSS</td><td>TEST5 A40 NC B1 VSS B34 TEST3 A41 VDDC B2 VDDC B35 VDDC A42 NC B3 VDDAUX B36 PWR SAV A43 VDDAUX B4 NC B37 VDDR A44 VDDA B5 NC B38 GPIO[1] A45 VDDA B6 TEST4 B39 GPIO[2] A46 NC B7 SMBCLK B40 GPIO[2] A46 NC B7 SMBCLK B40 GPIO[4] A47 VDDC B8 SMBDATA B41 GPIO[6] A48 NC B9 P0_CTCDIS B42 NC A49 NC B10 GPIO[0] B43 TEST1 A50 NC B11 GPIO[3] B44 P2_CTCDIS A51 VDDA B12 GPIO[5] B45 NC A52 DWNRST L[1] B13</td></t<>	TEST5 A40 NC B1 VSS TEST3 A41 VDDC B2 VDDC VDDC A42 NC B3 VDDAUX PWR_SAV A43 VDDAUX B4 NC VDDR A44 VDDA B5 NC GPIO[1] A45 VDDA B6 TEST4 GPIO[2] A46 NC B7 SMBCLK GPIO[4] A47 VDDC B8 SMBDATA GPIO[6] A48 NC B9 P0_CTCDIS NC A49 NC B10 GPIO[0] TEST1 A50 NC B11 GPIO[3] P2_CTCDIS A51 VDDA B12 GPIO[5] NC A52 DWNRST L[1] B13 GPIO[7] NC A53 NC B14 VDDC VDDC A54 NC B15 P1_CTCDIS VDDR A55 NC B16 VSS	TEST5 A40 NC B1 VSS B34 TEST3 A41 VDDC B2 VDDC B35 VDDC A42 NC B3 VDDAUX B36 PWR SAV A43 VDDAUX B4 NC B37 VDDR A44 VDDA B5 NC B38 GPIO[1] A45 VDDA B6 TEST4 B39 GPIO[2] A46 NC B7 SMBCLK B40 GPIO[2] A46 NC B7 SMBCLK B40 GPIO[4] A47 VDDC B8 SMBDATA B41 GPIO[6] A48 NC B9 P0_CTCDIS B42 NC A49 NC B10 GPIO[0] B43 TEST1 A50 NC B11 GPIO[3] B44 P2_CTCDIS A51 VDDA B12 GPIO[5] B45 NC A52 DWNRST L[1] B13



5 FUNCTIONAL DESCRIPTION

Multiple virtual PCI-to-PCI Bridges (VPPB), connected by a virtual PCI bus, reside in the Switch. Each VPPB contains the complete PCIe architecture layers that consist of the physical, data link, and transaction layer. The packets entering the Switch via one of VPPBs are first converted from serial bit-stream into parallel bus signals in physical layer, stripped off the link-related header by data link layer, and then relayed up to the transaction layer to extract out the transaction header. According to the address or ID embedded in the transaction header, the entire transaction packets are forwarded to the destination VPPB for formatting as a serial-type PCIe packet through the transmit circuits in the data link layer and physical layer. The following sections describe these function elements for processing PCIe packets within the Switch.

5.1 PHYSICAL LAYER CIRCUIT

The physical layer circuit design is based on the PHY Interface for PCI Express Architecture (PIPE). It contains Physical Media Attachment (PMA) and Physical Coding Sub-layer (PCS) blocks. PMA includes Serializer/ Deserializer (SERDES), PLL¹, Clock Recovery module, receiver detection circuits, electrical idle detector, and input/output buffers. PCS consists of framer, 8B/10B encoder/decoder, receiver elastic buffer, and PIPE PHY control/status circuitries. To provide the flexibility for port configuration, each lane has its own control and status signals for MAC to access individually. In addition, a pair of PRBS generator and checker is included for PHY built-in self test. The main functions of physical layer circuits include the conversion between serial-link and parallel bus, provision of clock source for the Switch, resolving clock difference in receiver end, and detection of physical layer errors.

In order to meet the different application needs, the driving current and equalization of each transmitting channels can be adjusted using EEPROM individually. The driver current of each channel is set to 20mA in default mode. To change the current value, the user can program the EEPROM for nominal value (HIDRV, LODRV) or actual value (DTX [3:0]), which is a scaled multiple of Inom. The following tables illustrate the possible transmitted current values the chip provides.

Table 5-1 Nominal Driver Current Values (Inom)

HIDRV	LODRV	NOMINAL DRIVER CURENT
0	0	20 mA
0	1	10 mA
1	0	28 mA
1	1	Reserved

Table 5-2 Ratio of Actual Current and Nominal Current

DTX [3:0]	ACTUAL CURRENT / NOMINAL CURRENT
0000	1.00
0001	1.05
0010	1.10
0011	1.15
0100	1.20
0101	1.25
0110	1.30

¹ Multiple lanes could share the PLL.

_



DTX [3:0]	ACTUAL CURRENT / NOMINAL CURRENT
0111	1.35
1000	0.60
1001	0.65
1010	0.70
1011	0.75
1100	0.80
1101	0.85
1110	0.90
1111	0.95

The equalization function of transmitting channels can optimize the driver current for different back-plane lengths and materials. The table shown below lists the combinations of de-emphasized driver current (I_{TX} – I_{EQ}) to non-de-emphasized driver current (I_{TX}) for different values of DEQ [3:0].

Table 5-3 De-emphasis Level versus DEQ [3:0]

DEQ [3:0]	$(\mathbf{I}_{\mathrm{TX}} - \mathbf{I}_{\mathrm{EQ}}) / \mathbf{I}_{\mathrm{TX}}$	De-emphasis (dB)
0000	1.00	0.00
0001	0.96	-0.35
0010	0.92	-0.72
0011	0.88	-1.11
0100	0.84	-1.51
0101	0.80	-1.94
0110	0.76	-2.38
0111	0.72	-2.85
1000	0.68	-3.35
1001	0.64	-3.88
1010	0.60	-4.44
1011	0.56	-5.04
1100	0.52	-5.68
1101	0.48	-6.38
1110	0.44	-7.13
1111	0.40	-7.96

By default, the DEQ is set to "1000" to conform to the PCI Express specification, which calls for a de-emphasis level of between -3 dB and -4 dB.

In order to improve the data stream integrity across the channels, the receiver of each port of the Switch includes a reception equalizer to mitigate the effects of ISI. The reception equalizer is implemented as a selectable high-pass filter at the input node, and it is capable of removing as much as 0.4UI of ISI related jitter. The following table shows a simple guideline for selecting the appropriate value to adapt with different lengths or connector numbers in various applications.

Table 5-4 Rx Equalizer Settings (RXEQCTL)

RXEQCTL [1]	RXEQCTL [0]	Rx Eq Setting	Input Jitter	Channel Length
0	0	Max Rx Eq	> 0.25 UI	> 20" and two or more
				connectors
0	1	Min Rx Eq	Between 0.1 UI	Between 8" and 20" and up to
			and 0.25 UI	two connectors
1	X		< 0.1 UI	8" or less, up to one connector





5.2 DATA LINK LAYER (DLL)

The Data Link Layer (DLL) provides a reliable data transmission between two PCI Express points. An ACK/NACK protocol is employed to guarantee the integrity of the packets delivered. Each Transaction Layer Packet (TLP) is protected by a 32-bit LCRC for error detection. The DLL receiver performs LCRC calculation to determine if the incoming packet is corrupted in the serial link. If an LCRC error is found, the DLL transmitter would issue a NACK data link layer packet (DLLP) to the opposite end to request a re-transmission, otherwise an ACK DLLP would be sent out to acknowledge on reception of a good TLP.

In the transmitter, a retry buffer is implemented to store the transmitted TLPs whose corresponding ACK/NACK DLLP have not been received yet. When an ACK is received, the TLPs with sequence number equals to and smaller than that carried in the ACK would be flushed out from the buffer. If a NACK is received or no ACK/NACK is returned from the link partner after the replay timer expires, then a replay mechanism built in DLL transmitter is triggered to re-transmit the corresponding packet that receives NACK or time-out and any other TLP transmitted after that packet.

Meanwhile, the DLL is also responsible for the initialization, updating, and monitoring of the flow-control credit. All of the flow control information is carried by DLLP to the other end of the link. Unlike TLP, DLLP is guarded by 16-bit CRC to detect if data corruption occurs.

In addition, the Media Access Control (MAC) block, which is consisted of LTSSM, multiple lanes deskew, scrambler/de-scrambler, clock correction from inserting skip order-set, and PIPE-related control/status circuits, is implemented to interface physical layer with data link layer.

5.3 TRANSACTION LAYER RECEIVE BLOCK (TLP DECAPSULATION)

The receiving end of the transaction layer performs header information retrieval and TC/VC mapping (see section 5.5), and it validates the correctness of the transaction type and format. If the TLP is found to contain illegal header or the indicated packet length mismatches with the actual packet length, then a Malformed TLP is reported as an error associated with the receiving port. To ensure end-to-end data integrity, a 32-bit ECRC is checked against the TLP at the receiver if the digest bit is set in header.

5.4 ROUTING

The transaction layer implements three types of routing protocols: ID-based, address-based, and implicit routing. For configuration reads, configuration writes, transaction completion, and user-defined messages, the packets are routed by their destination ID constituted of bus number, device number, and function number. Address routing is employed to forward I/O or memory transactions to the destination port, which is located within the address range indicated by the address field carried in the packet header. The packet header indicates the packet types including memory read, memory write, IO read, IO write, Message Signaling Interrupt (MSI) and user-defined message. Implicit routing is mainly used to forward system message transactions such as virtual interrupt line, power management, and so on. The message type embedded in the packet header determines the routing mechanism.

If the incoming packet can not be forwarded to any other port due to a miss to hit the defined address range or targeted ID, this is considered as Unsupported Request (UR) packet, which is similar to a master abort event in PCI protocol.





5.5 TC/VC MAPPING

The 3-bit TC field defined in the header identifies the traffic class of the incoming packets. To enable the differential service, a TC/VC mapping table at destination port that is pre-programmed by system software or EEPROM pre-load is utilized to cast the TC labeled packets into the desired virtual channel. Note that all the traffic classes are mapped to VC0, since only VC0 is available on the Switch. After the TC/VC mapping, the receive block dispatches the incoming request, completion, or data into the VC0 queues.

5.6 QUEUE

In PCI Express, it defines six different packet types to represent request, completion, and data. They are respectively Posted Request Header (PH), Posted Request Data payload (PD), Non-Posted Request Header (NPH), Non-Posted Data Payload (NPD), Completion Header (CPLH) and Completion Data payload (CPLD). Each packet with different type would be put into a separate queue in order to facilitate the following ordering processor. Since NPD usually contains one DW, it can be merged with the corresponding NPH into a common queue named NPHD.

5.6.1 PH

PH queue provides TLP header spaces for posted memory writes and various message request headers. Each header space occupies sixteen bytes to accommodate 3 DW or 4 DW headers.

5.6.2 PD

PD queue is used for storing posted request data. If the received TLP is of the posted request type and is determined to have payload coming with the header, the payload data would be put into PD queue.

5.6.3 NPHD

NPHD queue provides TLP header spaces for non-posted request packets, which include memory read, IO read, IO write, configuration read, and configuration write. Each header space takes twenty bytes to accommodate a 3-DW header, s 4-DW header, s 3-WD header with 1-DW data, and a 4-DW header with 1-DW data.

5.6.4 CPLH

CPLH queue provides TLP header space for completion packets. Each header space takes twelve bytes to accommodate a 3-DW header. Please note that there is no 4-DW completion headers.

5.6.5 CPLD

CPLD queue is used for storing completion data. If the received TLP is of the completion type and is determined to have payload coming with the header, the payload data would be put into CPLD queue.



5.7 TRANSACTION ORDERING

Within a VPPB, a set of ordering rules is defined to regulate the transactions on the PCI Express Switch including Memory, IO, Configuration and Messages, in order to avoid deadlocks and to support the Producer-Consumer model. The ordering rules defined in table 5-4 apply within a single Traffic Class (TC). There is no ordering requirement among transactions within different TC labels.

Table 5-4 Summary of PCI Express Ordering Rules

Row Pass Column	Posted Request	Read Request	Non-posted Write Request	Read Completion	Non-posted Write Completion
Posted Request	Yes/No ¹	Yes ⁵	Yes ⁵	Yes ⁵	Yes ⁵
Read Request	No ²	Yes	Yes	Yes	Yes
Non-posted Write Request	No ²	Yes	Yes	Yes	Yes
Read Completion	Yes/No ³	Yes	Yes	Yes	Yes
Non-Posted Write	Yes ⁴	Yes	Yes	Yes	Yes
Completion					

- 1. When the Relaxed Ordering Attribute bit is cleared, the Posted Request transactions including memory write and message request must complete on the egress bus of VPPB in the order in which they are received on the ingress bus of VPPB. If the Relaxed Ordering Attribute bit is set, the Posted Request is permitted to pass over other Posted Requests occurring before it.
- 2. A Read Request transmitting in the same direction as a previously queued Posted Request transaction must push the posted write data ahead of it. The Posted Request transaction must complete on the egress bus before the Read Request can be attempted on the egress bus. The Read transaction can go to the same location as the Posted data. Therefore, if the Read transaction were to pass the Posted transaction, it would return stale data.
- 3. When the Relaxed Ordering Attribute bit is cleared, a Read completion must "pull" ahead of previously queued posted data transmitting in the same direction. In this case, the read data transmits in the same direction as the posted data, and the requestor of the read transaction is on the same side of the VPPB as the completer of the posted transaction. The posted transaction must deliver to the completer before the read data is returned to the requestor. If the Relaxed Ordering Attribute bit is set, then a read completion is permitted to pass a previously queued Memory Write or Message Request.
- 4. Non-Posted Write Completions are permitted to pass a previous Memory Write or Message Request transaction. Such transactions are actually transmitting in the opposite directions and hence have no ordering relationship.
- 5. Posted Request transactions must be given opportunities to pass Non-posted Read and Write Requests as well as Completions. Otherwise, deadlocks may occur when some older Bridges that do not support delayed transactions are mixed with PCIe Switch in the same system. A fairness algorithm is used to arbitrate between the Posted Write queue and the Non-posted transaction queue.

5.8 PORT ARBITRATION

Among multiple ingress ports, the port arbitration built in the egress port determines which input traffic to be forwarded to the output port. The arbitration algorithm contains hardware fixed Round Robin, 128-phase Weighted Round-Robin and programmable 128-phase time-based WRR. The port arbitration is held within the same VC channel. Each port has port arbitration circuitries for traffic handling in VC0. At upstream port, in addition to the traffic from inter-port, the intra-port packet such as configurations completion would also join the arbitration loop to get the service in Virtual Channel 0.





5.9 FLOW CONTROL

PCI Express employs Credit-Based Flow Control mechanism to make buffer utilization more efficient. The transaction layer transmitter ensures that it does not transmit a TLP to an opposite receiver unless the receiver has enough buffer space to accept the TLP. The transaction layer receiver has the responsibility to advertise the free buffer space to an opposite transmitter to avoid packet stale. In this switch, each port has separate queues for different traffic types and the credits are on the fly sent to data link layer, which compares the current available credits with the monitored one and reports the updated credit to the counterpart. If no new credit is acquired, the credit reported is scheduled for every 30 us to prevent from link entering retrain. On the other hand, the receiver at each egress port gets the usable credits from the opposite end in a link. It would broadcast them to all the other ingress ports for gating the packet transmission.

5.10 TRANSATION LAYER TRANSMIT BLOCK (TLP ENCAPSULATION)

The transmit portion of transaction layer performs the following functions. They are to construct the all types of forwarded TLP generated from VC arbiter, respond with the completion packet when the local resource (i.e. configuration register) is accessed and regenerate the message that terminated at receiver to RC if acts as an upstream port.



6 EEPROM INTERFACE AND SYSTEM MANAGEMENT BUS

The EEPROM interface consists of two pins: EECLK (EEPROM clock output) and EEPD (EEPROM bidirectional serial data). The Switch may control an ISSI IS24C04 or compatible parts using into 512x8 bits. The EEPROM is used to initialize a number of registers before enumeration. This is accomplished after PRST# is deasserted, at which time the data from the EEPROM is loaded. The EEPROM interface is organized into a 16-bit base, and the Switch supplies a 7-bit EEPROM word address. The Switch does not control the EEPROM address input. It can only access the EEPROM with address input set to 0.

The System Management Bus interface consists of two pins: SMBCLK (System Management Bus Clock input) and SMBDATA (System Management Bus Data input/ output).

6.1 EEPROM INTERFACE

6.1.1 AUTO MODE EERPOM ACCESS

The Switch may access the EEPROM in a WORD format by utilizing the auto mode through a hardware sequencer. The EEPROM start-control, address, and read/write commands can be accessed through the configuration register. Before each access, the software should check the Autoload Status bit before issuing the next start.

6.1.2 EEPROM MODE AT RESET

During a reset, the Switch will automatically load the information/data from the EEPROM if the automatic load condition is met. The first offset in the EEPROM contains a signature. If the signature is recognized, the autoload initiates right after the reset.

During the autoload, the Bridge will read sequential words from the EEPROM and write to the appropriate registers. Before the Bridge registers can be accessed through the host, the autoload condition should be verified by reading bit [3] offset DCh (EEPROM Autoload Status). The host access is allowed only after the status of this bit is set to '0' which indicates that the autoload initialization sequence is complete.

6.1.3 EEPROM SPACE ADDRESS MAP

15 – 8	15 – 8 7 – 0		
EEPROM Sig	EEPROM Signature (1516h)		
Vend	Vendor ID		
Devi	ce ID	04h	
Extended VC Count / Link Capability / Switch	h Mode Operation / Interrupt pin for Port 1 ~ 2	06h	
Subsystem	Vender ID	08h	
Subsys	stem ID	0Ah	
Max_Payload_Size Support / ASPM Support	rt / Role_Base Error Reporting / RefClk ppm	0Ch	
Diffe	Difference		
Reserved	Reserved Revision ID		
NFTS / Scrar	mble for Port0	10h	
NFTS / Scrar	NFTS / Scramble for Port1		
NFTS / Scrar	NFTS / Scramble for Port2		
Rese	16h		
Rese	18h		
Rese	1Ah		
Rese	erved	1Ch	



15 – 8	7 – 0	BYTE OFFSET
10 0	Reserved	1Eh
TC/VC Map for Port 0 (VC0		20h
TC/VC Map for Port 1(VC0)	Slot Implemented / Slot Clock / LPVC Count / Port Num, Port 1	22h
TC/VC Map for Port 2 (VC0)		24h
	Reserved	26h
	Reserved	
	Reserved	2Ah
	Reserved	2Ch
	Reserved	2Eh
CI.	Reserved	30h
	ot Capability 0 for Port 1 ot Capability 0 for Port 2	32h 34h
510	Reserved	36h
	Reserved	38h
	Reserved	3Ah
	Reserved	3Ch
	Reserved	3Eh
	Reserved	40h
Slo	ot Capability 1 for Port 1	42h
	ot Capability 1 for Port 2	44h
	Reserved	46h
	Reserved	48h
	Reserved	4Ah
	Reserved	4Ch
	Reserved	4Eh
PM Data for Port 0	PM Capability for Port 0	50h
PM Data for Port 1	PM Capability for Port 1	52h
PM Data for Port 2	PM Capability for Port 2	54h
Reserved		56h 58h
Reserved Reserved		5Ah
Reserved		5Ch
Reserved		5Eh
Power Budgeting Capability Register for Port 0		60h
Power Budgeting Capability Register for Port 1		62h
Power Budgeting Capability Register for Port 2		64h
Reserved		66h
	Reserved	68h
	Reserved	6Ah
	Reserved	6Ch
	Reserved	6Eh
	Time-out Counter for Port 0	70h
	Time-out Counter for Port 1	72h
Replay	Time-out Counter for Port 2	74h
	Reserved	76h
	Reserved	78h 7Ah
	Reserved Reserved	7Ch
	Reserved	7Eh
Acknowl	edge Latency Timer for Port 0	80h
	Acknowledge Latency Timer for Port 0 Acknowledge Latency Timer for Port 1	
	edge Latency Timer for Port 2	82h 84h
2 223410 W	Reserved	86h
	Reserved	88h
	Reserved	8Ah
	Reserved	8Ch
	Reserved	8Eh
	HY Parameter for Port 0	90h
	HY Parameter for Port 1	92h
DI	HY Parameter for Port 2	94h



15 – 8	7 – 0	BYTE OFFSET	
Res	erved	96h	
Res	erved	98h	
Res	erved	9Ah	
Res	Reserved		
Res	Reserved		
Reserved	PM Control Para/Rx Polarity for Port 0	A0h	
Reserved	PM Control Para/Rx Polarity for Port 1	A2h	
Reserved PM Control Para/Rx Polarity for Port 2		A4h	
Res	Reserved		

6.1.4 MAPPING EEPROM CONTENTS TO CONFIGURATION REGISTERS

ADDRESS	PCI CFG OFFSET	DESCRIPTION
00h	T CI CFG OFFSET	EEPROM signature – 1516h
02h	00h ~ 01h	Vendor ID
04h	$02h \sim 03h$	Device ID
06h	144h (Port 0~2)	Extended VC Count for Port 0 ~ 2
UOII	144h (Folt 0~2)	Bit [0]: It represents the supported VC count other than the
	14411. Bit [0]	default VC
		default VC
	ECh (Port 0~2)	Link Capability for Port 0 ~ 2
	ECh: Bit [14:12]	Bit [3:1]: It represents L0s Exit Latency for all ports
	ECh: Bit [17:15]	Bit [6:4]: It represents L1 Exit Latency for all ports
	Len. Bit [17:15]	Bit [0.4]. It represents by Exit Eutency for all ports
	B4h (Port 0~2)	Switch Mode Operation for Port 0
	B4h:Bit [5]	Bit [8]: no ordering on packets for different egress port mode
	Bit [6]	Bit [9]: no ordering on different tag of completion mode
	Bit [0]	 Bit [10]: Store and Forward
	Bit [2:1]	■ Bit [12:11]: Cut-through Threshold
	Bit [3]	 Bit [13]: Port arbitrator Mode
	Bit [4]	■ Bit [14]: Credit Update Mode
	3Ch (Port 1~2)	Interrupt pin for Port 1 ~ 2
	3Ch: Bit [8]]	 Bit [15]: Set when INTA is requested for interrupt resource
08h	C4h: Bit [15:0]	Subsystem Vender ID
0Ah	C4h: Bit [31:16]	Subsystem ID
0Ch	E4h(Port 0~2)	Max_Payload_Size Support for Port 0 ~ 2
	E4h: Bit 0	 Bit [0]: Indicated the maximum payload size that the device can
		support for the TLP
	ECLOP (A A)	ACDAG AS DAG
	ECh(Port 0~2)	ASPM Support for Port 0 ~ 2
	ECh: Bit[11:10]	Bit [2:1]: Indicate the level of ASPM supported on the PCIe link
	E4h(Port 0~2)	Role_Base Error Reporting for Port 0 ~ 2
	E4h: Bit[15]	Bit [3]: Indicate implement the role-base error reporting
	Lan. Bit[13]	Bit [5]: indicate implement the fole base error reporting
	B0h(port 0~2)	MSI Capability Disable for Port 0~2
	B0h : Bit [14]	 Bit [4]: Disable MSI capability
	B0h(port 0~2)	AER Capability Disable for Port 0~2
	B0h : Bit [15]	■ Bit [5] : Disable AER capability
	B4h(port 0~2)	Compliance Pattern Parity Control Disable for Port 0~2
	B4h : Bit [15]	 Bit [6]: Disable compliance pattern parity
	P01 (+ 0 2)	
	B0h(port 0~2)	Power Management Capability Disable for Port 0~2
	B0h : Bit [13]	 Bit [7]: Disable Power Management Capability
	PAh(Port 0 2)	Ordaning Fragon for Port 0, 2
	B4h(Port 0~2) B4h: Bit [7]	Ordering Frozen for Port 0~2 Bit [10]: Freeze the ordering feature
	DHII. DIL [/]	- Dit [10]. Piceze the oldering reature
	BCh(Port 0~2)	TX SOF Latency Mode for Port 0~2



ADDDEGG	DCI CEC OFFCET	Description
ADDRESS	PCI CFG OFFSET BCh: Bit[0]	DESCRIPTION ■ Bit [11]: Set to zero to shorten latency
	Ben. Bit[0]	- Bit [11]. Set to zero to shorten fatelicy
	ECh(port0~2)	Surprise Down Capability Enable for Port 0~2
	ECh : Bit [19]	 Bit [12]: Enable Surprise Down Capability
	DCh(Dort 0, 2)	Described for Described Described Division Division Described for Described
	BCh(Port 0~2) BCh: Bit[1]	Power Management's Data Select Register R/W Capability for Port 0~2 Bit [13]: Enable Data Select Register R/W
	DCII. DIQ1	- Bit [13]. Eliable Data Select Register R/W
	BCh(Port 0~2)	Flow Control Update Type for Port 0~2
	BCh: Bit[2]	 Bit [14]: Select Flow Control Update Type
	BCh(Port 0~2)	4KB Boundary Check Enable
	BCh: Bit[3]	Bit [15]: Enable 4KB Boundary Check
0Eh	08h: Bit[7:0]	Revision ID
		■ Bit [7:0]: Indicates the Revision ID of chip.
10h	B8h (port 0)	FTS Number for Port 0
	B8h : Bit[7:0]	■ Bit [7:0]: FTS number at receiver side
	A8h(Port 0)	RefClk ppm Difference for Port 0
	A8h: Bit [14:13]	Bit [9:8]: It represents RefClk ppm difference between the two
		ends in one link; 00: 0 ppm, 01: 100 ppm, 10: 200 ppm, 11: 300
		ppm
	B8h (port0)	Scrambler Control for Port 0
	B8h : Bit[11:10]	Bit [11:10]: scrambler control
	B8h : Bit[12]	■ Bit [12]: L0s
12h	B8h (port 1)	FTS Number for Port 1
	B8h : Bit[7:0]	■ Bit [7:0]: FTS number at receiver side
	A8h(Port 1)	RefClk ppm Difference for Port 1
	A8h: Bit [14:13]	■ Bit [9:8]: It represents RefClk ppm difference between the two
		ends in one link; 00: 0 ppm, 01: 100 ppm, 10: 200 ppm, 11: 300
		ppm
	B8h (port1)	Scrambler Control for Port 1
	B8h : Bit[11:10]	Bit [11:10]: scrambler control
	B8h : Bit[12]	■ Bit [12]: L0s
14h	B8h (port 2)	FTS Number for Port 2
	B8h : Bit[7:0]	■ Bit [7:0]: FTS number at receiver side
	A8h(Port 2)	RefClk ppm Difference for Port 2
	A8h: Bit [14:13]	■ Bit [9:8]: It represents RefClk ppm difference between the two
		ends in one link; 00: 0 ppm, 01: 100 ppm, 10: 200 ppm, 11: 300
		ppm
	B8h (port2)	Scrambler Control for Port 2
	B8h : Bit[11:10]	 Bit [11:10]: scrambler control
201	B8h : Bit[12]	• Bit [12]: L0s
20h	F0h (Port 0) F0h: Bit [28]	Slot Clock Configuration for Port 0 Bit [1]: When set, the component uses the clock provided on the
	ron. Bit [26]	connector
	80h (Port 0)	Device specific Initialization for Port 0
	80h: Bit[21]	Bit [2]: When set, the DSI is required
	ECh (Port 0)	Port Number for Port 0
	ECh: Bit [25:24]	Bit [5:4]: It represents the logic port numbering for physical port
		0
	9.4h (D+0)	PMCCD Data Cools for Deat 0
	84h (Port 0) 84h: Bit [14:13]	PMCSR Data Scale for Port 0 Bit [7:6]: It represents the PMCSR Data Scale for physical port 0
	154h (Port 0)	VC0 TC/VC Map for Port 0
	154h: Bit [7:1]	Bit [15:9]: When set, it indicates the corresponding TC is
		mapped into VC0



A DDDEGG	DOLGEG OFFGER	Description
ADDRESS	PCI CFG OFFSET	DESCRIPTION POL COLUMN STATE OF A 1 STATE O
22h	E0h (Port1)	PCIe Capability Slot Implemented for Port 1
	E0h: Bit [24]	Bit [0]: When set, the slot is implemented for Port 1
	701 (7 . 1)	
	F0h (Port 1)	Slot Clock Configuration for Port 1
	F0h: Bit [28]	Bit [1]: When set, the component uses the clock provided on the
		Connector
	80h (Port 1)	Device specific Initialization for Port 1
	80h: Bit[21]	Bit [2]: When set, the DSI is required
	ECh (Port 1)	Port Number for Port 1
	ECh: Bit [25:24]	 Bit [5:4]: It represents the logic port numbering for physical port
		1
	84h (Port 1)	PMCSR Data Scale for Port 1
	84h: Bit [14:13]	Bit [7:6]: It represents the PMCSR Data Scale for physical port 1
	154h (Port 1)	VC0 TC/VC Map for Port 1
	154h: Bit [7:1]	 Bit [15:9]: When set, it indicates the corresponding TC is
		mapped into VC0
24h	E0h (Port 2)	PCIe Capability Slot Implemented for Port 2
	E0h: Bit [24]	Bit [0]: When set, the slot is implemented for Port 2
	Eon. Dit [21]	Dit [0]. When set, the slot is implemented for 1 of 2
	F0h (Port 2)	Slot Clock Configuration for Port 2
	F0h: Bit [28]	Bit [1]: When set, the component uses the clock provided on the
	1 on. Bit [20]	Connector
		Connector
	80h (Port 2)	Device specific Initialization for Port 2
	80h: Bit[21]	Bit [2]: When set, the DSI is required
	oon. Bit[21]	- Bit [2]. When set, the BSI is required
	ECh (Port 2)	Port Number for Port 2
	ECh: Bit [25:24]	Bit [5:4]: It represents the logic port numbering for physical port
	ECII. Bit [23.24]	2
		2
	84h (Port 2)	PMCSR Data Scale for Port 2
	84h: Bit [14:13]	Bit [7:6]: It represents the PMCSR Data Scale for physical port 2
	154h (Port 2)	VC0 TC/VC Map for Port 2
	154h: Bit [7:1]	Bit [15:9]: When set, it indicates the corresponding TC is
221	E41 (P. +1)	mapped into VC0
32h	F4h (Port 1)	Slot Capability 0 of Port 1
	F4h: Bit [15:0]	Bit [15:0]: Mapping to the low word of slot capability register
34h	F4h (Port 2)	Slot Capability 0 of Port 2
401	F4h: Bit [15:0]	Bit [15:0]: Mapping to the low word of slot capability register
42h	F4h (Port 1)	Slot Capability 1 of Port 1
	F4h: Bit [31:16]	 Bit [15:0]: Mapping to the high word of slot capability register
44h	F4h (Port 2)	Slot Capability 1 of Port 2
	F4h: Bit [31:16]	 Bit [15:0]: Mapping to the high word of slot capability register
50h	84h (Port 0)	No_Soft_Reset for Port 0
	84h: Bit [3]	Bit [0]: No_Soft_Reset.
	80h (Port 0)	Power Management Capability for Port 0
	80h: Bit [24:22]	■ Bit [3:1]: AUX Current.
	80h: Bit [25]	 Bit [4]: read only as 1 to indicate Bridge supports the D1 power
		management state
	80h: Bit [26]	 Bit [5]: read only as 1 to indicate Bridge supports the D2 power
		management state
	80h: Bit [29:28]	 Bit [7:6]: PME Support for D2 and D1 states
51h	84h (Port 0)	Power Management Data for Port 0
	84h: Bit [31:24]	Bit [15:8]: read only as Data register
L	[]	



	T.	Datasii
ADDRESS	PCI CFG OFFSET	DESCRIPTION
52h	84h (Port 1)	No_Soft_Reset for Port 1
	84h: Bit [3]	Bit [0]: No Soft Reset.
	80h (Port 1)	Power Management Capability for Port 1
	80h: Bit [24:22]	Bit [3:1]: AUX Current.
	80h: Bit [25]	Bit [4]: read only as 1 to indicate Bridge supports the D1 power
	8011. Bit [23]	0 11
	901 Div [26]	management state
	80h: Bit [26]	 Bit [5]: read only as 1 to indicate Bridge supports the D2 power
		management state
	80h: Bit [29:28]	 Bit [7:6]: PME Support for D2 and D1 states
53h	84h (Port 1)	Power Management Data for Port 1
	84h: Bit [31:24]	 Bit [15:8]: read only as Data register
54h	84h (Port 2)	No_Soft_Reset for Port 2
3 111	84h: Bit [3]	Bit [0]: No Soft Reset
	04II. Bit [5]	Bit [0]. 110_Boit_Reset
	901- (D 2)	D M (C 1274 6 D (A
	80h (Port 2)	Power Management Capability for Port 2
	80h: Bit [24:22]	Bit [3:1]: AUX Current
	80h: Bit [25]	 Bit [4]: read only as 1 to indicate Bridge supports the D1 power
		management state
	80h: Bit [26]	 Bit [5]: read only as 1 to indicate Bridge supports the D2 power
		management state
	80h: Bit [29:28]	 Bit [7:6]: PME Support for D2 and D1 states
55h	84h (Port 2)	Power Management Data for Port 2
3311	84h: Bit [31:24]	Bit [15:8] – read only as Data register
(Ol-		
60h	214h (Port 0)	Power Budget Register for Port 0
	214h– Bit [7:0]	Bit [7:0]: Base Power
	214h– Bit [9:8]	■ Bit [9:8]: Data Scale
	214h– Bit [14:13]	 Bit [11:10]: PM State
	218h– Bit [0]	 Bit [15]: System Allocated
62h	214h (Port 1)	Power Budget Register for Port 1
	214h– Bit [7:0]	Bit [7:0]: Base Power
	214h– Bit [9:8]	■ Bit [9:8]: Data Scale
	214h– Bit [14:13]	Bit [11:10]: PM State
	218h– Bit [0]	Bit [15]: System Allocated
64h	• • • • • • • • • • • • • • • • • • • •	
0411	214h (Port 2)	Power Budget Register for Port 2
	214h– Bit [7:0]	Bit [7:0]: Base Power
	214h– Bit [9:8]	Bit [9:8]: Data Scale
	214h– Bit [14:13]	 Bit [11:10]: PM State
	218h– Bit [0]	 Bit [15]: System Allocated
70h	B0h (Port 0)	Replay Time-out Counter for Port 0
	B0h – Bit [15:0]	■ Bit [15:0]: Relay Time-out Counter
72h	B0h (Port 1)	Replay Time-out Counter for Port 1
·	B0h – Bit [15:0]	Bit [15:0]: Relay Time-out Counter
74h	B0h (Port 2)	Replay Time-out Counter for Port 2
7-11	B0h – Bit [15:0]	Bit [15:0]: Relay Time-out Counter
0.01-		
80h	B0h (Port 0)	Acknowledge Latency Timer for Port 0
	B0h – Bit [31:16]	■ Bit [31:16]: Acknowledge Latency Timer
82h	B0h (Port 1)	Acknowledge Latency Timer for Port 1
	B0h – Bit [31:16]	 Bit [31:16]: Acknowledge Latency Timer
84h	B0h (Port 2)	Acknowledge Latency Timer for Port 2
	B0h – Bit [31:16]	 Bit [31:16]: Acknowledge Latency Timer
90h	B4h (Port 0)	PHY Parameter for Port 0
7 ***	B4h: Bit [31:16]	Bit [31:16]: PHY Parameter
92h	B4h (Port 1)	PHY Parameter for Port 1
9211	()	
0.41	B4h: Bit [31:16]	Bit [31:16]: PHY Parameter
94h	B4h (Port 2)	PHY Parameter for Port 2
	B4h: Bit [31:16]	Bit [31:16]: PHY Parameter



		Datasiie
ADDRESS	PCI CFG OFFSET	DESCRIPTION
A0h	B0h (Port0)	Decode VGA for Port0
	B0h: Bit[31]	■ Bit [7]
	B4h (Port 0)	PM Control Parameter for Port 0
	B4h: Bit [13:8]	■ Bit [5:4] : L0s enable
		■ Bit [3:2] : L1 delay count select
		■ Bit [1:0] : D3 enters L1
	B4h (Port 0)	Rx Polarity Inversion Disable for port 0
	B4h : Bit [14]	 Bit [6]: Disable Rx polarity capability
A2h	B0h (Port1)	Decode VGA for Port1
	B0h: Bit[31]	■ Bit [7]
	B4h (Port 1)	PM Control Parameter for Port 1
	B4h: Bit [13:8]	■ Bit [5:4] : L0s enable
		■ Bit [3:2] : L1 delay count select
		■ Bit [1:0] : D3 enters L1
	B4h (Port 1)	Rx Polarity Inversion Disable for port 1
	B4h : Bit [14]	 Bit [6]: Disable Rx polarity capability
A4h	B0h (Port2)	Decode VGA for Port2
	B0h: Bit[31]	■ Bit [7]
	B4h (Port 2)	PM Control Parameter for Port 2
	B4h: Bit [13:8]	■ Bit [5:4] : L0s enable
		Bit [3:2]: L1 delay count select
		■ Bit [1:0] : D3 enters L1
	B4h (Port 2)	Rx Polarity Inversion Disable for port 2
	B4h : Bit [14]	 Bit [6]: Disable Rx polarity capability



6.2 SMBus INTERFACE

The PI7C9X20303UL provides the System Management Bus (SMBus), a two-wire interface through which a simple device can communicate with the rest of the system. The SMBus interface on the PI7C9X20303UL is a bi-directional slave interface. It can receive data from the SMBus master or send data to the master. The interface allows full access to the configuration registers. A SMBus master, such as the processor or other SMBus devices, can read or write to every RW configuration register (read/write register). In addition, the RO and HwInt registers (read-only and hardware initialized registers) that can be auto-loaded by the EEPROM interface can also be read and written by the SMBus interface. This feature allows increases in the system expandability and flexibility in system implementation.




Figure 6-1 SMBus Architecture Implementation on PI7C9X20303UL

The SMBus interface on the PI7C9X20303UL consists of one SMBus clock pin (SMBCLK), a SMBus data pin (SMBDATA), and 3 SMBus address pins (GPIO[5:7]). The SMBus clock pin provides or receives the clock signal. The SMBus data pin facilitates the data transmission and reception. Both of the clock and data pins are bidirectional. The SMBus address pins determine the address to which the PI7C9X20303UL responds to. The SMBus address pins generate addresses according to the following table:

Table 6-1 SMBus Address Pin Configuration

BIT	SMBus Address
0	GPIO[5]
1	GPIO[6]
2	GPIO[7]
3	1
4	0
5	1
6	1



7 REGISTER DESCRIPTION

7.1 REGISTER TYPES

REGISTER TYPE	DEFINITION
HwInt	Hardware Initialization
RO	Read Only
RW	Read / Write
RWC	Read / Write 1 to Clear
RWCS	Sticky - Read Only / Write 1 to Clear
RWS	Sticky - Read / Write
ROS	Sticky – Read Only

7.2 TRANSPARENT MODE CONFIGURATION REGISTERS

When the port of switch is set to operate at the transparent mode, it is represented by a logical PCI-to-PCI bridge that implements type 1 configuration space header. The following table details the allocation of the register fields of the PCI 2.3 compatible type 1 configuration space header.

31 –24	23 – 16	15 - 8	7 –0	BYTE OFFSET
Device ID		Vendor ID		00h
Prima	ry Status	Command		04h
	Class Code		Revision ID	08h
Reserved	Header Type	Primary Latency Timer	Cache Line Size	0Ch
		served	10h – 17h	
Secondary Latency Timer	Subordinate Bus Number	Secondary Bus Number	Primary Bus Number	18h
Second	ary Status	I/O Limit Address	I/O Base Address	1Ch
Memory L	imit Address	Memory Ba	ase Address	20h
Prefetchable Mer	nory Limit Address	Prefetchable Men	nory Base Address	24h
	Prefetchable Memory E	Base Address Upper 32-bit	-	28h
	Prefetchable Memory L	imit Address Upper 32-bit		2Ch
I/O Limit Add	ress Upper 16-bit	I/O Base Addre	ess Upper 16-bit	30h
	Reserved		Capability Pointer to 80h	34h
	Res	served		38h
Bridge	Control	Interrupt Pin	Interrupt Line	3Ch
	Res	served	40h – 7Fh	
Power Manage	ment Capabilities	Next Item Pointer=8C	Capability ID=01	80h
PM Data	PPB Support Extensions	Power Management Data		84h
Messag	e Control	Next Item Pointer=A4	Capability ID=05	8Ch
	Messag	e Address		90h
	Message U	pper Address		94h
Res	erved	Messag	ge Data	98h
VPD	Register	Next Item Pointer=A4	Capability ID=03	9Ch
	VPD Da	ta Register	A0h	
Length in	Bytes (14h)	Next Item Pointer=C0	Capability ID=09	A4h
	XPIF	CSR0	A8h	
	XPIF		ACh	
ACK Lat	ency Timer	Replay Time-out Counter		B0h
PHY Parameters		Switch Operation Mode		B4h
	XPIF	CSR2	B8h	
	TL	CSR		BCh
Res	erved	Next Item Pointer=E0	SSID/SSVID Capability ID=0D	C0h
S	SID	SSV		C4h



31 –24	23 – 16	15 - 8	7 –0	BYTE OFFSET		
	Reserved					
	GPIO Data	and Control		D8h		
EEPRO	OM Data	EEPROM Address	EEPROM Control	DCh		
PCI Express Ca	pabilities Register	Next Item Pointer=00	Capability ID=10	E0h		
	Device C	Capabilities		E4h		
Devic	Device Status		Device Control			
	Link Capabilities					
Link	Link Status		Link Control			
	Slot Ca	apabilities		F4h		
Slot	Slot Status		Slot Control			
	Reserved					

Other than the PCI 2.3 compatible configuration space header, the Switch also implements PCI express extended configuration space header, which includes advanced error reporting, virtual channel, and power budgeting capability registers. The following table details the allocation of the register fields of PCI express extended capability space header. The first extended capability always begins at offset 100h with a PCI Express Enhanced Capability header and the rest of capabilities are located at an offset greater than 0FFh relative to the beginning of PCI compatible configuration space.

31 –24	23	- 16	15 - 8	7 –0	BYTE OFFSET	
Next Capability Offset Cap. Version		PCI Express Extended Capability ID=0001h		100h		
	Uncorrectable Error Status Register					
			ror Mask Register		104h 108h	
			or Severity Register		10Ch	
			or Status Register		110h	
			or Mask Register		114h	
			ities and Control Register		118h	
			og Register		11Ch – 128h	
			erved		12Ch – 13Fh	
Next Capability Offs	et=20Ch	Cap. Version	PCI Express Extended	d Capability ID=0002h	140h	
	F	ort VC Capab	pility Register 1		144h	
VC Arbitration Table Offset=3		Po	ort VC Capability Register	7 2	148h	
	atus Register		Port VC Cor	ntrol Register	14Ch	
Port Arbitration Table Offset=4		VC R	Resource Capability Register (0)		150h	
	VC	Resource Co	ntrol Register (0)		154h	
VC Resource St				erved	158h	
		Rese	erved		15Ch-17Ch	
	Port Arbit	ration Table v	vith 128 Phases for VC0		180h – 1BCh	
		Rese	erved		1C0h - 1FCh	
		Rese	erved		200h - 20Bh	
Next Capability Offset=000h Cap. Version		PCI Express Extended Capability ID=0004h		20Ch		
	Reserved Data Select Register					
	Data Register					
	Reserved Power Budget Capability Register					



7.2.1 VENDOR ID REGISTER - OFFSET 00h

BIT	FUNCTION	TYPE	DESCRIPTION
15:0	Vendor ID	RO	Identifies Pericom as the vendor of this device. The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 12D8h.

7.2.2 DEVICE ID REGISTER - OFFSET 00h

BIT	FUNCTION	TYPE	DESCRIPTION
31:16	Device ID	RO	Identifies this device as the PI7C9X20303UL. The default value may be changed by SMBus or auto-loading from EEPROM.
			Resets to 0303h.

7.2.3 COMMAND REGISTER - OFFSET 04h

BIT	FUNCTION	TYPE	DESCRIPTION	
0	I/O Space Enable	RW	0b: Ignores I/O transactions on the primary interface 1b: Enables responses to I/O transactions on the primary interface	
			Resets to 0b.	
1	Memory Space Enable	RW	0b: Ignores memory transactions on the primary interface 1b: Enables responses to memory transactions on the primary interface Reset to 0b.	
2	Bus Master Enable	RW	0b: Does not initiate memory or I/O transactions on the upstream port and handles as an Unsupported Request (UR) to memory and I/O transactions on the downstream port. For Non-Posted Requests, a completion with UR completion status must be returned 1b: Enables the Switch Port to forward memory and I/O Read/Write transactions in the upstream direction	
3	Special Cycle Enable	RO	Reset to 0b. Does not apply to PCI Express. Must be hardwired to 0b.	
4	Memory Write And Invalidate Enable	RO	Does not apply to PCI Express. Must be hardwired to 0b.	
5	VGA Palette Snoop Enable	RO	Does not apply to PCI Express. Must be hardwired to 0b.	
6	Parity Error Response Enable	RW	Ob: Switch may ignore any parity errors that it detects and continue normal operation 1b: Switch must take its normal action when a parity error is detected	
			Reset to 0b.	
7	Wait Cycle Control	RO	Does not apply to PCI Express. Must be hardwired to 0.	
8	SERR# enable	RW	Ob: Disables the reporting of Non-fatal and Fatal errors detected by the Switch to the Root Complex b1: Enables the Non-fatal and Fatal error reporting to Root Complex Reset to 0b.	
9	Fast Back-to-Back Enable	RO	Does not apply to PCI Express. Must be hardwired to 0b.	
10	Interrupt Disable	RW	Controls the ability of a PCI Express device to generate INTx Interrupt Messages. In the Switch, this bit does not affect the forwarding of INTx messages from the downstream ports.	
			Reset to 0b.	

BIT	FUNCTION	TYPE	DESCRIPTION
15:11	Reserved	RO	Reset to 0b.

7.2.4 PRIMARY STATUS REGISTER - OFFSET 04h

BIT	FUNCTION	TYPE	DESCRIPTION
18:16	Reserved	RO	Reset to 000b.
19	Interrupt Status	RO	Indicates that an INTx Interrupt Message is pending internally to the device. In the Switch, the forwarding of INTx messages from the downstream device of the Switch port is not reflected in this bit. Must be hardwired to 0b.
20	Capabilities List	RO	Set to 1 to enable support for the capability list (offset 34h is the pointer to the data structure). Reset to 1b.
21	66MHz Capable	RO	Does not apply to PCI Express. Must be hardwired to 0b.
22	Reserved	RO	Reset to 0b.
23	Fast Back-to-Back Capable	RO	Does not apply to PCI Express. Must be hardwired to 0b.
24	Master Data Parity Error	RWC	Set to 1 (by a requester) whenever a Parity error is detected or forwarded on the primary side of the port in a Switch. If the Parity Error Response Enable bit is cleared, this bit is never set. Reset to 0b.
26:25	DEVSEL# timing	RO	Does not apply to PCI Express. Must be hardwired to 0b.
27	Signaled Target Abort	RO	Set to 1 (by a completer) whenever completing a request on the primary side using the Completer Abort Completion Status. Reset to 0b.
28	Received Target Abort	RO	Set to 1 (by a requestor) whenever receiving a Completion with Completer Abort Completion Status on the primary side. Reset to 0b.
29	Received Master Abort	RO	Set to 1 (by a requestor) whenever receiving a Completion with Unsupported Request Completion Status on primary side. Reset to 0b.
30	Signaled System Error	RWC	Set to 1 when the Switch sends an ERR_FATAL or ERR_NONFATAL Message, and the SERR Enable bit in the Command register is 1. Reset to 0b.
31	Detected Parity Error	RWC	Set to 1 whenever the primary side of the port in a Switch receives a Poisoned TLP. Reset to 0b.

7.2.5 REVISION ID REGISTER - OFFSET 08h

BIT	FUNCTION	TYPE	DESCRIPTION
7:0	Revision	RO	Indicates revision number of device. Hardwired to 03h.

7.2.6 CLASS CODE REGISTER - OFFSET 08h

BIT	FUNCTION	TYPE	DESCRIPTION
15:8	Programming	RO	Read as 00h to indicate no programming interfaces have been defined for
	Interface		PCI-to-PCI Bridges.
23:16	Sub-Class Code	RO	Read as 04h to indicate device is a PCI-to-PCI Bridge.
31:24	Base Class Code	RO	Read as 06h to indicate device is a Bridge device.

7.2.7 CACHE LINE REGISTER - OFFSET 0Ch

BIT	FUNCTION	TYPE	DESCRIPTION
7:0	Cache Line Size	RW	The cache line size register is set by the system firmware and the operating system cache line size. This field is implemented by PCI Express devices as a RW field for legacy compatibility, but it has no impact on any PCI Express device functionality. Reset to 0b.

7.2.8 PRIMARY LATENCY TIMER REGISTER – OFFSET 0Ch

BIT	FUNCTION	TYPE	DESCRIPTION
15:8	Primary Latency timer	RO	Does not apply to PCI Express. Must be hardwired to 00h.

7.2.9 HEADER TYPE REGISTER – OFFSET 0Ch

BIT	FUNCTION	TYPE	DESCRIPTION
23:16	Header Type	RO	Read as 01h to indicate that the register layout conforms to the standard PCI-to-PCI Bridge layout.

7.2.10 PRIMARY BUS NUMBER REGISTER - OFFSET 18h

BIT	FUNCTION	TYPE	DESCRIPTION
7:0	Primary Bus Number	RW	Indicates the number of the PCI bus to which the primary interface is connected. The value is set in software during configuration. Reset to 00h.

7.2.11 SECONDARY BUS NUMBER REGISTER - OFFSET 18h

BIT	FUNCTION	TYPE	DESCRIPTION
15:8	Secondary Bus Number	RW	Indicates the number of the PCI bus to which the secondary interface is connected. The value is set in software during configuration.
			Reset to 00h.

7.2.12 SUBORDINATE BUS NUMBER REGISTER – OFFSET 18h

BIT	FUNCTION	TYPE	DESCRIPTION
23:16	Subordinate Bus Number	RW	Indicates the number of the PCI bus with the highest number that is subordinate to the Bridge. The value is set in software during configuration.
			Reset to 00h.



7.2.13 SECONDARY LATENCY TIMER REGISTER – OFFSET 18h

В	IT	FUNCTION	TYPE	DESCRIPTION
3	1:24	Secondary Latency Timer	RO	Does not apply to PCI Express. Must be hardwired to 00h.

7.2.14 I/O BASE ADDRESS REGISTER - OFFSET 1Ch

BIT	FUNCTION	TYPE	DESCRIPTION
3:0	32-bit Indicator	RO	Read as 01h to indicate 32-bit I/O addressing.
7:4	I/O Base Address [15:12]	RW	Defines the bottom address of the I/O address range for the Bridge to determine when to forward I/O transactions from one interface to the other. The upper 4 bits correspond to address bits [15:12] and are writable. The lower 12 bits corresponding to address bits [11:0] are assumed to be 0. The upper 16 bits corresponding to address bits [31:16] are defined in the I/O base address upper 16 bits address register. Reset to 0h.

7.2.15 I/O LIMIT ADDRESS REGISTER – OFFSET 1Ch

BIT	FUNCTION	TYPE	DESCRIPTION
11:8	32-bit Indicator	RO	Read as 01h to indicate 32-bit I/O addressing.
15:12	I/O Limit Address [15:12]	RW	Defines the top address of the I/O address range for the Bridge to determine when to forward I/O transactions from one interface to the other. The upper 4 bits correspond to address bits [15:12] and are writable. The lower 12 bits corresponding to address bits [11:0] are assumed to be FFFh. The upper 16 bits corresponding to address bits [31:16] are defined in the I/O limit address upper 16 bits address register. Reset to 0h.

7.2.16 SECONDARY STATUS REGISTER - OFFSET 1Ch

BIT	FUNCTION	TYPE	DESCRIPTION
20:16	Reserved	RO	Reset to 00000b.
21	66MHz Capable	RO	Does not apply to PCI Express. Must be hardwired to 0b.
22	Reserved	RO	Reset to 0b.
23	Fast Back-to-Back Capable	RO	Does not apply to PCI Express. Must be hardwired to 0b.
24	Master Data Parity Error	RWC	Set to 1 (by a requester) whenever a Parity error is detected or forwarded on the secondary side of the port in a Switch. If the Parity Error Response Enable bit is cleared, this bit is never set. Reset to 0b.
26:25	DEVSEL_L timing	RO	Does not apply to PCI Express. Must be hardwired to 0b.
27	Signaled Target Abort	RO	Set to 1 (by a completer) whenever completing a request in the secondary side using Completer Abort Completion Status. Reset to 0b.
28	Received Target Abort	RO	Set to 1 (by a requestor) whenever receiving a Completion with Completer Abort Completion Status in the secondary side. Reset to 0b.



BIT	FUNCTION	TYPE	DESCRIPTION
29	Received Master Abort	RO	Set to 1 (by a requestor) whenever receiving a Completion with Unsupported Request Completion Status in secondary side. Reset to 0b.
30	Received System Error	RWC	Set to 1 when the Switch sends an ERR_FATAL or ERR_NONFATAL Message, and the SERR Enable bit in the Bridge Control register is 1. Reset to 0b.
31	Detected Parity Error	RWC	Set to 1 whenever the secondary side of the port in a Switch receives a Poisoned TLP. Reset to 0b.

7.2.17 MEMORY BASE ADDRESS REGISTER – OFFSET 20h

BIT	FUNCTION	TYPE	DESCRIPTION
3:0	Reserved	RO	Reset to 0h.
15:4	Memory Base Address [15:4]	RW	Defines the bottom address of an address range for the Bridge to determine when to forward memory transactions from one interface to the other. The upper 12 bits correspond to address bits [31:20] and are able to be written to. The lower 20 bits corresponding to address bits [19:0] are assumed to be 0. Reset to 000h.

7.2.18 MEMORY LIMIT ADDRESS REGISTER - OFFSET 20h

BIT	FUNCTION	TYPE	DESCRIPTION
19:16	Reserved	RO	Reset to 0h.
31:20	Memory Limit Address [31:20]	RW	Defines the top address of an address range for the Bridge to determine when to forward memory transactions from one interface to the other. The upper 12 bits correspond to address bits [31:20] and are writable. The lower 20 bits corresponding to address bits [19:0] are assumed to be FFFFFh. Reset to 000h.

7.2.19 PREFETCHABLE MEMORY BASE ADDRESS REGISTER - OFFSET 24h

BIT	FUNCTION	TYPE	DESCRIPTION
3:0	64-bit addressing	RO	Read as 0001b to indicate 64-bit addressing.
15:4	Prefetchable Memory Base Address [31:20]	RW	Defines the bottom address of an address range for the Bridge to determine when to forward memory read and write transactions from one interface to the other. The upper 12 bits correspond to address bits [31:20] and are writable. The lower 20 bits are assumed to be 0. The memory base register upper 32 bits contain the upper half of the base address. Reset to 000h.

7.2.20 PREFETCHABLE MEMORY LIMIT ADDRESS REGISTER - OFFSET 24h

BIT	FUNCTION	TYPE	DESCRIPTION
19:16	64-bit addressing	RO	Read as 0001b to indicate 64-bit addressing.



BIT	FUNCTION	TYPE	DESCRIPTION
31:20	Prefetchable Memory Limit Address [31:20]	RW	Defines the top address of an address range for the Bridge to determine when to forward memory read and write transactions from one interface to the other. The upper 12 bits correspond to address bits [31:20] and are writable. The lower 20 bits are assumed to be FFFFFh. The memory limit upper 32 bits register contains the upper half of the limit address. Reset to 000h.

7.2.21 PREFETCHABLE MEMORY BASE ADDRESS UPPER 32-BITS REGISTER – OFFSET 28h

BIT	FUNCTION	TYPE	DESCRIPTION
31:0	Prefetchable Memory Base Address, Upper 32-bits [63:32]	RW	Defines the upper 32-bits of a 64-bit bottom address of an address range for the Bridge to determine when to forward memory read and write transactions from one interface to the other. Reset to 00000000h.

7.2.22 PREFETCHABLE MEMORY LIMIT ADDRESS UPPER 32-BITS REGISTER – OFFSET 2Ch

BIT	FUNCTION	TYPE	DESCRIPTION
31:0	Prefetchable Memory Limit Address, Upper 32-bits [63:32]	RW	Defines the upper 32-bits of a 64-bit top address of an address range for the Bridge to determine when to forward memory read and write transactions from one interface to the other. Reset to 00000000h.

7.2.23 I/O BASE ADDRESS UPPER 16-BITS REGISTER – OFFSET 30h

BIT	FUNCTION	TYPE	DESCRIPTION
15:0	I/O Base Address, Upper 16-bits [31:16]	RW	Defines the upper 16-bits of a 32-bit bottom address of an address range for the Bridge to determine when to forward I/O transactions from one interface to the other. Reset to 0000h.

7.2.24 I/O LIMIT ADDRESS UPPER 16-BITS REGISTER - OFFSET 30h

BIT	FUNCTION	TYPE	DESCRIPTION
31:16	I/O Limit Address, Upper 16-bits [31:16]	RW	Defines the upper 16-bits of a 32-bit top address of an address range for the Bridge to determine when to forward I/O transactions from one interface to the other. Reset to 0000h.

7.2.25 CAPABILITY POINTER REGISTER - OFFSET 34h

BIT	FUNCTION	TYPE	DESCRIPTION
7:0	Capability Pointer	RO	Pointer points to the PCI power management registers (80h).



BIT	FUNCTION	TYPE	DESCRIPTION
			Reset to 80h.

7.2.26 INTERRUPT LINE REGISTER - OFFSET 3Ch

BIT	FUNCTION	TYPE	DESCRIPTION
7:0	Interrupt Line	RW	Reset to 00h.

7.2.27 INTERRUPT PIN REGISTER – OFFSET 3Ch

BIT	FUNCTION	TYPE	DESCRIPTION
15:8	Interrupt Pin	RO	The Switch implements INTA virtual wire interrupt signals to represent hot- plug events at downstream ports. The default value on the downstream ports may be changed by SMBus or auto-loading from EEPROM. Reset to 00h.

7.2.28 BRIDGE CONTROL REGISTER - OFFSET 3Ch

BIT	FUNCTION	TYPE	DESCRIPTION
16	Parity Error Response	RW	0b: Ignore Poisoned TLPs on the secondary interface 1b: Enable the Poisoned TLPs reporting and detection on the secondary interface Reset to 0b.
17	S_SERR# enable	RW	0b: Disables the forwarding of EER_COR, ERR_NONFATAL and ERR_FATAL from secondary to primary interface 1b: Enables the forwarding of EER_COR, ERR_NONFATAL and ERR_FATAL from secondary to primary interface Reset to 0b.
18	ISA Enable	RW	0b: Forwards downstream all I/O addresses in the address range defined by the I/O Base, I/O Base, and Limit registers 1b: Forwards upstream all I/O addresses in the address range defined by the I/O Base and Limit registers that are in the first 64KB of PCI I/O address space (top 768 bytes of each 1KB block) Reset to 0b.
19	VGA Enable	RW	0: Ignores access to the VGA memory or IO address range 1: Forwards transactions targeted at the VGA memory or IO address range VGA memory range starts from 000A 0000h to 000B FFFFh VGA IO addresses are in the first 64KB of IO address space. AD [9:0] is in the ranges 3B0 to 3BBh and 3C0h to 3DFh. Reset to 0b. Please note that this bit is reserved in Port 2.
20	VGA 16-bit decode	RW	0b: Executes 10-bit address decoding on VGA I/O accesses 1b: Executes 16-bit address decoding on VGA I/O accesses Reset to 0b. Please note that this bit is reserved in Port 2.
21	Master Abort Mode	RO	Does not apply to PCI Express. Must be hardwired to 0b.
22	Secondary Bus Reset	RW	0b: Does not trigger a hot reset on the corresponding PCI Express Port 1b: Triggers a hot reset on the corresponding PCI Express Port At the downstream port, it asserts PORT_RST# to the attached downstream device. At the upstream port, it asserts the PORT_RST# at all the downstream ports.
			Reset to 0b.



BIT	FUNCTION	TYPE	DESCRIPTION
23	Fast Back-to-Back Enable	RO	Does not apply to PCI Express. Must be hardwired to 0b.
24	Primary Master Timeout	RO	Does not apply to PCI Express. Must be hardwired to 0b.
25	Secondary Master Timeout	RO	Does not apply to PCI Express. Must be hardwired to 0b.
26	Master Timeout Status	RO	Does not apply to PCI Express. Must be hardwired to 0b.
27	Discard Timer SERR# enable	RO	Does not apply to PCI Express. Must be hardwired to 0b.
31:28	Reserved	RO	Reset to 0h.

7.2.29 POWER MANAGEMENT CAPABILITY ID REGISTER - OFFSET 80h

BIT	FUNCTION	TYPE	DESCRIPTION
7:0	Enhanced	RO	Read as 01h to indicate that these are power management enhanced capability
	Capabilities ID		registers.

7.2.30 NEXT ITEM POINTER REGISTER - OFFSET 80h

BIT	FUNCTION	TYPE	DESCRIPTION
15:8	Next Item Pointer	RO	At upstream ports, the pointer points to the Vital Protocol Data (VPD) capability register (9Ch). At downstream ports, the pointer points to the Message capability register (8Ch). Reset to 9Ch (Upstream port). Reset to 8Ch (Downstream port).

7.2.31 POWER MANAGEMENT CAPABILITIES REGISTER - OFFSET 80h

BIT	FUNCTION	TYPE	DESCRIPTION
18:16	Power Management	RO	Read as 011b to indicate the device is compliant to Revision 1.2 of <i>PCI</i>
18.10	Revision	KO	Power Management Interface Specifications.
19	PME# Clock	RO	Does not apply to PCI Express. Must be hardwired to 0b.
20	Reserved	RO	Reset to 0b.
21	Device Specific Initialization	RO	Read as 0b to indicate Switch does not have device specific initialization requirements. The default value may be changed by SMBus or auto-loading from EEPROM.
24:22	AUX Current	RO	Reset as 111b to indicate the Switch needs 375 mA in D3 state. The default value may be changed by SMBus or auto-loading from EEPROM.
25	D1 Power State Support	RO	Read as 1b to indicate Switch supports the D1 power management state. The default value may be changed by SMBus or auto-loading from EEPROM.
26	D2 Power State Support	RO	Read as 1b to indicate Switch supports the D2 power management state. The default value may be changed by SMBus or auto-loading from EEPROM.
31:27	PME# Support	RO	Read as 11111b to indicate Switch supports the forwarding of PME# message in all power states. The default value may be changed by SMBus or autoloading from EEPROM.

7.2.32 POWER MANAGEMENT DATA REGISTER - OFFSET 84h

BIT	FUNCTION	TYPE	DESCRIPTION
1:0	Power State	RW	Indicates the current power state of the Switch. Writing a value of D0 when the previous state was D3 cause a hot reset without asserting DWNRST_L.



BIT	FUNCTION	TYPE	DESCRIPTION
			00b: D0 state
			01b: D1 state
			10b: D2 state
			11b: D3 hot state
			Reset to 00b.
2	Reserved	RO	Reset to 0b.
3	No_Soft_Reset	RO	When set, this bit indicates that device transitioning from D3hot to D0 does not perform an internal reset. When clear, an internal reset is performed when power state transits from D3hot to D0. This bit can be rewritten with EEPROM programming. The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 1b.
7:4	Reserved	RO	Reset to 0b.
8	PME# Enable	RWS	When asserted, the Switch will generate the PME# message. Reset to 0b.
12:9	Data Select	RW	Select data registers. Reset to 0h.
14:13	Data Scale	RO	Reset to 00b.
15	PME status	ROS	Read as 0b as the PME# message is not implemented.

7.2.33 PPB SUPPORT EXTENSIONS - OFFSET 84h

BIT	FUNCTION	TYPE	DESCRIPTION
21:16	Reserved	RO	Reset to 000000b.
22	B2_B3 Support for D3 _{HOT}	RO	Does not apply to PCI Express. Must be hardwired to 0b.
23	Bus Power / Clock Control Enable	RO	Does not apply to PCI Express. Must be hardwired to 0b.

7.2.34 DATA REGISTER - OFFSET 84h

BIT	FUNCTION	TYPE	DESCRIPTION
31:24	Data Register	RO	Data Register. The default value may be changed by SMBus or auto-loading from EEPROM.
			Reset to 0b.

7.2.35 MSI CAPABILITY ID REGISTER – OFFSET 8Ch (Downstream Port Only)

BIT	FUNCTION	TYPE	DESCRIPTION
7:0	Enhanced Capabilities ID	RO	Read as 05h to indicate that this is message signal interrupt capability register.



7.2.36 NEXT ITEM POINTER REGISTER – OFFSET 8Ch (Downstream Port Only)

BIT	FUNCTION	TYPE	DESCRIPTION
			Pointer points to the Vendor specific capability register (A4h).
15:8	Next Item Pointer	RO	
			Reset to A4h.

7.2.37 MESSAGE CONTROL REGISTER – OFFSET 8Ch (Downstream Port Only)

BIT	FUNCTION	TYPE	DESCRIPTION
16	MSI Enable	RW	0b: The function is prohibited from using MSI to request service 1b: The function is permitted to use MSI to request service and is prohibited from using its INTx # pin Reset to 0b.
19:17	Multiple Message Capable	RO	Read as 000b.
22:20	Multiple Message Enable	RW	Reset to 000b.
23	64-bit address capable	RO	0b: The function is not capable of generating a 64-bit message address 1b: The function is capable of generating a 64-bit message address Reset to 1b.
31:24	Reserved	RO	Reset to 00h.

7.2.38 MESSAGE ADDRESS REGISTER – OFFSET 90h (Downstream Port Only)

BIT	FUNCTION	TYPE	DESCRIPTION
1:0	Reserved	RO	Reset to 00b.
31:2	Message Address	RW	If the message enable bit is set, the contents of this register specify the DWORD aligned address for MSI memory write transaction.
			Reset to 0.

7.2.39 MESSAGE UPPER ADDRESS REGISTER – OFFSET 94h (Downstream Port Only)

BIT	FUNCTION	TYPE	DESCRIPTION
31:0	Message Upper Address	RW	This register is only effective if the device supports a 64-bit message address is set.
			Reset to 00000000h.

7.2.40 MESSAGE DATA REGISTER – OFFSET 98h (Downstream Port Only)

BIT	FUNCTION	TYPE	DESCRIPTION
15:0	Message Data	RW	Reset to 0000h.

7.2.41 VPD CAPABILITY ID REGISTER – OFFSET 9Ch (Upstream Port Only)

BIT	FUNCTION	TYPE	DESCRIPTION
7:0	7:0 Enhanced	RO	Read as 03h to indicate that these are VPD enhanced capability registers.
	Capabilities ID		Reset to 03h.

7.2.42 NEXT ITEM POINTER REGISTER – OFFSET 9Ch (Upstream Port Only)

BIT	FUNCTION	TYPE	DESCRIPTION
15:8	Next Item Pointer	RO	Pointer points to the Vendor specific capability register (A4h).
			Reset to A4h.

7.2.43 VPD REGISTER – OFFSET 9Ch (Upstream Port Only)

BIT	FUNCTION	TYPE	DESCRIPTION
17:16	Reserved	RO	Reset to 00b.
23:18	VPD Address	RW	Contains DWORD address that is used to generate read or write cycle to the VPD table stored in EEPROM.
			Reset to 000000b.
30:24	Reserved	RO	Reset to 0000000b.
31	VPD operation	RW	Ob: Performs VPD read command to VPD table at the location as specified in VPD address. This bit is kept '0' and then set to '1' automatically after EEPROM cycle is finished 1b: Performs VPD write command to VPD table at the location as specified in VPD address. This bit is kept '1' and then set to '0' automatically after EEPROM cycle is finished. Reset to 0b.

7.2.44 VPD DATA REGISTER – OFFSET A0h (Upstream Port Only)

BIT	FUNCTION	TYPE	DESCRIPTION
31:0	VPD Data	RW	When read, it returns the last data read from VPD table at the location as specified in VPD Address.
			When written, it places the current data into VPD table at the location as specified in VPD Address.

7.2.45 VENDOR SPECIFIC CAPABILITY ID REGISTER – OFFSET A4h

BIT	FUNCTION	TYPE	DESCRIPTION
7:0	Enhanced Capabilities ID	RO	Read as 09h to indicate that these are vendor specific capability registers. Reset to 09h.



7.2.46 NEXT ITEM POINTER REGISTER – OFFSET A4h

BIT	FUNCTION	TYPE	DESCRIPTION
			Pointer points to the SSID/SSVID capability register (C0h).
15:8	Next Item Pointer	RO	
			Reset to C0h.

7.2.47 LENGTH REGISTER – OFFSET A4h

BIT	FUNCTION	TYPE	DESCRIPTION
31:16	Length Information	RO	The length field provides the information for number of bytes in the capability structure (including the ID and Next pointer bytes).
			Reset to 000Ch.

7.2.48 XPIP CSR0 – OFFSET A8h (Test Purpose Only)

BIT	FUNCTION	TYPE	DESCRIPTION
31:0	Reserved	RW	Reset to 04001060h.

7.2.49 XPIP CSR1 – OFFSET ACh (Test Purpose Only)

BIT	FUNCTION	TYPE	DESCRIPTION
31:0	Reserved	RW	Reset to 04000800h.

7.2.50 REPLAY TIME-OUT COUNTER - OFFSET B0h

BIT	FUNCTION	TYPE	DESCRIPTION
11:0	User Replay Timer	RW	A 12-bit register contains a user-defined value. The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 000h.
12	Enable User Replay Timer	RW	When asserted, the user-defined replay time-out value is be employed. The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 0b.
13	Power Management Capability Disable	RO	The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 0b.
14	MSI Capability Disable	RO	The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 0b.
15	AER Capability Disable	RO	The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 0b.



7.2.51 ACKNOWLEDGE LATENCY TIMER - OFFSET B0h

BIT	FUNCTION	TYPE	DESCRIPTION
29:16	User ACK Latency Timer	RW	A 14-bit register contains a user-defined value. The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 0.
30	Enable User ACK Latency	RW	When asserted, the user-defined ACK latency value is be employed. The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 0b.
31	VGA Capability Enable	RO	When asserted, the VGA Capability is enabled. The value may be changed by auto-loading from EEPROM. Reset to 1b.

7.2.52 SWITCH OPERATION MODE – OFFSET B4h (Upstream Port)

BIT	FUNCTION	TYPE	DESCRIPTION
0	Store-Forward	RW	When set, a store-forward mode is used. Otherwise, the chip is working under cut-through mode. The default value may be changed by SMBus or autoloading from EEPROM.
2:1	Cut-through Threshold	RW	Reset to 0b. Cut-through Threshold. When forwarding a packet from low-speed port to high-speed mode, the chip provides the capability to adjust the forwarding threshold. The default value may be changed by SMBus or auto-loading from EEPROM. 00b: the threshold is set at the middle of forwarding packet 01b: the threshold is set ahead 1-cycle of middle point 10b: the threshold is set ahead 2-cycle of middle point. 11b: the threshold is set ahead 3-cycle of middle point. Reset to 01b.
3	Port Arbitration Mode	RW	When set, the round-robin arbitration will stay in the arbitrated port even if the credit is not enough but request is pending. When clear, the round-robin arbitration will always go to the requesting port, which the outgoing credit is enough for the packet queued in the port. The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 0b.
4	Credit Update Mode	RW	When set, the frequency of releasing new credit to the link partner will be one credit per update. When clear, the frequency of releasing new credit to the link partner will be two credits per update. The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 0b.
5	Ordering on Different Egress Port Mode	RW	When set, there has ordering rule on packets for different egress port. The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 0b.
6	Ordering on Different Tag of Completion Mode	RW	When set, there has ordering rule between completion packet with different tag. The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 0b.
7	Reserved	RO	Reset to 0b.
/	IXESEI VEU	KU	NOSCI 10 U.



BIT	FUNCTION	TYPE	DESCRIPTION
13:8	Power management Control parameter	RW	The default value may be changed by SMBus or auto-loading from EEPROM.
			Reset to 000001b.
14	RX Polarity Inversion Disable	RO	The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 0b.
15	Compliance pattern Parity Control Disable	RO	The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 0b.
16	Low Driver Current	RO	Low Driver Current (LODRV). The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 0b.
17	High Driver Current	RO	High Driver Current (HIDRV). The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 0b.
21:18	Driver Transmit Current	RO	Driver Transmit Current (DTX[3:0]). The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 0000b.
25:22	De-emphasis Transmit Equalization	RO	De-emphasis Transmit Equalization (DEQ[3:0]). The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 1000b.
27:26	Receive Termination Adjustment	RO	Receive Termination Adjustment (RXTRMADJ[1:0]). The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 00b.
29:28	Transmit Termination Adjustment	RO	Transmit Termination Adjustment (TXTRMADJ[1:0]). The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 00b.
31:30	Receiver Equalization Level Control	RO	Receiver Equalization Level Control (RXEQCTL[1:0]). The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 00b.

7.2.53 SWITCH OPERATION MODE – OFFSET B4h (Downstream Port)

BIT	FUNCTION	TYPE	DESCRIPTION
7:0	Reserved	RO	Reset to 0.
13:8	Power Management Control Parameter	RW	The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 000001b.
14	RX Polarity Inversion Disable	RW	The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 0b.
15	Compliance Pattern Parity Control Disable	RW	The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 0b.
16	Low Driver Current	RO	It indicates the status of the strapping pin LODRV. The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 0b.



BIT	FUNCTION	TYPE	DESCRIPTION
17	High Driver Current	RO	It indicates the status of the strapping pin HIDRV. The default value may be changed by SMBus or auto-loading from EEPROM.
21:18	Driver Transmit Current	RO	Reset to 0b. It indicates the status of the strapping pins DTX[3:0]. The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 0000b.
25:22	De-emphasis Transmit Equalization	RO	It indicates the status of the strapping pins DEQ[3:0]. The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 1000b.
27:26	Receive Termination Adjustment	RO	It indicates the status of the strapping pins RXTRMADJ[1:0]. The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 00b.
29:28	Transmit Termination Adjustment	RO	It indicates the status of the strapping pins TXTRMADJ[1:0]. The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 00b.
31:30	Receiver Equalization Level Control	RO	It indicates the status of the strapping pins RXEQCTL[1:0]. The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 00b.

7.2.54 XPIP CSR2 – OFFSET B8h (Test Purpose Only)

BIT	FUNCTION	TYPE	DESCRIPTION
31:0	Reserved	RO	Reset to 00000030h.

7.2.55 TL CSR - OFFSET BCh

BIT	FUNCTION	TYPE	DESCRIPTION
31:0	Reserved	RO	Reset to 00000004h.

7.2.56 SSID/SSVID CAPABILITY ID REGISTER - OFFSET COh

BIT	FUNCTION	TYPE	DESCRIPTION
7:0	SSID/SSVID	RO	Read as 0Dh to indicate that these are SSID/SSVID capability registers.
7.0	Capabilities ID	RO	

7.2.57 NEXT ITEM POINTER REGISTER – OFFSET C0h

BIT	FUNCTION	TYPE	DESCRIPTION
			Pointer points to the PCI Express capability register (E0h).
15:8	Next Item Pointer	RO	
			Reset to E0h.

7.2.58 SUBSYSTEM VENDOR ID REGISTER – OFFSET C4h

BIT FUNCTION TYPE DESCRIPTION	BIT	FUNCTION	TYPE	DESCRIPTION
-------------------------------------	-----	----------	------	-------------



15:0	SSVID	RO	It indicates the sub-system vendor id. The default value may be changed by SMBus or auto-loading from EEPROM.
			Reset to 0000h.

7.2.59 SUBSYSTEM ID REGISTER – OFFSET C4h

BIT	FUNCTION	TYPE	DESCRIPTION
31:16	SSID	RO	It indicates the sub-system device id. The default value may be changed by SMBus or auto-loading from EEPROM.
			Reset to 0000h.

7.2.60 GPIO CONTROL REGISTER – OFFSET D8h (Upstream Port Only)

BIT	FUNCTION	TYPE	DESCRIPTION
0	GPIO [0] Input	RO	State of GPIO [0] pin
			0b: GPIO [0] is an input pin
1	GPIO [0] Output	RW	1b: GPIO [0] is an output pin
1	Enable	IC VV	
			Reset to 0b.
			Value of this bit will be output to GPIO [0] pin if GPIO [0] is configured as
2	GPIO [0] Output	RW	an output pin.
_	Register	1011	
			Reset to 0b.
3	Reserved	RO	Reset to 0b.
4	GPIO [1] Input	RO	State of GPIO [1] pin.
			0b: GPIO [1] is an input pin
5	GPIO [1] Output	RW	1b: GPIO [1] is an output pin
	Enable		D Ol
			Reset to 0b.
	CDYO F11 O		Value of this bit will be output to GPIO [1] pin if GPIO [1] is configured as
6	GPIO [1] Output	RW	an output pin.
	Register		D 44 01
7	D 1	D.O.	Reset to 0b.
7	Reserved	RO	Reset to 0b.
8	GPIO [2] Input	RO	State of GPIO [2] pin
	CDIO [2] Outmot		0b: GPIO [2] is an input pin
9	GPIO [2] Output Enable	RW	1b: GPIO [2] is an output pin
	Eliable		Reset to 0b.
			Value of this bit will be output to GPIO [2] pin if GPIO [2] is configured as
	GPIO [2] Output		an output pin.
10	Register	RW	un output pin.
	register		Reset to 0b.
11	Reserved	RO	Reset to 0b.
12	GPIO [3] Input	RO	State of GPIO [3] pin.
	5-10 [5] mpar	110	0b: GPIO [3] is an input pin
1.0	GPIO [3] Output	D.V.	1b: GPIO [3] is an output pin
13	Enable	RW	
			Reset to 0b.
			Value of this bit will be output to GPIO [3] pin if GPIO [3] is configured as
1.4	GPIO [3] Output	DW	an output pin.
14	Register	RW	
			Reset to 0b.
15	Reserved	RO	Reset to 0b.
16	GPIO [4] Input	RO	State of GPIO [4] pin.



BIT	FUNCTION	TYPE	DESCRIPTION
17	GPIO [4] Output Enable	RW	0b: GPIO [4] is an input pin 1b: GPIO [4] is an output pin
			Reset to 0b. Value of this bit will be output to GPIO [4] pin if GPIO [4] is configured as
18	GPIO [4] Output Register	RW	an output pin.
10		7.0	Reset to 0b.
19	Reserved	RO	Reset to 0b.
20	GPIO [5] Input	RO	State of GPIO [5] pin.
21	GPIO [5] Output Enable	RW	0b: GPIO [5] is an input pin 1b: GPIO [5] is an output pin
			Reset to 0b.
22	GPIO [5] Output Register	RW	Value of this bit will be output to GPIO [5] pin if GPIO [5] is configured as an output pin.
	register		Reset to 0b.
23	Reserved	RO	Reset to 0b.
24	GPIO [6] Input	RO	State of GPIO [6] pin.
25	GPIO [6] Output Enable	RW	0b: GPIO [6] is an input pin 1b: GPIO [6] is an output pin
			Reset to 0b.
26	GPIO [6] Output Register	RW	Value of this bit will be output to GPIO [6] pin if GPIO [6] is configured as an output pin.
			Reset to 0b.
27	Reserved	RO	Reset to 0b.
28	GPIO [7] Input	RO	State of GPIO [7] pin.
29	GPIO [7] Output	RW	0b: GPIO [7] is an input pin 1b: GPIO [7] is an output pin
			Reset to 0b.
30	GPIO [7] Output Register	RW	Value of this bit will be output to GPIO [7] pin if GPIO [7] is configured as an output pin.
			Reset to 0b.
31	Reserved	RO	Reset to 0b.

7.2.61 EEPROM CONTROL REGISTER – OFFSET DCh (Upstream Port Only)

BIT	FUNCTION	TYPE	DESCRIPTION
0	EEPROM Start	RW	Starts the EEPROM read or write cycle. Reset to 0b.
1	EEPROM Command	RW	Sends the command to the EEPROM. 0b: EEPROM read 1b: EEPROM write Reset to 0b.
2	EEPROM Error Status	RO	1b: EEPROM acknowledge was not received during the EEPROM cycle. Reset to 0b.
3	EEPROM Autoload Success	RO	Ob: EEPROM autoload was unsuccessful or is disabled 1b: EEPROM autolad occurred successfully after RESET. Configuration registers were loaded with values in the EEPROM It will be cleared when read at this bit.

BIT	FUNCTION	TYPE	DESCRIPTION
4	EEPROM Autoload Status	RO	0b: EEPROM autoload was unsuccessful or is disabled 1b: EEPROM autoload occurred successfully after PREST. Configuration registers were loaded with values stored in the EEPROM Reset to 0b.
5	EEPROM Autoload Disable	RW	0b: EEPROM autoload enabled 1b: EEPROM autoload disabled Reset to 1b.
7:6	EEPROM Clock Rate	RW	Determines the frequency of the EEPROM clock, which is derived from the primary clock. 00b: Reserved 01b: PEXCLK / 1024 (PEXCLK is 125MHz) 10b: Reserved 11b: Test Mode Reset to 01b.

7.2.62 EEPROM ADDRESS REGISTER – OFFSET DCh (Upstream Port Only)

BIT	FUNCTION	TYPE	DESCRIPTION
8	Reserved	RO	Reset to 0b.
15:9	EEPROM Address	RW	Contains the EEPROM address. Reset to 0.

7.2.63 EEPROM DATA REGISTER – OFFSET DCh (Upstream Port Only)

BIT	FUNCTION	TYPE	DESCRIPTION
31:16	EEPROM Data	RW	Contains the data to be written to the EEPROM. After completion of a read cycle, this register will contain the data from the EEPROM.
			Reset to 0000h.

7.2.64 PCI EXPRESS CAPABILITY ID REGISTER - OFFSET E0h

BIT	FUNCTION	TYPE	DESCRIPTION
7:0	Enhanced	RO	Read as 10h to indicate that these are PCI express enhanced capability
7.0	Capabilities ID	RO	registers.

7.2.65 NEXT ITEM POINTER REGISTER - OFFSET E0h

BIT	FUNCTION	TYPE	DESCRIPTION
15:8	Next Item Pointer	RO	Read as 00h. No other ECP registers.

7.2.66 PCI EXPRESS CAPABILITIES REGISTER – OFFSET E0h

BIT	FUNCTION	TYPE	DESCRIPTION
19:16	Capability Version	RO	Read as 0001b to indicate the device is compliant to the PCI Express Base Specifications.



BIT	FUNCTION	TYPE	DESCRIPTION
23:20	Device/Port Type	RO	Indicates the type of PCI Express logical device. Reset to 0101b (Upstream port). Reset to 0110b (Downstream port).
24	Slot Implemented	HwInt	When set, indicates that the PCIe Link associated with this Port is connected to a slot. This field is valid for downstream port of the Switch. The default value may be changed by the status of strapped pin, SMBUs, or auto-loading from EEPROM.
29:25	Interrupt Message Number	RO	Read as 0b. No MSI messages are generated in the transparent mode.
31:30	Reserved	RO	Reset to 00b.

7.2.67 DEVICE CAPABILITIES REGISTER - OFFSET E4h

BIT	FUNCTION	TYPE	DESCRIPTION
2:0	Max_Payload_Size Supported	RO	Indicates the maximum payload size that the device can support for TLPs. Each port of the Switch supports 256 bytes max payload size. The default value may be changed by SMBus or auto-loading from EEPROM.
			Reset to 001b.
4:3	Phantom Functions Supported	RO	Indicates the support for use of unclaimed function numbers as Phantom functions. Read as 00b, since the Switch does not act as a requester. Reset to 00b.
5	Extended Tag Field Supported	RO	Indicates the maximum supported size of Tag field as a Requester. Read as 0, since the Switch does not act as a requester. Reset to 0b.
8:6	Endpoint L0s Acceptable Latency	RO	Acceptable total latency that an Endpoint can withstand due to the transition from L0s state to the L0 state. For Switch, the ASPM software would not check this value. Reset to 000b.
11:9	Endpoint L1 Acceptable Latency	RO	Acceptable total latency that an Endpoint can withstand due to the transition from L1 state to the L0 state. For Switch, the ASPM software would not check this value.
			Reset to 000b.
14:12	Reserved	RO	Reset to 000b.
15	Role_Based Error Reporting	RO	When set, indicates that the device implements the functionality originally defined in the Error Reporting ECN. The default value may be changed by SMBus or auto-loading from EEPROM.
			Reset to 1b.
17:16	Reserved	RO	Reset to 00b.
			It applies to Upstream Port only. In combination with the Slot Power Limit Scale value, specifies the upper limit on power supplied by slot.
25:18	Captured Slot Power Limit Value	RO	This value is set by the Set_Slot_Power_Limit message or hardwired to 00h.
			Reset to 00h.
27.24	Captured Slot Power	no.	It applies to Upstream Port only. Specifies the scale used for the Slot Power Limit Value.
27:26	Limit Scale	RO	This value is set by the Set_Slot_Power_Limit message or hardwired to 00b.
			Reset to 00b.
31:28	Reserved	RO	Reset to 0h.



7.2.68 DEVICE CONTROL REGISTER - OFFSET E8h

BIT	FUNCTION	TYPE	DESCRIPTION
0	Correctable Error Reporting Enable	RW	0b: Disable Correctable Error Reporting 1b: Enable Correctable Error Reporting
1	Non-Fatal Error Reporting Enable	RW	Reset to 0b. 0b: Disable Non-Fatal Error Reporting 1b: Enable Non-Fatal Error Reporting Reset to 0b.
2	Fatal Error Reporting Enable	RW	0b: Disable Fatal Error Reporting 1b: Enable Fatal Error Reporting Reset to 0b.
3	Unsupported Request Reporting Enable	RW	0b: Disable Unsupported Request Reporting 1b: Enable Unsupported Request Reporting Reset to 0b.
4	Enable Relaxed Ordering	RO	When set, it permits the device to set the Relaxed Ordering bit in the attribute field of transaction. Since the Switch can not either act as a requester or alter the content of packet it forwards, this bit always returns '0' when read. Reset to 0b.
7:5	Max_Payload_Size	RW	This field sets maximum TLP payload size for the device. Permissible values that can be programmed are indicated by the Max_Payload_Size Supported in the Device Capabilities register. Any value exceeding the Max_Payload_Size Supported written to this register results into clamping to the Max_Payload_Size Supported value.
			Reset to 000b.
8	Extended Tag Field Enable	RW	Does not apply to PCI Express Switch. Returns '0' when read. Reset to 0.
9	Phantom Function Enable	RW	Does not apply to PCI Express Switch. Returns '0' when read. Reset to 0b.
10	Auxiliary (AUX) Power PM Enable	RWS	When set, indicates that a device is enabled to draw AUX power independent of PME AUX power. Reset to 0b.
11	Enable No Snoop	RO	When set, it permits to set the No Snoop bit in the attribute field of transaction. Since the Switch can not either act as a requester or alter the content of packet it forwards, this bit always returns '0' when read.
14:12	Max_Read_ Request_Size	RO	Reset to 0b. This field sets the maximum Read Request size for the device as a Requester. Since the Switch does not generate read request by itself, these bits are hardwired to 000b.
1.5	D 1	D.O.	Reset to 000b.
15	Reserved	RO	Reset to 0b.

7.2.69 DEVICE STATUS REGISTER - OFFSET E8h

BIT	FUNCTION	TYPE	DESCRIPTION
16	Correctable Error Detected	RW1C	Asserted when correctable error is detected. Errors are logged in this register regardless of whether error reporting is enabled or not in the Device Control register. Reset to 0b.



BIT	FUNCTION	TYPE	DESCRIPTION
17	Non-Fatal Error Detected	RW1C	Asserted when non-fatal error is detected. Errors are logged in this register regardless of whether error reporting is enabled or not in the Device Control register. Reset to 0b.
18	Fatal Error Detected	RW1C	Asserted when fatal error is detected. Errors are logged in this register regardless of whether error reporting is enabled or not in the Device Control register. Reset to 0b.
19	Unsupported Request Detected	RW1C	Asserted when unsupported request is detected. Errors are logged in this register regardless of whether error reporting is enabled or not in the Device Control register. Reset to 0b.
20	AUX Power Detected	RO	Asserted when the AUX power is detected by the Switch Reset to 1b.
21	Transactions Pending	RO	Each port of Switch does not issue Non-posted Requests on its own behalf, so this bit is hardwired to 0b. Reset to 0b.
31:22	Reserved	RO	Reset to 0.

7.2.70 LINK CAPABILITIES REGISTER - OFFSET ECh

BIT	FUNCTION	TYPE	DESCRIPTION
3:0	Maximum Link Speed	RO	Read as 0001b to indicate the maximum speed of the Express link is 2.5 Gb/s.
9:4	Maximum Link Width	RO	Indicates the maximum width of the given PCIe Link. The width of each port is determined by strapped pin or EEPROM pre-loaded value. Reset to 000001b (x1) for Port 0. Reset to 000001b (x1) for Port 1. Reset to 000001b (x1) for Port 2.
11:10	Active State Power Management (ASPM) Support	RO	Indicates the level of ASPM supported on the given PCIe Link. Each port of Switch supports L0s and L1 entry. The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 01b.
14:12	L0s Exit Latency	RO	Indicates the L0s exit latency for the given PCIe Link. The length of time this port requires to complete transition from L0s to L0 is in the range of 256ns to less than 512ns. The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 011b.
17:15	L1 Exit Latency	RO	Indicates the L1 exit latency for the given PCIe Link. The length of time this port requires to complete transition from L1 to L0 is in the range of 16us to less than 32us. The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 000b.
18	Reserved	RO	Reset to 0b.
19	Surprise Down Error Reporting Capable	RO	For a Downstream port, this bit must be set to 1b if the component supports the optional capability of detecting and reporting a Surprise Down error condition. For Upstream Ports, which does not support this optional capability, this bit must be hardwired to 0b.
			Rest to 0b.



BIT	FUNCTION	TYPE	DESCRIPTION
20	Data Link Layer Active Reporting	RO	For a Downstream Port, this bit must be set to 1b if the component supports the optional capability of reporting the DL_Active state of the Data Link Control and Management State Machine. For a hot-plug capable Downstream Port, this bit must be set to 1b.
	Capable		For Upstream Port, this bit must be hardwired to 0b.
			Reset to 0b for upstream port. Reset to 1b for downstream ports.
23:21	Reserved	R0	Reset to 000b
			Indicates the PCIe Port Number for the given PCIe Link. The default value may be changed by SMBus or auto-loading from EEPROM.
31:24	Port Number	RO	Reset to 00h for Port 0. Reset to 01h for Port 1.
			Reset to 02h for Port 2.

7.2.71 LINK CONTROL REGISTER - OFFSET F0h

BIT	FUNCTION	TYPE	DESCRIPTION
1:0	Active State Power Management (ASPM) Control	RW	00b: ASPM is Disabled 01b: L0s Entry Enabled 10b: L1 Entry Enabled 11b: L0s and L1 Entry Enabled Note that the receiver must be capable of entering L0s even when the field is disabled. Reset to 00b.
2	Reserved	RO	Reset to 0b.
3	Read Completion Boundary (RCB)	RO	Does not apply to PCI Express Switch. Returns '0' when read. Reset to 0b.
4	Link Disable	RW	At upstream port, it is not allowed to disable the link, so this bit is hardwired to '0'. For downstream ports, it disables the link when this bit is set. Reset to 0b.
5	Retrain Link	RW	At upstream port, it is not allowed to retrain the link, so this bit is hardwired to 0b. For downstream ports, it initiates Link Retraining when this bit is set. This bit always returns 0b when read.
6	Common Clock Configuration	RW	Ob: The components at both ends of a link are operating with asynchronous reference clock 1b: The components at both ends of a link are operating with a distributed common reference clock Reset to 0b.
7	Extended Synch	RW	When set, it transmits 4096 FTS ordered sets in the L0s state for entering L0 state and transmits 1024 TS1 ordered sets in the L1 state for entering L0 state. Reset to 0b.
15:8	Reserved	RO	Reset to 00h.

7.2.72 LINK STATUS REGISTER - OFFSET F0h

BIT	FUNCTION	TYPE	DESCRIPTION
19:16	Link Speed	RO	Read as 0001b to indicate the negotiated speed of the Express link is 2.5 Gb/s.



BIT	FUNCTION	TYPE	DESCRIPTION
25:20	Negotiated Link Width	RO	Indicates the negotiated width of the given PCIe link. Reset to 000001b (x1).
26	Training Error	RO	When set, indicates a Link training error occurred. This bit is cleared by hardware upon successful training of the link to the L0 link state. Reset to 0b
27	Link Training	RO	When set, indicates the link training is in progress. Hardware clears this bit once link training is complete. Reset to 0b.
28	Slot Clock Configuration	HwInt	Ob: the Switch uses an independent clock irrespective of the presence of a reference on the connector 1b: the Switch uses the same reference clock that the platform provides on the connector The default value may be changed by the status of strapped pin, SMBus, or auto-loading from EEPROM. Reset to 0b.
29	Data Link Layer Link Active	RO	Indicates the status of the Data Link Control and Management State Machine. It returns a 1b to indicate the DL_Active state, 0b otherwise. Reset to 0b.
31:30	Reserved	RO	Reset to 00b.

7.2.73 SLOT CAPABILITIES REGISTER (Downstream Port Only) – OFFSET F4h

BIT	FUNCTION	TYPE	DESCRIPTION
0	Attention Button Present	RO	When set, it indicates that an Attention Button is implemented on the chassis for this slot. The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 0b.
1	Power Controller Present	RO	When set, it indicates that a Power Controller is implemented for this slot. The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 0b.
2	Reserved	RO	Reset to 0b.
3	Attention Indicator Present	RO	When set, it indicates that an Attention Indicator is implemented on the chassis for this slot. The default value may be changed by SMBus or autoloading from EEPROM. Reset to 0b.
4	Power Indicator Present	RO	When set, it indicates that a Power Indicator is implemented on the chassis for this slot. The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 0b.
5	Hot-Plug Surprise	RO	When set, it indicates that a device present in this slot might be removed from the system without any prior notification. The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 0b.
6	Hot-Plug Capable	HwInt	When set, it indicates that this slot is capable of supporting Hot-Plug operation. The default value may be changed by the status of strapped pin or auto-loading from EEPROM.



BIT	FUNCTION	TYPE	DESCRIPTION
14:7	Slot Power Limit Value	RW	It applies to Downstream Port only. In combination with the Slot Power Limit Scale value, specifies the upper limit on power supplied by slot. Writes to this register also cause the Port to send the Set_Slot_Power_Limit message. The default value may be changed by SMBus or auto-loading from EEPROM.
			Reset to 00h.
16:15	Slot Power Limit Scale	RW	It applies to Downstream Port only. Specifies the scale used for the Slot Power Limit Value. Writes to this register also cause the Port to send the Set_Slot_Power_Limit message. The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 00b.
18:17	Reserved	RO	Reset to 00b.
31:19	Physical Slot Number	RO	It indicates the physical slot number attached to this Port. The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 0.

7.2.74 SLOT CONTROL REGISTER (Downstream Port Only) – OFFSET F8h

BIT	FUNCTION	TYPE	DESCRIPTION
0	Attention Button Pressed Enable	RW	When set, it enables the generation of Hot-Plug interrupt or wakeup event on an attention button pressed event. Reset to 0b.
1	Power Fault Detected Enable	RW	When set, it enables the generation of Hot-Plug interrupt or wakeup event on a power fault event. Reset to 0b.
2	Reserved	RO	Reset to 0b.
3	Presence Detect Changed Enable	RW	When set, it enables the generation of Hot-Plug interrupt or wakeup event on a presence detect changed event. Reset to 0b.
4	Command Completed Interrupt Enable	RW	When set, it enables the generation of Hot-Plug interrupt when the Hot-Plug Controller completes a command. Reset to 0b.
5	Hot-Plug Interrupt Enable	RW	When set, it enables generation of Hot-Plug interrupt on enabled Hot-Plug events. Reset to 0b.
7:6	Attention Indicator Control	RW	Controls the display of Attention Indicator. 00b: Reserved 01b: On 10b: Blink 11b: Off Writes to this register also cause the Port to send the ATTENTION_INDICATOR_* Messages. Reset to 11b.



BIT	FUNCTION	TYPE	DESCRIPTION
9:8	Power Indicator Control	RW	Controls the display of Power Indicator. 00b: Reserved 01b: On 10b: Blink 11b: Off Writes to this register also cause the Port to send the POWER_INDICATOR_* Messages. Reset to 11b.
10	Power Controller Control	RW	0b: reset the power state of the slot (Power On) 1b: set the power state of the slot (Power Off) Reset to 0b.
11	Reserved	RO	Reset to 0b.
12	Data Link Layer State Changed Enable	RW	If the Data Link Layer Link Active capability is implemented, when set to 1b, this field enables software notification when Data Link Layer Link Active field is changed. Reset to 0b.
15:13	Reserved	RO	Reset to 000b

7.2.75 SLOT STATUS REGISTER (Downstream Port Only) – OFFSET F8h

BIT	FUNCTION	TYPE	DESCRIPTION
16	Attention Button Pressed	RW1C	When set, it indicates the Attention Button is pressed. Reset to 0b.
17	Power Fault Detected	RW1C	When set, it indicates a Power Fault is detected. Reset to 0b.
18	MRL Sensor Changed	RO	When set, it indicates a MRL Sensor Changed is detected. Reset to 0b.
19	Presence Detect Changed	RW1C	When set, it indicates a Presence Detect Changed is detected. Reset to 0b.
20	Command Completed	RW1C	When set, it indicates the Hot-Plug Controller completes an issued command. Reset to 0b.
21	MRL Sensor State	RO	Reflects the status of MRL Sensor. 0b: MRL Closed 1b: MRL Opened Reset to 0b.
22	Presence Detect State	RO	Indicates the presence of a card in the slot. 0b: Slot Empty 1b: Card Present in slot This register is implemented on all Downstream Ports that implement slots. For Downstream Ports not connected to slots (where the Slot Implemented bit of the PCI Express Capabilities register is 0b), this bit returns 1b. Reset to 1b.
23	Reserved	RO	Reset to 0.
24	Data Link Layer State Changed	RW1C	This bit is set when the value reported in the Data Link Layer Link Active field of the Link Status register is changed.
31:25	Reserved	RO	Reset to 0

7.2.76 PCI EXPRESS ADVANCED ERROR REPORTING CAPABILITY ID REGISTER – OFFSET 100h

BIT	FUNCTION	TYPE	DESCRIPTION
15:0	Extended	RO	Read as 0001h to indicate that these are PCI express extended capability
13.0	Capabilities ID	KO	registers for advance error reporting.

7.2.77 CAPABILITY VERSION - OFFSET 100h

BIT	FUNCTION	TYPE	DESCRIPTION
19:16	Capability Version	RO	Read as 1h. Indicates PCI-SIG defined PCI Express capability structure version number.
			Reset to 1h.

7.2.78 NEXT ITEM POINTER REGISTER – OFFSET 100h

BIT	FUNCTION	TYPE	DESCRIPTION
31:20	Next Capability Offset	RO	Pointer points to the PCI Express Extended VC capability register (140h). Reset to 140h (upstream port). Reset to 20Ch (downstream port).

7.2.79 UNCORRECTABLE ERROR STATUS REGISTER – OFFSET 104h

BIT	FUNCTION	TYPE	DESCRIPTION
0	Training Error Status	RW1CS	When set, indicates that the Training Error event has occurred. Reset to 0b.
3:1	Reserved	RO	Reset to 000b.
4	Data Link Protocol Error Status	RW1CS	When set, indicates that the Data Link Protocol Error event has occurred. Reset to 0b.
11:5	Reserved	RO	Reset to 0.
12	Poisoned TLP Status	RW1CS	When set, indicates that a Poisoned TLP has been received or generated. Reset to 0b.
13	Flow Control Protocol Error Status	RW1CS	When set, indicates that the Flow Control Protocol Error event has occurred. Reset to 0b.
14	Completion Timeout Status	RW1CS	When set, indicates that the Completion Timeout event has occurred. Reset to 0b.
15	Completer Abort Status	RW1CS	When set, indicates that the Completer Abort event has occurred. Reset to 0b.
16	Unexpected Completion Status	RW1CS	When set, indicates that the Unexpected Completion event has occurred. Reset to 0b.
17	Receiver Overflow Status	RW1CS	When set, indicates that the Receiver Overflow event has occurred. Reset to 0b.
18	Malformed TLP Status	RW1CS	When set, indicates that a Malformed TLP has been received. Reset to 0b.



BIT	FUNCTION	TYPE	DESCRIPTION
19	ECRC Error Status	RW1CS	When set, indicates that an ECRC Error has been detected. Reset to 0b.
20	Unsupported Request Error Status	RW1CS	When set, indicates that an Unsupported Request event has occurred. Reset to 0b.
31:21	Reserved	RO	Reset to 0.

7.2.80 UNCORRECTABLE ERROR MASK REGISTER - OFFSET 108h

BIT	FUNCTION	TYPE	DESCRIPTION
0	Training Error Mask	RWS	When set, the Training Error event is not logged in the Header Log register and not issued as an Error Message to RC either.
			Reset to 0b.
3:1	Reserved	RO	Reset to 000b.
4	Data Link Protocol Error Mask	RWS	When set, the Data Link Protocol Error event is not logged in the Header Log register and not issued as an Error Message to RC either.
11.7	D 1	D.O.	Reset to 0b.
11:5	Reserved	RO	Reset to 0.
12	Poisoned TLP Mask	RWS	When set, an event of Poisoned TLP has been received or generated is not logged in the Header Log register and not issued as an Error Message to RC either.
			Reset to 0b.
13	Flow Control Protocol Error Mask	RWS	When set, the Flow Control Protocol Error event is not logged in the Header Log register and not issued as an Error Message to RC either.
			Reset to 0b.
14	Completion Timeout Mask	RWS	When set, the Completion Timeout event is not logged in the Header Log register and not issued as an Error Message to RC either.
	1.500		Reset to 0b.
15	Completer Abort Mask	RWS	When set, the Completer Abort event is not logged in the Header Log register and not issued as an Error Message to RC either.
			Reset to 0b.
16	Unexpected Completion Mask	RWS	When set, the Unexpected Completion event is not logged in the Header Log register and not issued as an Error Message to RC either.
	•		Reset to 0b.
17	Receiver Overflow Mask	RWS	When set, the Receiver Overflow event is not logged in the Header Log register and not issued as an Error Message to RC either.
			Reset to 0b.
18	Malformed TLP Mask	RWS	When set, an event of Malformed TLP has been received is not logged in the Header Log register and not issued as an Error Message to RC either.
			Reset to 0b.
19	ECRC Error Mask	RWS	When set, an event of ECRC Error has been detected is not logged in the Header Log register and not issued as an Error Message to RC either.
			Reset to 0b.
20	Unsupported Request Error Mask	RWS	When set, the Unsupported Request event is not logged in the Header Log register and not issued as an Error Message to RC either.
	<u> </u>		Reset to 0b.
31:21	Reserved	RO	Reset to 0.



7.2.81 UNCORRECTABLE ERROR SEVERITY REGISTER - OFFSET 10Ch

BIT	FUNCTION	TYPE	DESCRIPTION
0	Training Error Severity	RWS	0b: Non-Fatal 1b: Fatal
3:1	Reserved	RO	Reset to 1b. Reset to 000b.
J.1	Reserved	RO	0b: Non-Fatal
4	Data Link Protocol Error Severity	RWS	1b: Fatal
11.5	D 1	D.O.	Reset to 1b.
11:5	Reserved	RO	Reset to 0. 0b: Non-Fatal
12	Poisoned TLP Severity	RWS	1b: Fatal
	,		Reset to 0b.
13	Flow Control Protocol Error	RWS	0b: Non-Fatal 1b: Fatal
	Severity		Reset to 1b.
			0b: Non-Fatal
14	Completion Timeout Error Severity	RWS	lb: Fatal
			Reset to 0b.
15	Completer Abort Severity	RWS	0b: Non-Fatal 1b: Fatal
			Reset to 0b.
16	Unexpected Completion Severity	RWS	0b: Non-Fatal 1b: Fatal
			Reset to 0b.
17	Receiver Overflow Severity	RWS	0b: Non-Fatal 1b: Fatal
			Reset to 1b.
18	Malformed TLP Severity	RWS	0b: Non-Fatal 1b: Fatal
	-		Reset to 1b.
19	ECRC Error Severity	RWS	0b: Non-Fatal 1b: Fatal
			Reset to 0.
20	Unsupported Request Error Severity	RWS	0b: Non-Fatal 1b: Fatal
			Reset to 0b.
31:21	Reserved	RO	Reset to 0.

7.2.82 CORRECTABLE ERROR STATUS REGISTER - OFFSET 110 h

BIT	FUNCTION	TYPE	DESCRIPTION
			When set, the Receiver Error event is detected.
0	Receiver Error Status	RW1CS	
			Reset to 0b.
5:1	Reserved	RO	Reset to 00000b.
			When set, the event of Bad TLP has been received is detected.
6	Bad TLP Status	RW1CS	
			Reset to 0b.



BIT	FUNCTION	TYPE	DESCRIPTION
7	Bad DLLP Status	RW1CS	When set, the event of Bad DLLP has been received is detected. Reset to 0b.
8	REPLAY_NUM Rollover status	RW1CS	When set, the REPLAY_NUM Rollover event is detected. Reset to 0b.
11:9	Reserved	RO	Reset to 000b.
12	Replay Timer Timeout status	RW1CS	When set, the Replay Timer Timeout event is detected. Reset to 0b.
13	Advisory Non-Fatal Error status	RW1CS	When set, the Advisory Non-Fatal Error event is detected. Reset to 0b.
31:14	Reserved	RO	Reset to 0b.

7.2.83 CORRECTABLE ERROR MASK REGISTER - OFFSET 114 h

BIT	FUNCTION	TYPE	DESCRIPTION
0	Receiver Error Mask	RWS	When set, the Receiver Error event is not logged in the Header Log register and not issued as an Error Message to RC either. Reset to 0b.
5:1	Reserved	RO	Reset to 00000b.
6	Bad TLP Mask	RWS	When set, the event of Bad TLP has been received is not logged in the Header Log register and not issued as an Error Message to RC either. Reset to 0b.
7	Bad DLLP Mask	RWS	When set, the event of Bad DLLP has been received is not logged in the Header Log register and not issued as an Error Message to RC either. Reset to 0b.
8	REPLAY_NUM Rollover Mask	RWS	When set, the REPLAY_NUM Rollover event is not logged in the Header Log register and not issued as an Error Message to RC either. Reset to 0b.
11:9	Reserved	RO	Reset to 000b.
12	Replay Timer Timeout Mask	RWS	When set, the Replay Timer Timeout event is not logged in the Header Log register and not issued as an Error Message to RC either. Reset to 0b.
13	Advisory Non-Fatal Error Mask	RWS	When set, the Advisory Non-Fatal Error event is not logged in the Header Long register and not issued as an Error Message to RC either. Reset to 1b.
31:14	Reserved	RO	Reset to 0.

7.2.84 ADVANCE ERROR CAPABILITIES AND CONTROL REGISTER – OFFSET 118h

BIT	FUNCTION	TYPE	DESCRIPTION
4:0	First Error Pointer	ROS	It indicates the bit position of the first error reported in the Uncorrectable Error Status register. Reset to 00000b.
5	ECRC Generation Capable	RO	When set, it indicates the Switch has the capability to generate ECRC. Reset to 1b.



BIT	FUNCTION	TYPE	DESCRIPTION
6	ECRC Generation Enable	RWS	When set, it enables the generation of ECRC when needed. Reset to 0b.
7	ECRC Check Capable	RO	When set, it indicates the Switch has the capability to check ECRC. Reset to 1b.
8	ECRC Check Enable	RWS	When set, the function of checking ECRC is enabled. Reset to 0b.
31:9	Reserved	RO	Reset to 0.

7.2.85 HEADER LOG REGISTER – OFFSET From 11Ch to 128h

BIT	FUNCTION	TYPE	DESCRIPTION
31:0	1 st DWORD	ROS	Hold the 1st DWORD of TLP Header. The Head byte is in big endian.
63:32	2 nd DWORD	ROS	Hold the 2nd DWORD of TLP Header. The Head byte is in big endian.
95:64	3 rd DWORD	ROS	Hold the 3rd DWORD of TLP Header. The Head byte is in big endian.
127:96	4 th DWORD	ROS	Hold the 4th DWORD of TLP Header. The Head byte is in big endian.

7.2.86 PCI EXPRESS VIRTUAL CHANNEL CAPABILITY ID REGISTER – OFFSET 140h (Upstream Only)

BIT	FUNCTION	TYPE	DESCRIPTION
15:0	Extended Capabilities ID	RO	Read as 0002h to indicate that these are PCI express extended capability registers for virtual channel.

7.2.87 CAPABILITY VERSION – OFFSET 140h (Upstream Only)

BIT	FUNCTION	TYPE	DESCRIPTION
			Read as 1h. Indicates PCIe Base Specification compliance.
19:16	Capability Version	RO	
			Reset to 1h.

7.2.88 NEXT ITEM POINTER REGISTER – OFFSET 140h (Upstream Only)

BIT	FUNCTION	TYPE	DESCRIPTION			
31:20	Next Capability Offset	RO	Pointer points to the PCI Express Power Budgeting Capability register (20Ch).			
			Reset to 20Ch.			

7.2.89 PORT VC CAPABILITY REGISTER 1 – OFFSET 144h (Upstream Only)

BIT	FUNCTION	TYPE	DESCRIPTION
2:0	Extended VC Count	RO	It indicates the number of extended Virtual Channels in addition to the default VC supported by the Switch. Reset to 000b.
3	Reserved	RO	Reset to 0b.



BIT	FUNCTION	TYPE	DESCRIPTION			
6:4	Low Priority Extended VC Count	RO	It indicates the number of extended Virtual Channels in addition to the default VC belonging to the low-priority VC (LPVC) group. The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 000b.			
7	Reserved	RO Reset to 0b.				
9:8	Reference Clock	RO	It indicates the reference clock for Virtual Channels that support time-based WRR Port Arbitration. Defined encoding is 00b for 100 ns reference clock. Reset to 00b.			
11:10	Port Arbitration Table Entry Size	Read as 10b to indicate the size of Port Arbitration table entry in the devic 4 bits. Reset to 10b.				
31:12	Reserved	RO				

7.2.90 PORT VC CAPABILITY REGISTER 2 – OFFSET 148h (Upstream Only)

BIT	FUNCTION	TYPE	DESCRIPTION
7:0	VC Arbitration Capability	RO	It indicates the types of VC Arbitration supported by the device for the LPVC group. This field is valid when LPVC is greater than 0. The Switch supports Hardware fixed arbitration scheme, e.g., Round Robin and Weight Round Robin arbitration with 32 phases in LPVC. Reset to 000000000b.
23:8	Reserved	RO	Reset to 0.
31:24	VC Arbitration Table Offset	RO	It indicates the location of the VC Arbitration Table as an offset from the base address of the Virtual Channel Capability register in the unit of DQWD (16 bytes). Reset to 00h.

7.2.91 PORT VC CONTROL REGISTER – OFFSET 14Ch (Upstream Only)

BIT	FUNCTION	TYPE	DESCRIPTION			
0	Load VC Arbitration Table	RW	When set, the programmed VC Arbitration Table is applied to the hardware. This bit always returns 0b when read. Reset to 0b.			
3:1	VC Arbitration Select	RW	This field is used to configure the VC Arbitration by selecting one of the supported VC Arbitration schemes. The valid values for the schemes supported by Switch are 0b and 1b. Other value than these written into this register will be treated as default. Reset to 0b.			
15:4	Reserved	RO	Reset to 0.			

7.2.92 PORT VC STATUS REGISTER – OFFSET 14Ch (Upstream Only)

BIT	FUNCTION	TYPE	DESCRIPTION			
16	VC Arbitration Table Status	RO	When set, it indicates that any entry of the VC Arbitration Table is written by software. This bit is cleared when hardware finishes loading values stored in the VC Arbitration Table after the bit of "Load VC Arbitration Table" is set. Reset to 0b.			
31:17	Reserved	RO	Reset to 0.			

7.2.93 VC RESOURCE CAPABILITY REGISTER (0) – OFFSET 150h (Upstream Only)

BIT	FUNCTION	TYPE	DESCRIPTION			
7:0	Port Arbitration Capability	RO	It indicates the types of Port Arbitration supported by the VC resource. The Switch supports Hardware fixed arbitration scheme, e.g., Round Robin, Weight Round Robin (WRR) arbitration with 128 phases (3~4 enabled ports) and Time-based WRR with 128 phases (3~4 enabled ports). Reset to 00001001b.			
13:8	Reserved	RO	Reset to 000000b.			
14	Advanced Packet Switching	RO	When set, it indicates the VC resource only supports transaction optimized for Advanced Packet Switching (AS). Reset to 0b.			
15	Reject Snoop Transactions	RO	This bit is not applied to PCIe Switch. Reset to 0b.			
22:16	Maximum Time Slots	RO	It indicates the maximum numbers of time slots (minus one) are allocated for Isochronous traffic. The default value may be changed by SMBus or autoloading from EEPROM. Reset to 7Fh.			
23	Reserved	RO	Reset to 0b.			
31:24	Port Arbitration Table Offset	RO	It indicates the location of the Port Arbitration Table (n) as an offset from the base address of the Virtual Channel Capability register in the unit of DQWD (16 bytes). Reset to 04h for Port Arbitration Table (0).			

7.2.94 VC RESOURCE CONTROL REGISTER (0) – OFFSET 154h (Upstream Only)

BIT	FUNCTION	TYPE	DESCRIPTION			
7:0	TC/VC Map	RW	This field indicates the TCs that are mapped to the VC resource. Bit locations within this field correspond to TC values. When the bits in this field are set, it means that the corresponding TCs are mapped to the VC resource. The default value may be changed by SMBus or auto-loading from EEPROM. Reset to FFh.			
15:8	Reserved	RO	Reset to 00h.			
16	Load Port Arbitration Table	RW	When set, the programmed Port Arbitration Table is applied to the hardware. This bit always returns 0b when read. Reset to 0b.			
19:17	Port Arbitration Select	RW This field is used to configure the Port Arbitration by selecting one of the supported Port Arbitration schemes. The permissible values for the schemes supported by Switch are 000b and 011b at VCO, other value than these written into this register will be treated as default. Reset to 000b.				
23:20	Reserved	RO	Reset to 0h.			
26:24	VC ID	RO	This field assigns a VC ID to the VC resource. Reset to 000b.			
30:27	Reserved	RO	Reset to 0h.			
31	VC Enable	RW	Ob: it disables this Virtual Channel 1b: it enables this Virtual Channel Reset to 1b.			



7.2.95 VC RESOURCE STATUS REGISTER (0) – OFFSET 158h (Upstream Only)

BIT	FUNCTION	TYPE	DESCRIPTION			
15:0	Reserved	RO	Reset to 0000h.			
16	Port Arbitration Table Status	RO	When set, it indicates that any entry of the Port Arbitration Table is written by software. This bit is cleared when hardware finishes loading values stored in the Port Arbitration Table after the bit of "Load Port Arbitration Table" is set. Reset to 0b.			
17	VC Negotiation Pending	RO	When set, it indicates that the VC resource is still in the process of negotiation. This bit is cleared after the VC negotiation is complete. Reset to 0b.			
31:18	Reserved	RO	Reset to 0.			

7.2.96 PORT ARBITRATION TABLE REGISTER (0) – OFFSET 180h-1BCh (Upstream Only)

The Port arbitration table is a read-write register array that contains a table for Port arbitration. Each table entry allocates two bits to represent Port Number. The table entry size is dependent on the number of enabled ports (refer to bit 10 and 11 of Port VC capability register 1). The arbitration table contains 128 entries if three or four ports are to be enabled. The following table shows the register array layout for the size of entry equal to two.

Table 7-1 Table Entry Size in 4 Bits

63 - 56	55 - 48	47 - 40	39 - 32	31 - 24	23 - 16	15 - 8	7 - 0	Byte Location
Phase	00h							
[15:14]	[13:12]	[11:10]	[9:8]	[7:6]	[5:4]	[3:2]	[1:0]	0011
Phase	08h							
[31:30]	[29:28]	[27:26]	[25:24]	[23:22]	[21:20]	[19:18]	[17:16]	Uoli
Phase	10h							
[47:46]	[45:44]	[43:42]	[41:40]	[39:38]	[37:36]	[35:34]	[33:32]	1011
Phase	18h							
[63:62]	[61:60]	[59:58]	[57:56]	[55:54]	[53:52]	[51:50]	[49:48]	1011
Phase	20h							
[79:78]	[77:76]	[75:74]	[73:72]	[71:70]	[69:68]	[67:66]	[65:64]	2011
Phase	28h							
[95:94]	[93:92]	[91:90]	[89:88]	[87:86]	[85:84]	[83:82]	[81:80]	2011
Phase	30h							
[111:110]	[109:108]	[107:106]	[105:104]	[103:102]	[101:100]	[99:98]	[97:96]	3011
Phase	38h							
[127:126]	[125:124]	[123:122]	[121:120]	[119:118]	[117:116]	[115:114]	[113:112]	3611

7.2.97 PCI EXPRESS POWER BUDGETING CAPABILITY ID REGISTER – OFFSET 20Ch

BIT	FUNCTION	TYPE DESCRIPTION	
15:0	Extended	RO	Read as 0004h to indicate that these are PCI express extended capability
13.0	Capabilities ID	KO	registers for power budgeting.

7.2.98 CAPABILITY VERSION - OFFSET 20Ch

BIT FUNCTION TYPE DESCRIPTION			
	BIT	FUNCTION	DESCRIPTION



BIT	FUNCTION	TYPE	DESCRIPTION	
			Read as 1h. Indicates PCIe Base Specification compliance.	
19:16	Capability Version	RO		
			Reset to 1h.	

7.2.99 NEXT ITEM POINTER REGISTER - OFFSET 20Ch

BIT	FUNCTION	TYPE	DESCRIPTION
31:20	Next Capability	RO	Read as 000h. No other ECP registers.
	Offset		Reset to 000h.

7.2.100 DATA SELECT REGISTER - OFFSET 210h

BIT	FUNCTION	TYPE	DESCRIPTION
7:0	Data Selection	RW	It indexes the power budgeting data reported through the data register. When 00h, it selects D0 Max power budget When 01h, it selects D0 Sustained power budget Other values would return zero power budgets, which means not supported Reset to 00h.
31:8	Reserved	RO	Reset to 000000h.

7.2.101 POWER BUDGETING DATA REGISTER - OFFSET 214h

BIT	FUNCTION	TYPE	DESCRIPTION
7:0	Base Power	RO	It specifies the base power value in watts. This value represents the required power budget in the given operation condition. The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 04h.
9:8	Data Scale	RO	It specifies the scale to apply to the base power value. The default value may be changed by auto-loading from EEPROM. Reset to 00b.
12:10	PM Sub State	RO	It specifies the power management sub state of the given operation condition. It is initialized to the default sub state. Reset to 000b.
14:13	PM State	RO	It specifies the power management state of the given operation condition. It defaults to the D0 power state. The default value may be changed by autoloading from EEPROM. Reset to 00b.
17:15	Туре	RO	It specifies the type of the given operation condition. It defaults to the Maximum power state. The default value may be changed by auto-loading from EEPROM. Reset to 111b.
20:18	Power Rail	RO	It specifies the power rail of the given operation condition. Reset to 010b.
31:21	Reserved	RO	Reset to 0.



7.2.102 POWER BUDGET CAPABILITY REGISTER - OFFSET 218h

BIT	FUNCTION	TYPE	DESCRIPTION
0	System Allocated	RO	When set, it indicates that the power budget for the device is included within the system power budget. The default value may be changed by auto-loading from EEPROM. Reset to 0b.
31:1	Reserved	RO	Reset to 0.



8 CLOCK SCHEME

The PI7C9X20303UL requires 100MHz differential clock inputs through REFCLKP and REFCLKN Pins as shown in the following table.

Table 8-1 Input Clock Requirements

Symbol	Description		Min	Typical	Max.	Unit
ClkIn _{FREQ}	Reference input clock range	-	100	-	MHz	
ClkIn _{DC}	Duty cycle of input clock	40	50	60	%	
T_R, T_F	Rise/Fall time of input clock	-	-	0.2	RCUI ^a	
V_{SW}	Differential input voltage swing	(peak-to-peak)	800	-	2000	mV
		(zero-to-peak)	400	-	1000	mV

a. RCUI (Reference Clock Unit Interval) refers to the reference clock period



9 IEEE 1149.1 COMPATIBLE JTAG CONTROLLER

An IEEE 1149.1 compatible Test Access Port (TAP) controller and associated TAP pins are provided to support boundary scan in PI7C9X20303UL for board-level continuity test and diagnostics. The TAP pins assigned are TCK, TDI, TDO, TMS and TRST L. All digital input, output, input/output pins are tested except TAP pins.

9.1 INSTRUCTION REGISTER

The IEEE 1149.1 Test Logic consists of a TAP controller, an instruction register, and a group of test data registers including Bypass and Boundary Scan registers. The TAP controller is a synchronous 16-state machine driven by the Test Clock (TCK) and the Test Mode Select (TMS) pins. An independent power on reset circuit is provided to ensure the machine is in TEST LOGIC RESET state at power-up.

PI7C9X20303UL implements a 5-bit Instruction register to control the operation of the JTAG logic. The defined instruction codes are shown in Table 10-1. Those bit combinations that are not listed are equivalent to the BYPASS (11111) instruction:

Table 9-1 Instruction register codes

Instruction	Operation Code (binary)	Register Selected	Operation
EXTEST	00000	Boundary Scan	Drives / receives off-chip test data
SAMPLE	00001	Boundary Scan	Samples inputs / pre-loads outputs
HIGHZ	00101	Bypass	Tri-states output and I/O pins except TDO pin
CLAMP	00100	Bypass	Drives pins from boundary-scan register and selects Bypass register for shifts
IDCODE	01100	Device ID	Accesses the Device ID register, to read manufacturer ID, part number, and version number
BYPASS	11111	Bypass	Selected Bypass Register
INT_SCAN	00010	Internal Scan	Scan test
MEM_BIST	01010	Memory BIST	Memory BIST test

9.2 BYPASS REGISTER

The required bypass register (one-bit shift register) provides the shortest path between TDI and TDO when a bypass instruction is in effect. This allows rapid movement of test data to and from other components on the board. This path can be selected when no test operation is being performed on the PI7C9X20303UL.

9.3 DEVICE ID REGISTER

This register identifies Pericom as the manufacturer of the device and details the part number and revision number for the device.

Table 9-2 JTAG device ID register

Bit	Type	Value	Description
31-28	RO	0001	Version number
27-12	RO	1001001000000100	Last 4 digits (hex) of the die part number
11-1	RO	01000111111	Pericom identifier assigned by JEDEC
0	RO	1	Fixed bit equal to 1'b1



9.4 BOUNDARY SCAN REGISTER

The boundary scan register has a set of serial shift-register cells. A chain of boundary scan cells is formed by connected the internal signal of the PI7C9X20303UL package pins. The VDD, VSS, and JTAG pins are not in the boundary scan chain. The input to the shift register is TDI and the output from the shift register is TDO. There are 4 different types of boundary scan cells, based on the function of each signal pin.

The boundary scan register cells are dedicated logic and do not have any system function. Data may be loaded into the boundary scan register master cells from the device input pins and output pin-drivers in parallel by the mandatory SAMPLE and EXTEST instructions. Parallel loading takes place on the rising edge of TCK.

9.5 JTAG BOUNDARY SCAN REGISTER ORDER

Table 9-3 JTAG boundary scan register definition

Boundary Scan Register Number	Pin Name	Pin No	Type	Tri-state Control Cell
0	NC	B4	Input	4
1	PRSNT[2]	A5	Bidir	4
2	NC	B5	Bidir	4
3	TEST5	A7	Bidir	4
4			Control	
5	TEST4	В6	Bidir	4
6	TEST3	A8	Bidir	4
7	SMBCLK	B7	Bidir	4
8	SMBDATA	B8	Bidir	4
9	PWR SAV	A10	Bidir	4
10	DEQ[3]	В9	Bidir	4
11	GPIO[0]	B10	Bidir	12
12			Control	
13	GPIO[1]	A12	Bidir	14
14			Control	
15	GPIO[2]	A13	Bidir	16
16			Control	
17	GPIO[3]	B11	Bidir	18
18			Control	
19	GPIO[4]	A14	Bidir	20
20			Control	
21	GPIO[5]	B12	Bidir	22
22			Control	
23	GPIO[6]	A15	Bidir	24
24			Control	
25	GPIO[7]	B13	Bidir	26
26	F 3		Control	
27	TEST1	A17	Bidir	4
28	HIDRV	B15	Bidir	4
29	LOWDRV	A18	Bidir	4
30	DTX[3]	B18	Bidir	4
31	EECLK	A23	Output2	
32	EEPD	B19	Bidir	33
33			Control	
34	PERST L	A25	Input	
35	PWR_IND[1]		Output2	
36	PWR_IND[3]		Output2	
37	PORTERR[0]	A26	Output2	
38	ATT_IND[1]		Output2	
39	ATT_IND[3]		Output2	



Boundary Scan				Datasneet
Register Number	Pin Name	Pin No	Type	Tri-state Control Cell
40	PORTERR [1]	A27	Output2	
41	ATT_BTN[1]		Input	
42	ATT_BTN[3]		Input	
43	PORTERR [2]	B24	Output2	
44	PRSNT[1]		Input	
45	PRSNT[3]		Input	
46	PWR_ENA[1]		Output2	
47	PWR_ENA[3]		Output2	
48	PWR_FLT[1]		Input	
49	PWR_FLT[3]		Input	
50	NC	A30	Output2	
51	TEST2	A38	Input	
52	DWNRST_L[1]	A52	Output2	
53	DWNRST_L[2]	B44	Output2	
54	NC	B46	Output2	
55	PWR_IND[2]		Output2	
56	TEST6	A70	Bidir	4
57	ATT IND[2]		Output2	
58	ATT RTN[2]		Input	
59	SLOTCLK	B59	Bidir	4
60	PRSNT[2]		Input	
61	PWR_ENA[2]		Output2	
62	PWR_FLT[2]		Input	
63	PRSNT[1]	A71	Bidir	4





10 POWER MANAGEMENT

The PI7C9X20303UL supports D0, D1, D2, D3-hot, and D3-cold Power States. The PCI Express Physical Link Layer of the PI7C9X20303UL device supports the PCI Express Link Power Management with L0, L0s, L1, L2/L3 ready and L3 Power States.

During the transition from D3-hot to D3-cold state, the main power supplies of VDDC and VDDR are turned off to save power while keeping the VDDAUX and VAUX with the auxiliary power supplies to maintain all necessary information to be restored to the full power D0 state. PI7C9X20303UL has been designed to have sticky registers that are powered by auxiliary power supplies. PI7C9X20303UL forwards power management messages to the upstream Switches or root complex.

PI7C9X20303UL also supports ASPM (Active State Power Management) to facilitate the link power saving.



11 ELECTRICAL AND TIMING SPECIFICATIONS

11.1 ABSOLUTE MAXIMUM RATINGS

Table 11-1 Absolute maximum ratings

(Above which the useful life may be impaired. For user guidelines, not tested.)

Storage Temperature	-65°C to 150°C
Ambient Temperature with power applied	-40°C to 85°C
PCI Express supply voltage to ground potential (VDDA, VDDC, and	-0.3v to 3.0v
VDDAUX)	
DC input voltage for PCI Express signals	-0.3v to 3.0v

Note:

Stresses greater than those listed under MAXIMUM RATINGS may cause permanent damage to the device. This is a stress rating only and functional operation of the device at these or any conditions above those indicated in the operational sections of this specification is not implied. Exposure to absolute maximum rating conditions for extended periods of time may affect reliability.

11.2 POWER CONSUMPTION

Table 11-2 PI7C9X303UL power dissipation

Mode	Power Saving	Typical Power Dissipation (Watts)
L0 Normal Mode	Enabled	0.30
	Disabled	0.40
L1 Standby Mode	Enabled	0.15
	Disabled	0.30

11.3 DC SPECIFICATIONS

Table 11-3 DC electrical characteristics

Power Pins	Min.	Тур.	Max.
VDDA	0.9v	1.0v	1.1v
VDDR	3.0v	3.3v	3.6v
VDDC	0.9v	1.0v	1.1v
VAUX	3.0v	3.3v	3.6v
VDDAUX	0.9v	1.0v	1.1v
VTT	VDDC	1.5v	1.8v

VDDA: analog power supply for PCI Express Interface VDDR: digital power supply for 3.3v I/O Interface

VDDC: digital power supply for the core

VAUX: digital auxiliary power supply for 3.3v I/O Interface VDDAUX: digital auxiliary power supply for the core

VTT: transmit termination power supply for PCI Express Interface

In order to support auxiliary power management fully, it is recommended to have VDDC and VDDAUX separated.



11.4 AC SPECIFICATIONS

Table 11-4 Transmitter Characteristics

Symbol	Description	Min	Typical	Max.	Unit
Voltage Para	meters				
V _{TX-DIFF} ^a	Output voltage compliance @ typical swing				
	V _{TX-DIFFp} (peak-to-peak, single ended)	400	500	600	mV
	V _{TX-DIFFpp} (peak-to-peak, differential)	800	1000	1200	mV
V_{SW}	Supported TX output voltage range (pp,	400 ^b		1500°	mV
	differential)				
V_{OL}	Low-level output voltage		V_{TT} - 1.5 * $V_{TX\text{-DIFFp}}$		V
V_{OH}	High-level output voltage		V_{TT} - $0.5V_{TX\text{-DIFFp}}$		V
V _{TX-CM-AC}	Transmit common-mode voltage in L0	0.50	V _{TT} - V _{TX-DIFFp}	1.45	V
V _{TX-CM-HiZ}	Transmit common-mode voltage in L0s		V _{TX-CM-AC}		V
	(TX) & L1				
V _{TX-DE-RATIO}	De-emphasized differential output voltage	0		-7.96	dB
V _{TX-IDLE-DIFFp}	Electric Idle differential peak voltage			20	mV
V _{TX-RCV-}	Voltage change during Receive Detection		$V_{TX\text{-DIFF}p}$		mV
DETECT			•		
RL _{TX-DIFF}	Transmitter Differential Return loss	10			dB
RL _{TX-CM}	Transmitter Common Mode Return loss	6			dB
Zose	Single-ended output impedance	40	50	60	Ω
Z _{TX-DIFF-DC}	DC Differential TX Impedance	80	100	120	Ω
T _{TX-RISE, TTX-}	Rise / Fall time of TxP, TxN outputs	80		110 ^d	ps
FALL					•
Jitter Parame	eters				
UI	Unit Interval	399.88	400	400.12	ps
T _{TX-MAX-JITTER}	Transmitter total jitter (peak-to-peak)			0.25 ^e	UI
T _{TX-EYE}	Minimum TX Eye Width (1 - T _{TX-MAX} -	0.75			UI
	JITTER)				
T _{TX-EYE-}	Maximum time between the jitter median			0.125	UI
MEDIAN-to-	and				
MAX-JITTER	maximum deviation from the median				
Timing Parar	neters				
L _{TLAT-10}	Transmitter data latency (for n=10)	9		11	UI
L _{TLAT-20}	Transmitter data latency (for n=20)	9		11	UI
L _{TX-SKEW}	Transmitter data skew between any 2 lanes	0		2 +	UI
	_			200ps	
T _{TX-IDLE-SET-}	Maximum time to transition to a valid		4	6	ns
TO-IDLE	electrical idle after sending an Electrical				
	Idle ordered set				
T _{EIExit}	Time to exit Electrical Idle (L0s) state into		12	16	ns
	L0				
$T_{RxDetectEn}$	Pulse width of RxDetectEn input	9.8	10	10.2	us
$T_{RxDetect}$	RxDetectEn falling edge to RxDetect		1	2	ns
	delay				

a. Measured with Vtt = 1.2V, HiDrv='0', LowDrv='0' and Dtx='0000'.
b. Minimum swing assumes LoDrv = 1, HiDrv = 0 and Dtx = 1100
c. Max swing assumes LoDrv = 0, HiDrv = 1, Dtx = 0010, VTT = 1.8V

d. As measured between 20% and 80% points. Will depend on package characteristics.

e. Measured using PCI Express Compliance Pattern

Table 11-5 Receiver Characteristics

Symbol	Description	Min	Typical	Max.	Unit
Voltage Param	eters				
V _{RX-DIFFp-p}	Differential input voltage (peak-to-peak)	170		1200	mV
V _{RX-IDLE-DET-}	Differential input threshold voltage (peak-	65		175	mV
DIFFp-p	to-peak) to assert TxIdleDetect output				
V _{RX-CM-AC}	Receiver common-mode voltage for AC-		0	150	mV
	coupling				
T _{RX-RISE, TRX-}	Rise time / Fall time of RxP, RxN inputs			160	Ps
FALL					
Z _{RX-DIFF-DC}	Differential input impedance (DC)	80	100	120	Ω
Z _{RX-COM-DC}	Single-ended input impedance	40	50	60	Ω
Z _{RX-COM-INITIAL-}	Initial input common mode impedance	5	50	60	Ω
DC	(DC)				
Z _{RX-COM-HIGH-}	Powered down input common mode	200k			Ω
IMP-DC	impedance (DC)				
RL _{RX-DIFF}	Receiver Differential Return Loss ^a	10			dB
RL _{RX-CM}	Receiver Common Mode Return Loss ^b	6			dB
Jitter Paramete	ers				
T _{RX-MAX-JITTER}	Receiver total jitter tolerance			0.65	UI
T _{RX-EYE}	Minimum Receiver Eye Width	0.35			UI
T _{RX-EYE-MEDIAN-}	Maximum time between jitter median and			0.325	UI
to-MAX-JITTER	max deviation from median				
Timing Parame	eters				
LRLAT-10	Receiver data latency for n=10	28		29	bits
LRLAT-20	Receiver data latency for n=20	49		60	bits
TRX-SKEW	Receiver data skew between any 2 lanes	0		1°	bits
TRX-	Delay from detection of Electrical Idle	İ	10	20	ns
IDLE_ENTER	condition on the channel to assertion of				
_	TxIdleDetect output				
TRX-	Delay from detection of L0s to L0		5	10	ns
IDLE_EXIT	transition to deassertion of TxIdleDetect				
	output				

a. Over a frequency range of 50 MHz to 1.25 GHz.


b. Over a frequency range of 50 MHz to 1.25 GHz.
c. Assuming synchronized bit streams at the respective receiver inputs.



12 PACKAGE INFORMATION

The package of PI7C9X20303UL is a 10mm x 10mm TQFN (132 Pin) package. The following are the package information and mechanical dimension:


Figure 12-1 Package outline drawing



- ALL DIMENSIONS ARE IN MILLIMETERS 'IN DEGREES
 BILATERAL COPLANARITY ZONE APPLIES TO THE EXPOSED HEAT SINK SLUG AS WELL AS THE TERMINALS.
- 3. REFER JEDEC: MO-267
- RECOMMENDED LAND PATTERN IS FOR REFERENCE ONLY.
 THERMAL PAD SOLDERING AREA



Figure 12-2 Package bottom view





13 ORDERING INFORMATION

Part Number	Temperature Range	Package	Pb-Free & Green
PI7C9X20303UL□ZPEX	-40° to 85°C	132-pin TQFN	Yes
11/0/120303020202121	(Industrial Temperature)	10mm x 10mm	

