B36J3RGB-F6C0001HOU1930




Features

- •Package: RGB 3 in 1 package/4pin Polarity
- •Anti-Reflection resin
- •View angle : >=120° (min 50% brightness)
- •Component solder able surface finish is gold
- •High contrast

Main Applications

- Indoor display
- •Full color display
- •Fine pitch application



Top Mount RGB Chip LED B36J3RGB-F6C0001HOU1930

| DISCLAIMER |
|--|
| PRODUCT SPECIFICATIONS |
| ATTENTION: ELECTROSTATIC DISCHARGE (ESD) PROTECTION |
| LABEL SPECIFICATIONS |
| SPECIFICATIONS RANGE |
| PRODUCT FEATURES |
| ELECTRO-OPTICAL CHARACTERISTICS8 |
| PACKAGE OUTLINE DIMENSION AND RECOMMENDED SOLDERING PATTERN FOR REFLOW |
| SOLDERING |
| ABSOLUTE MAXIMUM RATINGS |
| CHARACTERISTICS OF B36J3RGB-F69 |
| PRECAUTION FOR USE |
| PACKAGING 11 |
| TAPE DIMENSION |
| REEL DIMENSION12 |
| Packing12 |
| DRY PACK |
| BAKING |
| PRECAUTIONS |
| REFLOW SOLDERING |
| Reworking15 |
| CLEANING15 |
| REVISE HISTORY16 |

| Official Product | HT Part No. B36J3RGB-F6C0001HOU1930 | Customer Pa | art No. | Data Sheet No. |
|-------------------|--|-------------|-------------|----------------|
| Tentative Product | ***** | ********** | ** | |
| | t to changes for improvement without advance , drawings, company confidential all rights | 27/01/2022 | Version 1.1 | Page 2/16 |

DISCLAIMER

HARVATEK reserves the right to make changes without further notice to any products herein to improve reliability, function or design. HARVATEK does not assume any liability arising out of the application or use of any product or circuit described herein; neither does it convey any license under its patent rights, nor the rights of others.

LIFE SUPPORT POLICY

HARVATEK's products are not authorized for use as critical components in life support devices or systems without the express written approval of the President of HARVATEK or HARVATEK INTERNATIONAL. As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury of the user.

2. A critical component in any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

| Official Product | HT Part No. B36J3RGB-F6C0001HOU1930 | Customer Pa | art No. | Data Sheet No. |
|-------------------|--|-------------|-------------|----------------|
| Tentative Product | ***** | ********* | ** | |
| | t to changes for improvement without advance , drawings, company confidential all rights | 27/01/2022 | Version 1.1 | Page 3/16 |

Top Mount RGB Chip LED B36J3RGB-F6C0001HOU1930

Product Specifications

| | Specification | Material | Quantity |
|---------------|--|-----------------------------------|------------------|
| Luminous | Red : 32 mcd typical | | |
| Intensity(Iv) | Green : 46 mcd typical | | |
| | Blue : 8 mcd typical | | |
| | R@5mA;G/B@2mA/ Ts= 25 ⁰ C; Tolerance ±10% | | |
| Wavelength | Red : 621 nm typical | | |
| | Green: 530 nm typical | | |
| | Blue : 470 nm typical | | |
| | R@5mA;G/B@2mA/ Ts= 25 ⁰ C;Tolerance ± 0.5nm | | |
| Vf | Red : 2.4 V maximum | | |
| | Green:3.1 V maximum | | |
| | Blue : 3.1 V maximum | | |
| | R@5mA;G/B@2mA/ Ts= 25° C;Tolerance ± 0.05V | | |
| Ir | < =1 µA @ V _R = 5 V | | |
| Resin | Dark | Ероху | |
| Carrier tape | EIA 481-1A specs | Conductive black tape | 24000pcs/reel |
| Reel | EIA 481-1A specs | Conductive black | |
| Label | HT standard | Paper | |
| Packing bag | 250x230mm | Aluminum laminated bag/ no-zipper | One reel per bag |
| Carton | HT standard | Paper | Non-specified |

| Official Product | HT Part No. B36J3RGB-F6C0001HOU1930 | Customer Pa | art No. | Data Sheet No. |
|-------------------|---|-------------|-------------|----------------|
| Tentative Product | ****** | ********* | ** | |
| | t to changes for improvement without advance , drawings, company confidential all rights | 27/01/2022 | Version 1.1 | Page 4/16 |

Top Mount RGB Chip LED B36J3RGB-F6C0001HOU1930

Others:

Each immediate box consists of 28 reels. The 28 reels may not necessarily have the same lot number or the same bin

combinations of Iv, λ_D and Vf. Each reel has a label identifying its specification; the immediate box consists of a product label as well.

Note : This is shipped test conditions

%Remarks: This product should be operated in forward bias. If a reverse voltage is continuously applied to the product, such operation can cause migration resulting in LED damage.


ATTENTION: Electrostatic Discharge (ESD) protection



The symbol to the left denotes that ESD precaution is needed. ESD protection for GaP and AlGaAs based chips is necessary even though they are relatively safe in the presence of low static-electric discharge. Parts built with AlInGaP, GaN, or/and InGaN based chips are **STATIC SENSITIVE devices**. ESD precaution must be


taken during design and assembly.

If manual work or processing is needed, please ensure the device is adequately protected from ESD during the process.



| Official Product | HT Part No. B36J3RGB-F6C0001HOU1930 | Customer Pa | art No. | Data Sheet No. |
|-------------------|---|-------------|-------------|----------------|
| Tentative Product | ***** | ********* | | |
| | t to changes for improvement without advance , drawings, company confidential all rights | 27/01/2022 | Version 1.1 | Page 5/16 |

Harvatek P/N:



■ Lot No.

| 1 | 2 | 3 | 4 | 5 | 6 | 7 | 8 | 9 | 10 |
|-------------|------------|-------------------|--|---|------------|---------------|---|--------------|---------|
| 1 | 7 | Ν | Е | 4 | 1 | L | Ν | 1 | 1 |
| Cod | e 1 2 | Code 3 | Code 4 | Code 5 | Code 6 | Code 6 Code 7 | | Code 9 | Code 10 |
| | | | Mfg.Year | Mfg.Month | Consecutiv | ve number | | Special code | 5 |
| Internal Tr | acing Code | Mixing Lot No. | 2010-A 2011-B 2012-C 2013-D 2014-E | 1:Jan 2:Feb A:Oct B:Nov C:Dec | 01 | ~ZZ | | 000~ZZZ | |

| Official Product | HT Part No. B36J3RGB-F6C0001HOU1930 | Customer Pa | art No. | Data Sheet No. |
|-------------------|---|-------------|-------------|----------------|
| Tentative Product | ***** | ********* | ** | |
| | t to changes for improvement without advance , drawings, company confidential all rights | 27/01/2022 | Version 1.1 | Page 6/16 |

Specifications Range

Luminous Intensity (Iv) Bin:

Luminous Intensity (Iv) Bin: R@5mA;G/B @2mA

| | B36J3RGB Series | | | | | | | | | | | |
|----------------|-----------------|------|-----|------|------|-----|------|------|--|--|--|--|
| IV | | | | | | | | | | | | |
| Red Green Blue | | | | | | | | | | | | |
| HF3 | 21.3 | 26.7 | HG3 | 30 | 37.5 | HB3 | 5.4 | 6.8 | | | | |
| HG1 | 24 | 30 | HH1 | 33.5 | 42 | HC1 | 6 | 7.5 | | | | |
| HG2 | 26.7 | 33.5 | HH2 | 37.5 | 47 | HC2 | 6.8 | 8.5 | | | | |
| HG3 | 30 | 37.5 | HH3 | 42 | 52.5 | HC3 | 7.5 | 9.4 | | | | |
| HH1 | 33.5 | 42 | HJ1 | 47 | 60 | HD1 | 8.5 | 10.7 | | | | |
| HH2 | 37.5 | 47 | HJ2 | 52.5 | 65.7 | HD2 | 9.4 | 12 | | | | |
| HH3 | 42 | 52.5 | HJ3 | 60 | 75 | HD3 | 10.7 | 13.4 | | | | |

Note: It maintains a tolerance of ±10% on Luminous Intensity

Dominant Wavelength (λ_D) Bin: R@5mA;G/B @2mA

| | B36J3RGB Series | | | | | | | | | | |
|-----|-----------------|-------------|-----|-----|-----|------|-----|-----|--|--|--|
| WD | | | | | | | | | | | |
| | Red | Red Green B | | | | Blue | | | | | |
| RH2 | 618 | 623 | GH1 | 526 | 530 | BH1 | 464 | 468 | | | |
| RH3 | 623 | 628 | GH2 | 528 | 532 | BH2 | 466 | 470 | | | |
| RH4 | 628 | 633 | GH3 | 530 | 534 | BH3 | 468 | 472 | | | |
| | | | GH4 | 532 | 536 | BH4 | 470 | 474 | | | |
| | | | GH5 | 534 | 538 | | | | | | |

Note: It maintains a tolerance of ±0.5nm on Color Bin

Forward Voltage (Vf) Bin: R@5mA;G/B @2mA

| | B36J3RGB Series | | | | | | | | | |
|-----|-----------------|-----|-------|-----|-----|------|-----|-----|--|--|
| Vf | | | | | | | | | | |
| | Red | | Green | | | Blue | | | | |
| E18 | 1.6 | 2.4 | F2A | 2.1 | 3.1 | F2A | 2.1 | 3.1 | | |

Note: It maintains a tolerance of ±0.05V on forward voltage measurements


| Official Product | HT Part No. B36J3RGB-F6C0001HOU1930 | Customer Pa | art No. | Data Sheet No. |
|-------------------|---|-------------|-------------|----------------|
| Tentative Product | ***** | ********* | ** | |
| | t to changes for improvement without advance , drawings, company confidential all rights | 27/01/2022 | Version 1.1 | Page 7/16 |

Product Features

Electro-Optical Characteristics

| | (I _F Red@5mA,Green &Blue@2mA, T _s 25 °C) | | | | | | | |
|-------------------------|--|------|------------------------|-----|-----------------------------------|---------|------|-------------|
| Part number | | | /avelengt (nm) typ. | | l [*] _∨ (mcd) | Viewing | | |
| | | typ. | max. | λD | λр | Δλ | typ. | Angle 201/2 |
| B36J3RGB-F6C0001HOU1930 | Ultra Bright Red | 1.9 | 2.4 | 621 | 628 | 11 | 32 | 140 |
| | Green | 2.5 | 3.1 | 530 | 521 | 28 | 46 | 140 |
| | Blue | 2.5 | 3.1 | 469 | 465 | 16 | 8 | 140 |

Package Outline Dimension and Recommended Soldering Pattern for Reflow Soldering



| Absolute Maximum Ratings | | | | | | | | |
|--------------------------|--------------------------|---------------------|-----------------------|-----------------|----------------------|------------------------|--|--|
| | | | | | | (T _S 25 °C) | | |
| Series | P _D (mW) | I _F (mA) | I _{FP} (mA) | Vr(V) | T _{OP} (°C) | T _{ST} (°C) | | |
| Calar | Power Forward Current | | | Operation | Storage | | | |
| Color | Dissipation | Forward Current | Pulse Forward Current | Reverse Voltage | Temperature | Temperature | | |
| Red | 24.4 | 5 | 20 | F | 20 . 90 | 40.95 | | |
| Blue/Green | 24.4 | 2 | 20 | 5 | -30~+80 | -40~85 | | |


** Condition for I_{FP} is pulse of 1/10 duty and 0.1msec width

| Official Product | HT Part No. B36J3RGB-F6C0001HOU1930 | Customer Part No. | | Data Sheet No. |
|-------------------|---|-------------------|-------------|----------------|
| Tentative Product | ***** | ***** | | |
| | t to changes for improvement without advance , drawings, company confidential all rights | 27/01/2022 | Version 1.1 | Page 8/16 |



Top Mount RGB Chip LED B36J3RGB-F6C0001HOU1930

Characteristics of B36J3RGB-F6



| Official Product | HT Part No. B36J3RGB-F6C0001HOU1930 | Customer Part No. | | Data Sheet No. |
|-------------------|---|-------------------|-------------|----------------|
| Tentative Product | ***** | ***** | | |
| | t to changes for improvement without advance , drawings, company confidential all rights | 27/01/2022 | Version 1.1 | Page 9/16 |


Precaution for Use

- 1. The chips should not be used directly in any type of fluid such as water, oil, organic solvent, etc.
- 2. When the LEDs are illuminating, the maximum ambient temperature should be first considered before operation.
- 3. LEDs must be stored in a clean environment. A sealed container with a nitrogen atmosphere is necessary if the storage period is over 3 months after shipping.
- 4. The LEDs must be used within seven days after unpacked. Unused products must be repacked in an anti-electrostatic package, folded to close any opening and then stored in a dry and cool space.
- 5. The appearance and specifications of the products may be modified for improvement without further notice.
- 6. The LEDs are sensitive to the static electricity and surge. It is strongly recommended to use a grounded wrist band and anti-electrostatic glove when handling the LEDs.If a voltage over the absolute maximum rating is applied to LEDs, it will damage LEDs.Damaged LEDs will show some abnormal characteristics such as remarkable increase of leak current, lower turn-on voltage and getting unlit at low current.

| Official Product | HT Part No. B36J3RGB-F6C0001HOU1930 | Customer Part No. | | Data Sheet No. |
|-------------------|--|-------------------|-------------|----------------|
| Tentative Product | ***** | **** | | |
| | t to changes for improvement without advance , drawings, company confidential all rights | 27/01/2022 | Version 1.1 | Page 10/16 |




Packaging Tape Dimension



| Dim. A | Dim. B | Dim. C | Q'ty/Reel |
|-----------|-----------|-----------|-----------|
| 0.72±0.03 | 0.72±0.03 | 0.56±0.03 | 24K |


nit: mm




| Official Product | HT Part No. B36J3RGB-F6C0001HOU1930 | Customer Part No. | | Data Sheet No. |
|-------------------|---|-------------------|-------------|----------------|
| Tentative Product | ***** | ***** | | |
| | t to changes for improvement without advance , drawings, company confidential all rights | 27/01/2022 | Version 1.1 | Page 11/16 |



Reel Dimension



Packing



28 boxes per carton is available depending on shipment quantity.


| Official Product | HT Part No. B36J3RGB-F6C0001HOU1930 | Customer Part No. | | Data Sheet No. |
|-------------------|---|-------------------|-------------|----------------|
| Tentative Product | ***** | ***** | | |
| | t to changes for improvement without advance , drawings, company confidential all rights | 27/01/2022 | Version 1.1 | Page 12/16 |

Dry Pack

All SMD optical devices are **MOISTURE SENSITIVE**. Avoid exposure to moisture at all times during transportation or storage. Every reel is packaged in a moisture protected anti-static bag. Each bag is properly sealed prior to shipment.

Upon request, a humidity indicator will be included in the moisture protected anti-static bag prior to shipment.

The packaging sequence is as follows:



Baking

Baking before soldering is recommended when the package has been unsealed for 4weeks. The conditions are as followings:

- 1. MBB open≤672hrs, 50±3°C×(3hrs)
- 2. MBB open>672hrs, $60\pm3^{\circ}C\times(8^{-12hrs})$ and $5^{\circ}RH$, taped reel type.
- 3. 100±3℃×(45min~1hr), bulk type.(散裝)
- 4. 130±3℃×(15min~30min), bulk type.(散裝)

| Official Product | HT Part No. B36J3RGB-F6C0001HOU1930 | Customer Part No. | | Data Sheet No. |
|-------------------|---|-------------------|-------------|----------------|
| Tentative Product | ***** | ***** | | |
| | t to changes for improvement without advance , drawings, company confidential all rights | 27/01/2022 | Version 1.1 | Page 13/16 |

PRECAUTIONS

- 1. Avoid exposure to moisture at all times during transportation or storage.
- 2. Anti-Static precaution must be taken when handling GaN, InGaN, and AlInGaP products.
- 3. It is suggested to connect the unit with a current limiting resistor of the proper size. Avoid applying a reverse voltage beyond the specified limit.
- 4. Avoid operation beyond the limits as specified by the absolute maximum ratings.
- 5. Avoid direct contact with the surface through which the LED emits light.
- 6. If possible, assemble the unit in a clean room or dust-free environment.


Reflow Soldering

Recommend soldering paste specifications:

- 1. Operating temp.: Above 220 ^OC ,60sec
- 2. Peak temp.:260 ^OCMax.,10sec Max.
- 3. Never take next process until the component is cooled down to room temperature after reflow.
- 4. The recommended reflow soldering profile (measuring on the surface of the LED terminal) is following:

Lead-free Solder Profile

5. Reflow soldering should not be done more than two times



| Official Product | HT Part No. B36J3RGB-F6C0001HOU1930 | Customer Part No. | | Data Sheet No. |
|-------------------|---|-------------------|-------------|----------------|
| Tentative Product | ****** | ***** | | |
| | t to changes for improvement without advance , drawings, company confidential all rights | 27/01/2022 | Version 1.1 | Page 14/16 |

Reworking

- Rework should be completed within 5 seconds under 260 °C.
- The iron tip must not come in contact with the copper foil.
- Twin-head type is preferred.

Cleaning

Following are cleaning procedures after soldering:

- An alcohol-based solvent such as isopropyl alcohol (IPA) is recommended.
- Temperature x Time should be 50°C x 30sec. or <30°C x 3min
- Ultra sonic cleaning: < 15W/ bath; bath volume ≤ 1liter
- Curing: 100 ^OC max, <3min

Cautions of Pick and Place

- Avoid stress on the resin at elevated temperature.
- Avoid rubbing or scraping the resin by any object.
- Electric-static may cause damage to the component. Please ensure that the equipment is properly grounded. Use of an ionizer fan is recommended.

| Official Product | HT Part No. B36J3RGB-F6C0001HOU1930 | Customer Part No. | | Data Sheet No. |
|-------------------|---|-------------------|-------------|----------------|
| Tentative Product | ****** | ***** | | |
| | t to changes for improvement without advance , drawings, company confidential all rights | 27/01/2022 | Version 1.1 | Page 15/16 |



Top Mount RGB Chip LED B36J3RGB-F6C0001HOU1930

Revise History

| Rev. | Descriptions | Date | Page |
|------|-----------------------|------------|------|
| 1.0 | - | 01/09/2020 | - |
| 1.1 | Modify Tape Dimension | 27/01/2022 | 11 |
| | | | |
| | | | |
| | | | |
| | | | |
| | | | |
| | | | |
| | | | |
| | | | |
| | | | |
| | | | |
| | | | |
| | | | |
| | | | |

| Official Product | HT Part No. B36J3RGB-F6C0001HOU1930 | Customer Part No. | | Data Sheet No. |
|---|-------------------------------------|-------------------|-------------|----------------|
| Tentative Product | ****** | **** | | |
| Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved. | | 27/01/2022 | Version 1.1 | Page 16/16 |