

STMPE321

3-channel capacitive touchkey controller

Features

- Up to 3 GPIOs
- Up to 3 capacitive touchkey inputs
- Operating voltage 1.65 1.95 V
- Interrupt output pin
- I²C interface (1.8 V operation, 3.3 V tolerant)
- 8 kV HBM ESD protection
- 40 fF resolution, 128-step capacitance measurement
- Advanced data filtering (AFS)
- Environment tracking calibration (ETC)
- Individually adjustable touch variance (TVR) settings for all channels
- Adjustable environmental variance (EVR) for optimal calibration
- Capacitive key sensing capability in 27 µA sleep mode

Applications

- Mobile phones and smartphones
- Portable media players
- Game consoles



Description

The STMPE321 is a 3-channel capacitive touchkey controller. Capacitance measurement is implemented in fully optimized hardware.

All 3 I/Os can be configured via an I^2C bus to function as either capacitive touchkey, or as GPIOs (general purpose I/O).

Table 1.Device summary

Order code	Order code Package	
STMPE321QTR	QFN12 (2.2 x 1.5 mm)	Tape and reel

Contents

1	STMF	PE321 functional overview 3	3			
	1.1	STMPE321 block diagram 3	3			
	1.2	Pin assignment and function 4	1			
	1.3	STMPE321 typical application 5	5			
2	Capa	citance compensation6	ò			
	2.1	Calibration algorithm	7			
		2.1.1 Noise filtering	3			
		2.1.2 Data filtering	3			
	2.2	Power management 9)			
3	I ² C in	terface)			
4	Register map and function description					
5	Syste	em and identification registers 14	ł			
6	Interrupt controller module 17					
7	GPIO controller 22					
8	Capacitive touch module registers					
9	Maxir	num rating	3			
10	Electrical specifications					
	10.1	Capacitive sensing characteristics 34	1			
11	Packa	age mechanical data 35	5			
12	Revis	ion history)			



1 STMPE321 functional overview

The STMPE321 consists of the following blocks:

- GPIO controller
- Impedance sensor
- Touchkey controller
- I²C interface

1.1 STMPE321 block diagram





1.2 Pin assignment and function

Figure 2. QFN12 pin assignment (top view)



Table 2.Pin assignment and function

Pin number	Pin name	Description
1	GPIO_2 / touch 2	GPIO 2
2	GPIO_1 / touch 1	GPIO 1
3	GPIO_0 / touch 0	GPIO 0
4	NC	-
5	SDA	I ² C data
6	SCL	I ² C clock
7	GND	GND
8	VCC	Supply voltage
9	ARef	Reference capacitor for touch sensor
10	NC	-
11	INT	INT output (open drain)
12	RST	RESET (active low) This pin is internally pulled up to V _{CC}



1.3 STMPE321 typical application

The STMPE321 is capable of supporting capacitive sensors of up to 3 channels.







2 Capacitance compensation

The STMPE321 is capable to measuring up to 5.1pF in capacitance difference between the reference point (Zref) and the individual channels. In the case where PCB connection between the sensor pads and the device is too long, the "REFERENCE DELAY" register is able to shift the reference by up to 5.1pF, allowing the TOUCH channels to measure added capacitance 5.1pF with offset of 5.1pF, as shown in following diagram.

In the case where this is still not enough to compensate for the capacitance on sensor lines (due to very long sensor trace), an external capacitor of up to 30 pF could be connected at the A_Ref pin.

This would further shift up the dynamic range of the capacitance measurement.



Figure 4. Capacitance compensation

The sensed capacitance is accessible to the host through the IMPEDANCE registers.



2.1 Calibration algorithm

The STMPE321 maintains 2 parameters for each touch channel: TVR and CALIBRATED IMPEDANCE. CALIBRATED IMPEDANCE is an internal reference which, if the currently measured IMPEDANCE exceeds the CALIBRATED IMPEDANCE by a magnitude of TVR, is considered a "TOUCH".

If the IMPEDANCE is higher than the CALIBRATED IMPEDANCE, but the magnitude does not exceed CALIBRATED IMPEDANCE by TVR, it is not considered a TOUCH. In this case, 2 scenarios are possible:

- 1. Environmental changes have caused the IMPEDANCE to increase
- 2. Finger is near the sensing pad, but not near enough

In case 1, the change in IMPEDANCE is expected to be small, as environmental changes are normally gradual. A value "EVR" is maintained to specify the maximum IMPEDANCE change that is still considered an environmental change.

Table 3.	Calibration action under different scenarios
----------	--

Scenario	Touch sensing and calibration action
IMP>CALIBRATED IMP + TVR	TOUCH, no calibration
IMP <calibrated +="" imp="" td="" tvr<=""><td>NO TOUCH,</td></calibrated>	NO TOUCH,
IMP>CALIBRATED IMP + EVR	no calibration
IMP <calibrated +="" imp="" td="" tvr<=""><td>NO TOUCH,</td></calibrated>	NO TOUCH,
IMP <calibrated +="" evr<="" imp="" td=""><td>new CALIBRATED IMP = previous CALIBRATED</td></calibrated>	new CALIBRATED IMP = previous CALIBRATED
IMP>CALIBRATED IMP	IMP + change in IMP
IMP>CALIBRATED IMP	CALIBRATED IMP + change in IMP
IMP <calibrated imp<="" td=""><td>NO TOUCH, new CALIBRATED IMP = new IMP</td></calibrated>	NO TOUCH, new CALIBRATED IMP = new IMP

'IMP' and 'CALIBRATED IMP' used in this table is not the direct register read-out.

IMP = 127 - impedance register readout

CALIBRATED IMP = 127 - calibrated impedance register readout.

The ETC WAIT register states a period of time for which all TOUCH inputs must remain "NO TOUCH" for the next calibration to be carried out.

The CAL INTERVAL states the period of time between successive calibrations when there are prolonged NO TOUCH conditions.



2.1.1 Noise filtering

When the STMPE321 is operating in the vicinity of highly emissive circuits (DC-DC converters, PWM controllers/drives etc.), the sensor inputs can be affected by high-frequency noise. In this situation, the time-integrating function can be used to distinguish between a real touch, or an emission-related false touch.

The INTEGRATION TIME and STRENGTH THRES registers are used to configure the timeintegrating function of the STMPE321.

2.1.2 Data filtering

The output from the calibration unit provides an instantaneous TOUCH or NO TOUCH status. This output is directed to the filtering stage where the TOUCH is integrated across a programmable period of time. The output of the integration stage is a "STRENGTH" (in the STRENGTH register) that indicates the number of times a TOUCH is detected across the integration period.

The STRENGTH is then compared to the value in STRENGTH THRESHOLD register. If STRENGTH exceeds the STRENGTH THRESHOLD, it is considered a final, filtered TOUCH status.

In the data filtering stage, 3 modes of operation are supported:

Mode 1: Only the touch channel with highest STRENGTH is taken

Mode 2: All touch channels with STRENGTH > STRENGTH THRESHOLD are taken

Mode 3: The 2 touch channels with the highest STRENGTH are taken.

These modes are selected using the FEATURE SELECTOR register. The final, filtered data is accessible through the Touch Byte register.



2.2 Power management

The STMPE321 operates in 3 states, as described below:





On RESET, the STMPE321 enters the ACTIVE state immediately.

Upon a fixed period of inactivity, the device enters a SLEEP state. Any touch activity occurring during a SLEEP state causes the device to return to an ACTIVE state.

In SLEEP mode:

-Calibration continues if the F2A bit is set in the CONTROL register

-Calibration stops if the F2A bit is NOT set in the CONTROL register

If no touch activity is expected, the host may set the device to a HIBERNATE state to save power.

If any key is touched and held, the I²C command to enter SLEEP or HIBERNATE is put on hold until the key is released.



3 I²C interface

The following features are supported by the I²C interface:

- I²C slave device
- Compliance with Philips I²C specification version 2.1
- Standard (up to 100 kbps) and fast (up to 400 kbps) modes.
- 7-bit and 10-bit device addressing modes
- General call
- Start/Restart/Stop
- I²C address is 0x58 (0xB0/0xB1 for write/read, including the LSB)

Start condition

A Start condition is identified by a falling edge of SDATA while SCLK is stable at high state. A Start condition must precede any data/command transfer. The device continuously monitors for a Start condition and does not respond to any transaction unless one is encountered.

Stop condition

A Stop condition is identified by a rising edge of SDATA while SCLK is stable at high state. A Stop condition terminates communication between the slave device and bus master. A read command that is followed by NoAck can be followed by a Stop condition to force the slave device into idle mode. When the slave device is in idle mode, it is ready to receive the next I²C transaction. A Stop condition at the end of a write command stops the write operation to the registers.

Acknowledge bit (ACK)

The acknowledge bit is used to indicate a successful byte transfer. The bus transmitter releases the SDATA after sending eight bits of data. During the ninth bit, the receiver pulls the SDATA low to acknowledge the receipt of the eight bits of data. The receiver may leave the SDATA in high state if it does not acknowledge the receipt of the data.

Data Input

The device samples the data input on SDATA on the rising edge of the SCLK. The SDATA signal must be stable during the rising edge of SCLK and the SDATA signal must change only when SCLK is driven low.

Memory addressing

For the bus master to communicate to the slave device, the bus master must initiate a Start condition, followed by the slave device address. Accompanying the slave device address, there is a Read/WRITE bit (R/W). The bit is set to 1 for a read operation, and 0 for a write operation.

If a match occurs on the slave device address, the corresponding device gives an acknowledgement on the SDA during the 9th bit time. If there is no match, it deselects itself from the bus by not responding to the transaction.



Mode	Byte	Programming sequence			
		Start, Device address, $R/\overline{W} = 0$, Register address to be read			
		Restart, Device address, $R/\overline{W} = 1$, Data Read, STOP			
Read	≥1	If no Stop is issued, the Data Read can be continuously performed. If the register address falls within the range that allows an address auto- increment, then the register address auto-increments internally after every byte of data being read. For those register addresses that fall within a non-incremental address range, the address is kept static throughout the entire write operations. Refer to the memory map table for the address ranges that are auto and non-increment. An example of such a non-increment address is FIFO.			
Write	≥1	Start, Device address, $R/\overline{W} = 0$, Register address to be written, Data Write, Stop			
		If no Stop is issued, the Data Write can be continuously performed. If the register address falls within the range that allows address auto- increment, then the register address auto-increments internally after every byte of data being written in. For those register addresses that fall within a non-incremental address range, the address is kept static throughout the entire write operations. Refer to the memory map table for the address ranges that are auto and non-increment.			

Table 4.Operation modes





4 Register map and function description

This section lists and describes the registers in the STMPE321 device starting with a register map, and then provides detailed descriptions of the register types.

Address	Register name	Bit	Туре	Reset value	Function	
0x00	CHIP_ID_0	8	R	0x03	Device identification	
0x01	CHIP_ID_1	8	R	0x21	Device identification	
0x02	ID_VER	8	R	0x03	Revision number	
0x03	SYS_CFG_1	8	R/W	0x00	System configuration 1	
0x04	SYS_CFG_2	8	R/W	0xEF	System configuration 2	
0x08	INT_CTRL	8	R/W	0x01	Interrupt control register	
0x09	INT_EN	8	R/W	0x01	Interrupt enable register	
0x0A	INT_STA	8	R	0x09	Interrupt status register	
0x0B	GPIO_INT_EN_lsb	8	R/W	0x00	GPIO interrupt enable register	
0x0C	GPIO_INT_EN_msb	8	R/W	0x00	GPIO interrupt enable register	
0x0D	GPIO_INT_STA_lsb	8	R/W	0x00	GPIO interrupt status register	
0x0E	GPIO_INT_STA_msb	8	R/W	0x00	GPIO interrupt status register	
0x10	GPIO_MR	8	R/W	0x00	GPIO monitor pin	
0x12	GPIO_SET	8	R/W	0x00	GPIO set pin state register	
0x14	GPIO_DIR	8	R/W	0x00	GPIO set pin direction register	
0x16	GPIO_FUNCT	8	R/W	0x00	GPIO function register	
0x18	TOUCH_FIFO	64	R	0x00	Fifo access for touch data buffer	
0x20	FEATURE_SEL	8	R/W	0x04	Feature selection	
0x21	ETC_WAIT	8	R/W	0x27	Wait time	
0x22	CAL_INTERVAL	8	R/W	0x30	Calibration interval	
0x23	INTEGRATION_ TIME	8	R/W	0x0F	Integration time	
0x25	CTRL	8	R/W	0x00	Control	
0x26	INT_MASK	8	R/W	0x08	Interrupt mask	
0x27	INT_CLR	8	R/W	0x00	Interrupt clear	
0x28	FILTER_PERIOD	8	R/W	0x00	Filter period	
0x29	FILTER_THRESHOLD	8	R/W	0x00	Filter threshold	
0x2A	REF_DLY	8	R/W	0x00	Reference delay	
0x30 - 0x32	TVR [0-2]	8	R/W	0x08	Touch variance setting	
0x40	EVR	8	R/W	0x04	Environmental variance	

Table 5.Register summary map table



Address	Register name	Bit	Туре	Reset value	Function
0x50-0x52	STRENGTH_THRES [0-2]	8	R/W	0x01	Setting of strength threshold for each channel
0x60 - 0x62	STRENGTH [0-2]	8	R	0x00	Strength
0x70 - 0x72	CAL_IMPEDANCE [0-2]	8	R	0x00	Calibrated impedance
0x80 - 0x82	IMPEDANCE [0-2]	8	R	0x00	Impedance
0x92	INT_PENDING	8	R/W	0x00	Status of GINT interrupt sources

 Table 5.
 Register summary map table (continued)



5 System and identification registers

Address	Register name	Bit	Туре	Reset	Function
0x00	CHIP_ID_0	8	R	0x03	Device identification
0x01	CHIP_ID_1	8	R	0x21	Device identification
0x02	ID_VER	8	R	0x03	Revision number
0x03	SYS_CFG_1	8	R/W	0x00	System configuration 1
0x04	SYS_CFG_2	8	R/W	0xEF	System configuration 2

Table 6. System and identification registers map

CHIP_ID_x

Device identification

Address:	0x00, 0x01
Туре:	R
Reset:	0x03, 0x21
Description:	16(8+8)-bit device identification



ID_VER

Address:	0x02
Туре:	R
Reset:	0x03
Description:	8-bit revision number

SYS_CFG_1

System configuration 1

Revision number

7	6	5	4	3	2	1	0		
	RESERVED			SLEEP	WARM_RESET	SOFT_RESET	HIBERNATE		
Address:	0x03								
Туре:		R/W	R/W						
Reset:		0x00							
Description:		The reset control register enables the reset of the device							
	[7:4] RESERVED								
 [3] SLEEP: Write '1' to enable sleep m mode. [2] WARM_RESET: Write '1' to initiate a warm 1 [1] SOFT_RESET: 				de. Hardwar	e resets this bit to	'0' after it success	fully enters sleep		
				eset. Registe	er content remains	, state machine res	set.		

Write '1' to initiate a soft reset. All registers content and state machines reset.

[0] HIBERNATE: Force the device into hibernation mode.
 Write '1' to enter hibernate mode. Hardware resets this bit to '0' after it successfully enters hibernate mode.



SYS_CFG_2

7	6	5	4	3	2	1	0	
SENSOR CLOCK 2	SENSO CLOCK	R SENSOR 1 CLOCK 0	RESE	RESERVED GPIO CLOCK FIFO CLOCK TOUCH C DISABLE DISABLE DISABLE DISA			TOUCH CLOCK DISABLE	
Address:		0x04						
Туре:		R/W	R/W					
Reset:		0xEF						
Descriptio	scription: This register enables the switching off of the clock supply							
	[7:5]	[7:5] SENSOR CLOCK: See description in Table 7.						
[4] RESERVED								
[3] RESERVED								
[2] GPIO CLOCK DISABLE:								

Write '1' to disable the clock to GPIO unit.

[1] FIFO CLOCK DISABLE:

Write '1' to disable the clock to FIFO unit. This must be set to '0' if touch interrupt is required.

[0] TOUCH CLOCK DISABLE:

Write '1' to disable the clock to TOUCH unit.

Mode	Divider	Sensor clock [2:0]	Active	Calibration
	1	000	12.8 kHz	100 kHz
	2	001	6.4 kHz	50 kHz
Operational (6.5 MHz)	4	010	3.2 kHz	25 kHz
Autosleep (200 kHz)	8	011	1.6 kHz	12.5 kHz
	16	1xx	800 Hz	6.25 kHz
	1	000	400 Hz	3.2 kHz
	2	001	200 Hz	1.6 kHz
	4	010	100 Hz	800 Hz
	8	011	50 Hz	400 Hz
	16	1xx	25 Hz	200 Hz

System configuration 2



Interrupt controller module 6



Interrupt controller module block diagram



INT_CTRL

Interrupt control register

7		6	5	4	3	2	1	0	
			RESERVED			POLARITY	TYPE	INT_EN	
Address:		0x08							
Туре:		R/W							
Reset:	0x01								
Description:	[7.0]	This reg	gister is used ot system dev	to enable co rice.	ontrol of the p	olarity, edge/l	evel and ena	bling of the	
	[7.3]	POLARITY: '0' for active low '1' for active high For active low operation, the INT pin should be externally pulled high. The INT pin is pulled to GND when there is a pending interrupt. For active high operation, the INT pin should be externally pulled to GND. In this mode, the INT pin is pulled to Vace by the device when there is a pending interrupt.							
	[1]	TYPE : '0' for level trigger '1' for edge trigger (pulse width is 200 nS)							

[0] **INT_EN**:

'0' to disable all interrupts

'1' to enable all interrupts



Interrupt enable register

INT_EN

7	6	5	4	3	2	1	0
GPIO	RESERVED			GEN	FIFO	POR	

Address:	0x09
	0/100

Туре:

Reset:

Description:

: This register is used to enable the interruption from a system related interrupt source to the host. Writing '1' in this register enables the corresponding interrupt event to generate interrupt signal at the INT pin. Note that even if the interrupt is not enabled, an interrupt event is still reflected in the interrupt status register.

[7] **GPIO**:

R/W

0x01

One or more level transition in enabled GPIOs

[6:3] RESERVED

Must be set to '0' at all times.

[2] **GEN**:

System INT (A2I, I2A, EOC)

- FIFO: Data available in FIFO. This interrupt can be cleared only if FIFO is empty.
- [0] **POR**:

Power-on reset



INT_STA						Interrupt st	tatus register		
7	6	5	4	3	2	1	0		
GPIO		RESE	RVED		GEN	FIFO	POR		
Address:		0x0A							
Туре:		R/W							
Reset:		0x09	0x09						
Description:		This register i to the host. R ISSYSIOR bit no effect.	s used to e egardless c s are still u	nable the in of whether c pdated. Wri	terruption from a r not the IESYSI ting '1' clears a b	system related OR bits are ena bit in this registe	interrupt source bled, the r. Writing '0' has		
[7] GPIO :									
		One or more level transition in enabled GPIOs							
[6:3]		RESERVED: Some of these bits might be set to '1' by hardware during normal operation. The content of these bit is for internal operation and are not required for normal use of device.							
[2]		GEN: System INT (A2I, IA2, EOC)							
[1] FIFO : Data available in FIFO									
[0] POR : Power-on reset									



GPIO_INT_EN GPIO interrupt enable registerl 7 6 5 3 2 0 4 1 RESERVED IEG Address: 0x0B, 0x0C R/W Type: **Reset:** 0x00 **Description:** The GPIO interrupt enable register is used to enable the interruption from a particular GPIO interrupt source to the host. The IEg[2:0] bits and the interrupt enable mask bits correspond to the GPIO[2:0] pins. [7:3] RESERVED [2:0] IEG[2:0] Interrupt enable GPIO mask (where x = 2 to 0) Writing a '1' to the IE[x] bit enables the interruption to the host. **GPIO INT STA GPIO** interrupt status register

							atus registor
7	6	5	4	3	2	1	0
				ISG			
Address:		0x0D, 0x0E					
Туре:		R/W					
Reset:		0x00					
Description: The GPIO interrupt status register LSB monitors the status of the i particular GPIO pin interrupt source to the host. Regardless of whe IEGPIOR bits are enabled, the INT_STA_GPIO_LSB bits are still u ISG[2:0] bits are the interrupt status bits correspond to the GPIO[2					status of the inte ardless of wheth bits are still upo to the GPIO[2:0]	erruption from a er or not the lated. The pins.	
	[7:0]] ISG[x]: Interrupt status GPIO (where x = 2 to 0) Read:					
		Interrupt status	of the GPIC)[x]. Writing '1'	clears a bit. Wri	ting '0' has no effe	ct.



7 GPIO controller

A total of 3 GPIOs are available in the STMPE321. The GPIO controller contains the registers that allow the host system to configure each of the pins into either a GPIO or Touch input. Unused GPIOs should be configured as outputs to minimize power consumption.

A group of registers is used to control the exact function of each of the 3 GPIOs. The registers and their respective addresses are listed in *Table 8*.

Address	Register name	Description	Auto-increment				
0x10	GPIO_MR_LSB	GPIO monitor pin state	Vac				
0x11	GPIO_MR_MSB	register	165				
0x12	GPIO_SET_LSB	GPIO set pin state	Vos				
0x13	GPIO_SET_MSB	register	165				
0x14	GPIO_DIR_LSB	GPIO set pin direction	Vac				
0x15	GPIO_DIR_MSB	register	165				
0x16	GPIO_FUNCT_LSB		Vac				
0x17	GPIO_FUNCT_MSB	GPIO function register	ies				

Table 8. GPIO controller registers summary map

All GPIO registers are named GPxx, where:

Xxx represents the functional group

For LSB registers:





The function of each bit is shown in Table 9:

Table 9. GPI	O control b	bits function
--------------	-------------	---------------

Register name	Function
GPIO monitor pin state	Reading this bit yields the current state of the bit. Writing has no effect.
GPIO set pin state	Writing '1' to this bit causes the corresponding GPIO to go to '1' state Writing '0' to this bit causes the corresponding GPIO to go to '0' state
GPIO set pin direction	'0' sets the corresponding GPIO to input state, and '1' sets it to output state. All bits are '0' on reset.
GPIO function	'1' sets the corresponding GPIO to function as GPIO, and '0' sets it to touchkey mode.



Touch FIFO

8 Capacitive touch module registers

Table 10. TOUCH_FIFO summary table	
Address	Function
0x18	FIFO-0, LSB
0x19	FIFO-0, MSB
0x1A	FIFO-1, LSB
0x1B	FIFO-1, MSB
0x1C	FIFO-2, LSB
0x1D	FIFO-2, MSB
0x1E	FIFO-3, LSB
0x1F	FIFO-3, MSB

TOUCH_FIFO

7	6	5	4	3	2	1	0
T7	T6	T5	T4	Т3	T2	T1	T0

Address:	0x19, 0x18
Туре:	R

Reset: 0x00

Description:

TOUCH_FIFO is the access port for the internal 4-level FIFO used for buffering the touch events. While it is possible to access each byte in the data structure directly, it is recommended that the FIFO is accessed only via the 0x18 address. The FIFO must be accessed in multiples of 2 bytes (LSB, MSB). For the STMPE321, MSB is reserved and LSB contains a snapshot of the recent touch event. Where Tn is touch status of touch sensing channel n.



FEATURE_SELECT

Feature select

7	6	5	4	3	2	1	0
		RESERVED			AFS	6[1:0]	Filter EN
Address:		0x20					
Туре:		R/W					
Reset:		0x04					
Description:	[7:3]	Controls AFS RESERVED	(advanced	filtering sys	stem and second	d level filtering fea	ature)
	[2:1]	AFS[1:0] : "00': reserved "01' AFS mode '10': AFS mode '11': AFS mode	1 (only 1 str 2 (all keys t 3 (the 2 stro	ongest key) hat are abov ongest keys)	e threshold)		
	[0]	Filter EN: Write '1' to enat	ble filter				

ETC_WAIT

Wait time setting

7	6	5	4	3	2	1	0					
	ETC_WAIT[7:0]											
Address:		0x21										
Туре:		R/W										
Reset:		0x27										
Description:		Sets the wait ti	me betwe	en the calibr	ation and the la	st button touch						
	[7:0]	ETC_WAIT[7:0]:										
		ETC wait time =	ETC_Wait[[7:0] *64 + ser	nsor clock period							
A "non-touch" condition must persist for this wait time, before an ETC operation is carried or												

Range: 5 mS - 20 s



CAL_INTE	Calibratior	Calibration interval					
7	6	5	4	3	2	1	0
				CAL_INTERV/	AL.		
Address:		0x22					
Туре:		R/W					
Reset:		0x30					
Description:		Calibration in	terval				
	[7:0]	CALIBRATION	I INTERVAL	.: n = calibration	nterval [7:0] * se	ensor clock period * 50	

Range: 4 ms - 16 s

INTEGRATION TIME

Integration time

7	6	5	4	3	2	1	0					
	INTEGRATION_TIME[7:0]											
Address:		0x23										
Туре:		R/W										
Reset:		0x0F										
Description:		Integration time										
	[7:0]	Integration time in	n AFS moo	de								
		Total period of int	egration =	sensor clock p	period * integrati	on time [7:0]						

78 µs - 320 ms



CTRL							Control						
7	6	5	4	3	2	1	0						
	F	RESERVED		F2A	HDC_U	HDC_C	HOLD						
Address:		0x25											
Туре:		R/W	I										
Reset:		0x00	00										
Description		Control											
	[7:4]	RESERVED											
	[3]	F2A : Write '1' to force de	2A: Vrite '1' to force device to remain in ACTIVE state at all times										
	[2]	HDC_U: Write '1' to perform unconditional host driven calibration Cleared to '0' when calibration is completed Only applicable HOLD is '1'											
	 [1] HDC_C: Write '1' to perform conditional host driven calibration Calibration is performed if and only if no touch is detected Cleared to '0' when calibration is completed 												
	Only applicable HOLD is '1'												

[0] **HOLD**:

'0' to enable ETC '1' to disable ETC



INT_MASK	K						Interrupt mask
7	6	5	4	3	2	1	0
	F	RESERVED		EOC		RESERVED	
Address:		0x26					
Туре:		R/W					
Reset:		0x08					
Description:		Writing '1' to the	nis register	disables th	e correspondin	ig interrupt sour	ce.
	[7:4]	RESERVED					
	[3]	EOC: End of calibration This interrupt of	on ccurs on bot	h automatic	and forced calibr	ation	
	[2:0]	RESERVED					
INT_CLR							Interrupt clear

7	6	5	4	3	2	1	0
	F	RESERVED		EOC		RESERVED	
Address:		0x27					
Туре:		R/W					
Reset:		0x00					
Description:		Writing '1' to th register.	is register	clears the c	corresponding i	nterrupt source in	INT_PENDING
	[7:4]	RESERVED					
	[3]	EOC:					
		End of calibratio	n				
		This interrupt oc	curs on bot	h automatic a	and forced calibra	ation	

[2:0] RESERVED





FILTER_PERIOD

Filter period

7	6	5	4	3	2	1	0
				FILTER_COUN	NT		
Address:	0x	28					
Туре:	R/	N					
Reset:	0x	00					
Description:	Fil	er period.					
	[7:0] FIL	TER_COUN	T:				
	Ad	ditional filter t	o stabilize	touch output in	AFS mode.		

AFS touch output is monitored for Filter Count [7:0] times every integration time. For each time a "touch status" is detected, an internal "Filter Counter" is incremented once. This counter value is then compared with Filter Threshold (register 0x29).

FILTER_THRESHOLD

Filter threshold

7	6	5	4	3	2	1	0
			F	FILTER_THRE	SHOLD		
Address:	0	x29					
Туре:	F	R/W					
Reset:	0	x00					
Description:	F	ilter threshold					
	[7:0] F	ILTER_THRES	HOLD:				
	A h	n internal "Filte as occurred.	r Counter" is	s compared	with Filter Thresho	old [7:0] to determin	e if a valid touch

REFERENCE_DELAY

Reference delay

7	6	5	4	3	2	1	0			
RESERVED				REFER	ENCE_DELAY					
Address:		0x2A								
Туре:		R/W								
Reset:		0x00								
Description	:	Shifting of cap register is in e	Shifting of capacitive sensor dynamic range. The capacitance value set into this egister is in effect, equivalent to capacitor connected to the A_Ref pin.							
	[7]	RESERVED								
	[6:0]	REFERENCE_I Valid range = 0- Each step repre Warm reset is re	DELAY : 127 sents capac equired after	itance value this value is	of 0.04 pF supdated					



Capacitive touch module registers

TVR						Touch variance setting				
7	6	5	4	3	2	1	0			
RESERVED					TVR					
Address:		0x30 - 0x32								
Туре:		R/W								
Reset:		0x08								
Description	1	Touch variance	e setting							
	[7]	RESERVED								
	[6:0]	TVR:								
		Setting TVR between 0-99								
		A high TVR valu noise	le decrease	s sensitivity of	the sensor, but	increases its tolerar	nce to ambient			

A small TVR value increases the sensitivity

EVR

Environmental variance

7	6	5	4	3	2	1	0
RESERVED				Т	VR		
Address:	C)x40					
Туре:	F	R/W					
Reset:	C)x04					
Description:	E	Environmental	variance s	setting.			
	[7] F	RESERVED					
	[6] E	EVR:					

EVR is used to detect "Non-Touch" condition

STRENGTH_THRESHOLD

Strength threshold

7	6	5	4	3	2	1	0
			S	TRENGTH_THRE	SHOLD		
Address:	0	x50 - 0x52					
Туре:	F	?/W					
Reset:	0	x01					
Description:	S	Strength thres	hold.				
	[7:0] S	TRENGTH_TH	IRESHOLD):			
	S	etting threshold	d to be used	d in AFS mode	e to determine va	alid touch	

Doc ID 15791 Rev 3





STRENGTH							Strength
7	6	5	4	3	2	1	0
			STRE	NGTH			
Address:	0x60 - 0x	x62					
Туре:	R						
Reset:	0x00						
Description:	The num impedan	ber of time: ce	s a sensed ca	apacitance ex	ceeds the ca	librated refer	rence

[7:0] STRENGTH:

Read-only field

Counts the number of times a sensed impedance exceeds calibrated reference impedance and integration time. Maximum strength equals Integration Time [7:0]



Calibrated impedance

CALIBRATED_IMPEDANCE

7		6	5	4	3	2	1	0
				CAL_IMP	EDANCE			
Address:		0x70 - 0	x72					
Туре:		R						
Reset:		0x00						
Description:		Calibrate	ed impedan	ce is a refere	nce value ma	aintained by th	ne device.	
	[7:0]	CALIBR	ATED IMPED	ANCE:				
		Calibrate	d reference ir	mpedance				

IMPEDANCE

Impedance

7	6	5	4	3	2	1	0
			IMPEI	DANCE			
Address:	0x80 - (0x82					
Туре:	R						
Reset:	0x00						
Description:	Impedance is the instantaneous impedance value seen at the input pin of each apacitive sensing pin.					of each	
[7:0	IMPED Currentl capacita When th When th	ANCE: y sensed impendence at the sen nis register reations register reations register reations reations and the sentence at th	edance. This ir nsing channel. Ids 0x7F, refere Ids 0x00, refer	npedance reac ence capacitan ence capacitar	ling decreases ce should be r ice should be i	with the increa educed. ncreased.	ase of the

TINT_PENDING

Interrupt pending

7	6	5	4	3	2	1	0	
RESERVED			EOC		RESERVED			
Address:	0x92							
Туре:	R	ł						
Reset:	0x00							
Description: Reflects the status of each inter				upt source.				
[7	7:4] RESER	VED						
	[3] EOC : End of c	alibration						

[2:0] RESERVED



9 Maximum ratings

Stressing the device above the rating listed in the "absolute maximum ratings" table may cause permanent damage to the device. These are stress ratings only, and operation of the device at these or any other conditions above those indicated in the operating sections of this specification is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

Symbol	Parameter			Unit	
Symbol Parameter		Min	Тур	Max	Omt
V _{CC}	Power supply	-	-	2.5	V
V _{ESD}	ESD protection on each GPIO/touch pin			8	kV

Table 11.	Absolute	maximum	ratings
-----------	----------	---------	---------



10 Electrical specifications

Symbol	Paramatar	Test condition			Unit	
Symbol	Farameter	Test condition	Min	Тур	Max	Onit
V _{CC}	Core supply voltage		1.65	-	1.95	V
I _{hibernate}	HIBERNATE current	No touch sensing capability	-	1.8	3.0	μΑ
I _{sleep}	SLEEP current	Touch sensing active, no touch	-	27	43	μΑ
I _{active}	ACTIVE current	100% touch activity	-	280	470	μA
V _{IL}	Input voltage low state	V _{CC} =1.8 V	-0.3V	-	0.2V _{CC}	V
V _{IH}	Input voltage high state	V _{CC} =1.8 V	0.8Vcc	-	V_{CC} +0.3V	V
V _{OL}	Output voltage low state	V _{CC} =1.8 V, I _{OUT} = 4 mA	-0.3V	-	0.25V _{CC}	V
V _{OH}	Output voltage high state	V _{CC} =1.8 _{OUT} V, I _{OUT} = 4 mA	0.75Vcc	-	V _{CC} +0.3V	V
V _{OL} (I ² C)	Output voltage low state	I _{OL} =4 mA	-0.3V	-	0.25V _{CC}	V
L .	Input leakage (GPIO)	GPIO as input, V _{IN} = 2.0 V	-	-	0.5	μA
'leakage	Input leakage (SCL, SDA, RST)	V _{IN} = V _{CC} = 1.95 V	-	-	0.5	μA

Table 12.	DC electrical characteristics (-40 - 85 °C unless otherwise stated))

10.1 Capacitive sensing characteristics

Table 13. Capacitive sensing characteristics

Symbol	Parameter	Test condition	Value			llmit
		Test condition	Min	Тур	Max	Unit
Res	Capacitive measurement resolution	Aref = not connected	-	40	-	fF
DR	Dynamic range	Aref = not connected	-	5.1	-	pF
L	Linearity of sensor	Aref = not connected Maximum deviation calculated from full scale capacitance measurement data	-	10	-	%



11 Package mechanical data

In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK[®] packages, depending on their level of environmental compliance. ECOPACK[®] specifications, grade definitions and product status are available at: www.st.com. ECOPACK[®] is an ST trademark.



Figure 8. Package outline for QFN12 (2.2 x 1.5 x 0.5 mm) - 0.40 mm pitch

1. Drawing not to scale.

2. Dimensions are in millimeters.



			•	
Symbol	Millimeters			
Symbol	Min	Тур	Мах	
A	0.50	_	0.60	
A1	0	_	_	
b	0.15	_	0.25	
D	_	1.50	_	
E	_	2.20	_	
е	_	0.40	_	
L	0.35	_	0.45	

Table 14. Mechanical data for QFN12 (2.2 x 1.5 x 0.5 mm) - 0.40 mm pitch





1. Drawing not to scale.

2. Dimensions are in millimeters.





Figure 10. Carrier tape for QFN12 (2.2 x 1.5 x 0.5 mm) - 0.40 mm pitch





Figure 11. Reel information for QFN12 (2.2 x 1.5 x 0.5 mm) - 0.40 mm pitch

1. Drawing not to scale.

2. Dimensions are in millimeters





12 Revision history

Table 15. Document revision history

Date	Revision	Changes
19-Jun-2009	1	Initial release.
29-Jul-2009	2	Deleted "internal regulator" from the Features section. Modified: <i>Figure 1, Chapter 2, Figure 4. Chapter 4</i> and <i>Chapter 5, Chapter 1.3</i> and <i>Chapter 7</i> .
12-Aug-2009 3		Modified: <i>Figure 4</i> .



Please Read Carefully:

Information in this document is provided solely in connection with ST products. STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, modifications or improvements, to this document, and the products and services described herein at any time, without notice.

All ST products are sold pursuant to ST's terms and conditions of sale.

Purchasers are solely responsible for the choice, selection and use of the ST products and services described herein, and ST assumes no liability whatsoever relating to the choice, selection or use of the ST products and services described herein.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted under this document. If any part of this document refers to any third party products or services it shall not be deemed a license grant by ST for the use of such third party products or services, or any intellectual property contained therein or considered as a warranty covering the use in any manner whatsoever of such third party products or services or any intellectual property contained therein.

UNLESS OTHERWISE SET FORTH IN ST'S TERMS AND CONDITIONS OF SALE ST DISCLAIMS ANY EXPRESS OR IMPLIED WARRANTY WITH RESPECT TO THE USE AND/OR SALE OF ST PRODUCTS INCLUDING WITHOUT LIMITATION IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION), OR INFRINGEMENT OF ANY PATENT, COPYRIGHT OR OTHER INTELLECTUAL PROPERTY RIGHT.

UNLESS EXPRESSLY APPROVED IN WRITING BY AN AUTHORIZED ST REPRESENTATIVE, ST PRODUCTS ARE NOT RECOMMENDED, AUTHORIZED OR WARRANTED FOR USE IN MILITARY, AIR CRAFT, SPACE, LIFE SAVING, OR LIFE SUSTAINING APPLICATIONS, NOR IN PRODUCTS OR SYSTEMS WHERE FAILURE OR MALFUNCTION MAY RESULT IN PERSONAL INJURY, DEATH, OR SEVERE PROPERTY OR ENVIRONMENTAL DAMAGE. ST PRODUCTS WHICH ARE NOT SPECIFIED AS "AUTOMOTIVE GRADE" MAY ONLY BE USED IN AUTOMOTIVE APPLICATIONS AT USER'S OWN RISK.

Resale of ST products with provisions different from the statements and/or technical features set forth in this document shall immediately void any warranty granted by ST for the ST product or service described herein and shall not create or extend in any manner whatsoever, any liability of ST.

ST and the ST logo are trademarks or registered trademarks of ST in various countries.

Information in this document supersedes and replaces all information previously supplied.

The ST logo is a registered trademark of STMicroelectronics. All other names are the property of their respective owners.

© 2009 STMicroelectronics - All rights reserved

STMicroelectronics group of companies

Australia - Belgium - Brazil - Canada - China - Czech Republic - Finland - France - Germany - Hong Kong - India - Israel - Italy - Japan -Malaysia - Malta - Morocco - Philippines - Singapore - Spain - Sweden - Switzerland - United Kingdom - United States of America

www.st.com

Doc ID 15791 Rev 3

