

ISD8102 / ISD8104

2W Class-AB Audio Amplifier

with Chip Enable

2 Different Bonding Configurations:

i) ISD8102 - Headphone Sense IN (SE / Diff)

ii) ISD8104 - Differential Input pair



TABLE OF CONTENTS

1 GENERAL DESCRIPTION 3

2 FEATURES 4

3 BLOCK DIAGRAM 5

4 PINOUT CONFIGURATION: SOP- 8..... 7

5 PIN DESCRIPTION..... 8

6 ELECTRICAL CHARACTERISTICS 9

 6.1 OPERATING CONDITIONS9

 6.2 DC PARAMETERS9

 6.3 AC PARAMETERS 10

 6.3.1 Analog Characteristics; $C_{ref}=1\mu F / C_{vdd} = 1\mu F$ 10

 6.3.2 Speaker Outputs 11

 6.3.3 Chip Enable Threshold Voltage 12

 6.3.4 Output Noise Spectrum 12

PACKAGE SPECIFICATION..... 14

 6.4 8 LEAD SOP- 8 (EX-PAD)..... 14

ORDERING INFORMATION 15

7 REVISION HISTORY 16

Preliminary

1 GENERAL DESCRIPTION

The **ISD8102/ ISD8104 (bonding option)** is a general purpose analog audio amplifier, which is capable of driving a 4-ohm load with up to 2Wrms output power. This device includes current limiting and a chip enable pin with extremely low standby current and excellent pop-and-click suppression.

Also included is the ability to be configured with either single-ended or differential inputs. Internal resistors set the device to have default 20dB gain (ISD8102/ISD8104), and with external resistors any gain less than this can be achieved. The device is unity gain stable, including use with external feedback resistors and external capacitors as may be optionally used for implementing simple filtering functions.

ISD8102:

ISD8102 has a special function to choose SE/BTL outputs, which is useful in Headphone Sense Input applications, and its internal gain setting is 20dB. SE is used to drive the Headphone load; otherwise, BTL is used to drive the speaker load as low as 4Ω.

ISD8104:

ISD8104 can have Single-Ended / Differential inputs, and its internal gain setting is 20dB.

2 FEATURES

- 2 Different Bonding Options
- Wide power supply range and excellent standby current
 - 2.0Vdc - 6.8Vdc operation
 - <1uA standby current
- High power output (capless BTL configuration)
 - Up to 2-W output into 4-ohm load (<10% distortion) with 5Vdc supply voltage
 - < 0.1% distortion at 600mW into 8-ohms with 5Vdc supply voltage
- Robust High Power Operation and Protection Features
 - Package option for SOP-8 with integrated metal thermal heatsink pad
 - Current limiting for over-current conditions
- Excellent pop-and-click performance
 - Low to inaudible pop/click using Chip Enable
- Single-Ended or Differential signal inputs
 - > 75dB common mode rejection in differential mode
 - > 70dB power supply noise rejection
- Very fast start-up time
 - Less than 1msec when using Chip Enable
- Suitable for a wide range of applications
- Less BOM cost / Easy PCB layout
- Package options: Pb-free SOP-8, SOP-8 (Ex-Pad)
- Temperature Range: -40°C to +85°C



3 BLOCK DIAGRAM




Figure 3-1 ISD8102 Headphone Configuration Block Diagram




Figure 3-3 ISD8104 Differential Input Pair Block Diagram

Preliminary

4 PINOUT CONFIGURATION: SOP- 8




Figure 4-1 ISD8102 8-Lead SOP Pin Configuration




Figure 4-3 ISD8104 8-Lead SOP Pin Configuration

5 PIN DESCRIPTION

Pin Number	Pin Name	I/O	Function
1	CE	I	Chip Enable
2	VREF	O	Internal Reference Voltage (1/2 Vdd)
3	MODE	I	Single-Ended / Differential Output Logic Control
4	VIN	I	Inverting Signal Input
5	VOUTP	O	Non-Inverting Speaker Output
6	VDD	I	Supply Voltage
7	GND	I	Ground
8	VOUTN	O	Inverting Speaker Output
9	Ex-Pad	I	Thermal Tab (must be connected to Vss, SOP-8 package, only)

Table 5-1 ISD8102 8-Lead SOP Pin Description

Pin Number	Pin Name	I/O	Function
1	CE	I	Chip Enable
2	VREF	O	Internal Reference Voltage (1/2 Vdd)
3	VIP	I	Non-Inverting Signal Input
4	VIN	I	Inverting Signal Input
5	VOUTP	O	Non-Inverting Speaker Output
6	VDD	I	Supply Voltage
7	GND	I	Ground
8	VOUTN	O	Inverting Speaker Output
9	Ex-Pad	I	Thermal Tab (must be connected to Vss, SOP-8 package, only)

Table 5-3 ISD8104 8-Lead SOP Pin Description

6 ELECTRICAL CHARACTERISTICS

6.1 OPERATING CONDITIONS

OPERATING CONDITIONS (DIE)

CONDITIONS	VALUES
Operating temperature range ¹	-40°C to +85°C
Supply voltage (V_{DD})	+2.0V to +6.8V
Ground voltage (V_{SS})	0V
Input voltage (V_{DD})	V_{SS} to V_{DD}
Voltage applied to any pins	$(V_{SS} - 0.3V)$ to $(V_{DD} + 0.3V)$

OPERATING CONDITIONS (INDUSTRIAL PACKAGED PARTS)

CONDITIONS	VALUES
Operating temperature range (Case temperature) ¹	-40°C to +85°C
Supply voltage (V_{DD})	+2.0V to +6.8V
Ground voltage (V_{SS})	0V
Input voltage (V_{DD})	V_{SS} to V_{DD}
Voltage applied to any pins	$(V_{SS} - 0.3V)$ to $(V_{DD} + 0.3V)$

Notes: ^[1] Conditions $V_{DD}=5V$, $T_A=25^\circ C$ unless otherwise stated. Die temperature must at all times be kept less than 125°C by appropriate thermal design of the system.

6.2 DC PARAMETERS

PARAMETER	SYMBOL	MIN	TYP ^[1]	MAX	UNITS	CONDITIONS
Supply Voltage	V_{DD}	2.0		6.8	V	
Operating Current	I_{DD}		3.6		mA	$V_{DD}= 5V$, no load
Standby Current	I_{SB}		0.1	<1	μA	$V_{DD}= 5V$
CE input resistance			20k		ohm	Internal pull-down @ 0dB
CE input current			120		μA	CE=2.3V, $V_{DD}= 5V$
CE threshold enabled	V_{ENL}		<0.9		V	All supply voltages
CE threshold standby	V_{ENH}		>1.5		V	All supply voltages
VREF Reference Voltage			$V_{DD}/2$		V	

Notes: ^[1] Conditions $V_{DD}=5V$, $T_A=25^\circ C$ unless otherwise stated. Die temperature must at all times be kept less than 125°C by appropriate thermal design of the system.

6.3 AC PARAMETERS

6.3.1 Analog Characteristics; Cref=1uF / Cvdd = 1uF

PARAMETER	SYMBOL	MIN	TYP	MAX	UNITS	CONDITIONS
Audio Input Voltage Range			0.3 - 6.5		V	Vdd = 6.8Vdc
			0.3 - 3.4		V	Vdd = 3.7Vdc
			0.3 - 1.7		V	Vdd = 2.0Vdc
Inverting Input Impedance			TBD			Gain=20dB
Non-Inverting Input Impedance			TBD			Gain=20dB
Power Supply Rejection Ratio	PSRR		75dB			Vdd = 5Vdc
Common Mode Rejection Ratio	CMRR		70dB			Signal at INP = INV
Voltage Gain			20dB			Rinput = zero-ohms
Enable Time from power-on Vdd = CE (device always on)			n/a			determined by application circuit
Enable Time from Standby			0.5		msec	Single-ended
Enable Time from Standby			0.5		msec	Differential
Pop-and-Click from Standby ¹			<10		mV	Single Ended
Pop-and-Click from Standby ¹			<10		mV	Differential
Thermal Resistance			60		°C/W	SOP-8 (with Ex-Pad)
Thermal Resistance			150		°C/W	SOP-8

Notes: ^[1] Impulse voltage that is potentially audible. After impulse, there is a slow ramp from standby Vref to operating Vref, which is typically inaudible with Cref = 1uF

6.3.2 Speaker Outputs

PARAMETER	SYMBOL	MIN	TYP ^[1]	MAX	UNITS	CONDITIONS
Signal-to-Noise Ratio	SNR		100		dB	0dB gain, 5Vdc
Load Impedance	$R_{L(SPK)}$		4		Ω	
Output Offset Voltage			8		mV	


PARAMETER	SYMBOL	MIN	TYP ^[1]	MAX	UNITS	CONDITIONS (THD+N)
Output Power (BTL mode) Load 4 Ω Vdd=5Vdc / 0dB gain	P_{BTL}		600		mW	<0.1% distortion
	P_{BTL}		1600		mW	<1% distortion
	P_{BTL}		2000		mW	<10% distortion

PARAMETER	SYMBOL	MIN	TYP ^[1]	MAX	Units	Conditions (THD+N)
Output Power (BTL mode) Load 8 Ω Vdd=5Vdc / 0dB gain	P_{BTL}		600		mW	<0.1% distortion
	P_{BTL}		1200		mW	<1% distortion
	P_{BTL}		1400		mW	<10% distortion

Notes: ^[1] Conditions $V_{DD}=5V$, $T_A=25^\circ C$ unless otherwise stated. Die temperature must at all times be kept less than $125^\circ C$ by appropriate thermal design of the system.




6.3.3 Chip Enable Threshold Voltage




6.3.4 Output Noise Spectrum

Noise spectrum at Vdd = 5.0Vdc, Gain = 0dB, BW < 22kHz





Noise Spectrum at Vdd = 5.0Vdc, Gain = 20dB, BW < 22kHz





Preliminary

PACKAGE SPECIFICATION

6.48 LEAD SOP-8 (EX-PAD)



DETAIL A




CONTROL DIMENSIONS ARE IN MILLIMETERS.

SYMBOL	MILLIMETER			INCH		
	MIN.	NOM.	MAX.	MIN.	NOM.	MAX.
A	1.35	-	1.75	0.053	-	0.069
A1	0.05	-	0.15	0.002	-	0.006
b	0.33	-	0.51	0.013	-	0.020
C	0.19	-	0.25	0.008	-	0.010
D	4.8	-	5.00	0.188	-	0.196
E	3.8	-	4.0	0.150	-	0.157
e	1.27 BASIC			0.050 BASIC		
H _E	5.8	-	6.20	0.228	-	0.244
Y	-	-	0.10	-	-	0.004
L	0.40	-	1.27	0.016	-	0.050
θ	0°	-	10°	0°	-	10°

ORDERING INFORMATION

ISD8102 X Y I



7 REVISION HISTORY

Version	Date	Description
0.0	Aug, 2010	Initial draft
0.1	Aug, 2010	Package Update
0.2	Oct, 2010	Internal Gain Spec Update

Preliminary

Nuvoton products are not designed, intended, authorized or warranted for use as components in systems or equipment intended for surgical implantation, atomic energy control instruments, airplane or spaceship instruments, transportation instruments, traffic signal instruments, combustion control instruments, or for other applications intended to support or sustain life. Furthermore, Nuvoton products are not intended for applications wherein failure of Nuvoton products could result or lead to a situation wherein personal injury, death or severe property or environmental damage could occur.

Nuvoton customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Nuvoton for any damages resulting from such improper use or sales.

The contents of this document are provided only as a guide for the applications of Nuvoton products. Nuvoton makes no representation or warranties with respect to the accuracy or completeness of the contents of this publication and reserves the right to discontinue or make changes to specifications and product descriptions at any time without notice. No license, whether express or implied, to any intellectual property or other right of Nuvoton or others is granted by this publication. Except as set forth in Nuvoton's Standard Terms and Conditions of Sale, Nuvoton assumes no liability whatsoever and disclaims any express or implied warranty of merchantability, fitness for a particular purpose or infringement of any Intellectual property.

The contents of this document are provided "AS IS", and Nuvoton assumes no liability whatsoever and disclaims any express or implied warranty of merchantability, fitness for a particular purpose or infringement of any Intellectual property. In no event, shall Nuvoton be liable for any damages whatsoever (including, without limitation, damages for loss of profits, business interruption, loss of information) arising out of the use of or inability to use the contents of this documents, even if Nuvoton has been advised of the possibility of such damages.

Application examples and alternative uses of any integrated circuit contained in this publication are for illustration only and Nuvoton makes no representation or warranty that such applications shall be suitable for the use specified.

This datasheet and any future addendum to this datasheet is(are) the complete and controlling ISD[®] ChipCorder[®] product specifications. In the event any inconsistencies exist between the information in this and other product documentation, or in the event that other product documentation contains information in addition to the information in this, the information contained herein supersedes and governs such other information in its entirety. This datasheet is subject to change without notice.

Copyright[®] 2005, Nuvoton Technology Corporation. All rights reserved. ChipCorder[®] and ISD[®] are trademarks of Nuvoton Technology Corporation. All other trademarks are properties of their respective owners.

Headquarters

No. 4, Creation Rd. III
Science-Based Industrial Park,
Hsinchu, Taiwan
TEL: 886-3-5770066
FAX: 886-3-5665577
<http://www.Nuvoton.com.tw/>

Nuvoton Technology Corporation America

2727 North First Street, San Jose,
CA 95134, U.S.A.
TEL: 1-408-9436666
FAX: 1-408-5441797
<http://www.Nuvoton-usa.com/>

Nuvoton Technology (Shanghai) Ltd.

27F, 299 Yan An W. Rd. Shanghai,
200336 China
TEL: 86-21-62365999
FAX: 86-21-62356988

Taipei Office

9F, No. 480, Pueiguang Rd.
Neihu District
Taipei, 114 Taiwan
TEL: 886-2-81777168
FAX: 886-2-87153579

Nuvoton Technology Corporation Japan

7F Daini-ueno BLDG. 3-7-18
Shinyokohama Kohokuku,
Yokohama, 222-0033
TEL: 81-45-4781881
FAX: 81-45-4781800

Nuvoton Technology (H.K.) Ltd.

Unit 9-15, 22F, Millennium City,
No. 378 Kwun Tong Rd.,
Kowloon, Hong Kong
TEL: 852-27513100
FAX: 852-27552064

Please note that all data and specifications are subject to change without notice.
All the trademarks of products and companies mentioned in this datasheet belong to their respective owners.